

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921530

Luminaire Tested: DFN2DIP-HX2F0-020D060US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921530
REPORT IS A COMBINATION OF REPORTS P899191 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D060US940-FLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6500.6 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921530

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921530

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1635	1635	1635
5°	1635	1608	1620
10°	1619	1583	1595
15°	1593	1553	1558
20°	1558	1513	1520
25°	1523	1466	1476
30°	1481	1422	1422
35°	1440	1370	1365
40°	1390	1318	1309
45°	1340	1266	1253
50°	1286	1210	1189
55°	1228	1147	1128
60°	1164	1072	1059
65°	1092	994	977
70°	1002	898	889
75°	878	784	803
80°	727	638	647
85°	493	400	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2268 cd/sqm

TEST NUMBER: P921530

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	1.0
10°-20°	183.8	2.8
20°-30°	270.1	4.2
30°-40°	313.7	4.8
40°-50°	313.3	4.8
50°-60°	273.2	4.2
60°-70°	201.9	3.1
70°-80°	114.2	1.8
80°-90°	35.0	0.5
90°-100°	104.7	1.6
100°-110°	332.7	5.1
110°-120°	569.3	8.8
120°-130°	748.8	11.5
130°-140°	840.5	12.9
140°-150°	824.2	12.7
150°-160°	691.4	10.6
160°-170°	458.5	7.1
170°-180°	160.3	2.5
0°-30°	519.1	8.0
0°-40°	832.8	12.8
0°-60°	1419.3	21.8
0°-90°	1770.4	27.2
90°-120°	1006.7	15.5
90°-150°	3420.1	52.6
90°-180°	4730.0	72.8
0°-180°	6500.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	694	691	684	689	688	66
15°	661	657	648	651	647	186
25°	598	592	581	582	581	275
35°	516	509	498	494	491	322
45°	420	415	405	398	395	324
55°	318	314	306	298	294	284
65°	214	210	204	198	194	212
75°	112	111	107	103	105	120
85°	27	27	26	24	23	30
90°	2	18	50	47	48	6
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	

TEST NUMBER: P921530

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	693.9	693.9	693.9	693.9	693.9
2.5°	697.9	694.6	687.2	693.9	692.7
5°	693.9	691.3	683.9	689.3	688.0
7.5°	689.3	685.3	678.0	683.3	682.0
10°	682.0	677.3	669.3	674.6	672.6
12.5°	671.9	668.0	660.0	663.3	661.9
15°	660.6	656.7	647.9	650.6	647.3
17.5°	646.6	642.7	633.9	637.2	633.9
20°	631.2	627.2	617.9	619.9	617.2
22.5°	615.9	609.9	601.2	601.2	599.9
25°	597.9	592.5	581.2	582.5	581.2
27.5°	577.8	573.2	564.5	562.6	559.2
30°	557.9	552.5	542.5	540.6	537.8
32.5°	536.5	532.5	521.8	517.8	515.1
35°	515.9	509.2	498.5	494.5	491.1
37.5°	492.5	486.4	475.7	471.1	467.7
40°	468.4	463.1	452.4	446.5	443.7
42.5°	445.1	439.7	429.1	422.4	418.4
45°	419.7	415.1	405.0	397.7	395.0
47.5°	395.0	390.4	379.7	372.3	368.4
50°	369.0	365.7	356.3	347.0	343.7
52.5°	343.7	338.9	330.3	323.0	318.3
55°	317.6	313.6	305.6	297.7	294.3
57.5°	291.6	288.3	279.6	271.6	268.9
60°	265.6	263.0	253.6	246.2	244.2
62.5°	240.2	235.5	228.9	222.2	219.5
65°	214.2	210.2	203.6	197.5	194.2
67.5°	187.5	184.1	178.2	173.5	170.9
70°	162.8	160.2	154.1	149.5	146.9
72.5°	137.5	134.8	131.4	126.8	124.8
75°	112.1	110.8	107.4	103.4	104.8
77.5°	89.4	86.8	85.3	83.4	81.4
80°	66.8	66.1	64.7	62.7	61.3
82.5°	45.4	45.4	44.8	42.1	42.1
85°	27.3	26.7	26.0	24.0	23.4
87.5°	12.0	10.7	9.4	7.4	6.7
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7

TEST NUMBER: P921530

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1

TEST NUMBER: P921530

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.23	6.92	7.36	8.04	9.61	5.81	6.50	6.94	7.62	9.18
	3H	7.85	8.47	8.99	9.60	11.18	7.40	8.01	8.53	9.14	10.72
	4H	8.42	9.00	9.57	10.13	11.72	7.96	8.54	9.11	9.68	11.26
	6H	8.79	9.33	9.95	10.46	12.06	8.33	8.87	9.49	10.00	11.60
	8H	8.88	9.39	10.04	10.54	12.13	8.42	8.93	9.58	10.08	11.67
	12H	8.91	9.40	10.08	10.54	12.15	8.45	8.94	9.61	10.08	11.69
4H	2H	6.66	7.25	7.82	8.38	9.96	6.32	6.91	7.48	8.04	9.63
	3H	8.48	8.97	9.64	10.13	11.73	8.10	8.59	9.26	9.75	11.34
	4H	9.17	9.62	10.33	10.77	12.38	8.78	9.23	9.94	10.37	11.99
	6H	9.65	10.04	10.82	11.21	12.81	9.26	9.64	10.43	10.81	12.42
	8H	9.79	10.15	10.95	11.31	12.93	9.39	9.75	10.56	10.91	12.53
	12H	9.84	10.17	11.02	11.34	12.96	9.43	9.76	10.62	10.93	12.56
8H	4H	9.34	9.70	10.51	10.86	12.48	8.99	9.35	10.16	10.51	12.13
	6H	9.94	10.23	11.13	11.44	13.05	9.59	9.88	10.77	11.08	12.70
	8H	10.14	10.40	11.33	11.58	13.22	9.78	10.04	10.98	11.22	12.86
	12H	10.25	10.47	11.44	11.65	13.32	9.88	10.11	11.07	11.28	12.95
12H	4H	9.32	9.64	10.50	10.81	12.44	8.97	9.30	10.16	10.47	12.10
	6H	9.96	10.22	11.15	11.40	13.04	9.62	9.88	10.81	11.06	12.70
	8H	10.18	10.40	11.37	11.58	13.25	9.83	10.06	11.03	11.24	12.91

END OF REPORT