

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921532

Luminaire Tested: DFN2DIP-HX2F0-020D060US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P921532  
REPORT IS A COMBINATION OF REPORTS P899192 AND P896039  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-020D060US940-RLLFLL  
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6250.9 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 63.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P921532  
CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-RLFL

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ··· 90°-270°



TEST NUMBER: P921532

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24				24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18				18
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20	15				15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	13				13
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16	12				12
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14	11				11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12	9				9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11	8				8
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8				8
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9	7				7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1737	1737	1737
5°	1737	1705	1717
10°	1717	1667	1658
15°	1690	1608	1569
20°	1656	1529	1460
25°	1622	1440	1355
30°	1576	1349	1224
35°	1530	1253	1108
40°	1484	1153	976
45°	1431	1042	857
50°	1376	931	741
55°	1318	814	629
60°	1251	691	515
65°	1174	567	460
70°	1079	450	412
75°	961	389	369
80°	791	315	309
85°	516	195	218

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2268 cd/sqm



TEST NUMBER: P921532

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.1	1.1
10°-20°	189.6	3.0
20°-30°	266.3	4.3
30°-40°	290.2	4.6
40°-50°	266.8	4.3
50°-60°	209.5	3.4
60°-70°	136.4	2.2
70°-80°	70.2	1.1
80°-90°	22.7	0.4
90°-100°	104.7	1.7
100°-110°	332.7	5.3
110°-120°	569.3	9.1
120°-130°	748.8	12.0
130°-140°	840.5	13.4
140°-150°	824.2	13.2
150°-160°	691.4	11.1
160°-170°	458.5	7.3
170°-180°	160.3	2.6
0°-30°	525.0	8.4
0°-40°	815.2	13.0
0°-60°	1291.4	20.7
0°-90°	1520.7	24.3
90°-120°	1006.7	16.1
90°-150°	3420.1	54.7
90°-180°	4730.0	75.7
0°-180°	6250.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	737	734	725	731	729	70
15°	701	694	671	658	652	198
25°	636	615	571	544	534	293
35°	548	514	456	414	399	343
45°	448	404	334	286	270	346
55°	341	289	217	177	164	305
65°	230	176	116	94	91	228
75°	123	76	53	49	48	130
85°	29	15	13	13	13	33
90°	2	18	50	47	48	6
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P921532

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	737.1	737.1	737.1	737.1	737.1
2.5°	740.4	737.1	729.7	736.5	735.1
5°	737.1	733.8	725.0	731.1	729.1
7.5°	731.1	727.1	717.7	720.4	717.0
10°	723.1	718.4	705.1	703.0	699.1
12.5°	713.1	707.0	689.0	685.1	677.7
15°	701.1	693.7	671.0	658.3	651.8
17.5°	687.1	676.4	648.4	633.6	623.0
20°	671.0	657.6	624.4	607.7	593.0
22.5°	653.7	638.4	599.7	577.0	567.0
25°	636.4	615.0	571.0	543.7	533.6
27.5°	615.7	593.0	544.3	512.9	497.6
30°	593.7	568.3	515.0	481.0	462.9
32.5°	572.3	541.6	487.0	446.9	430.3
35°	548.3	514.3	455.7	413.6	398.9
37.5°	524.9	488.2	426.2	380.2	363.6
40°	500.2	460.3	395.6	348.2	330.8
42.5°	474.9	432.3	364.9	315.5	298.9
45°	448.3	403.5	333.6	286.1	270.1
47.5°	422.9	375.6	303.5	256.1	241.5
50°	394.9	347.6	274.2	228.1	214.2
52.5°	367.5	317.4	246.1	202.2	189.5
55°	340.8	288.8	216.8	176.8	164.1
57.5°	313.5	260.1	190.8	153.5	142.8
60°	285.5	232.1	163.5	129.5	118.8
62.5°	258.2	204.8	140.1	108.1	102.7
65°	230.2	176.1	116.1	93.5	91.4
67.5°	203.5	149.4	93.5	82.0	80.1
70°	175.4	123.4	77.3	70.7	68.0
72.5°	148.7	99.3	64.6	59.4	58.1
75°	122.7	76.0	53.3	48.7	48.1
77.5°	96.8	54.0	42.0	39.3	38.0
80°	72.7	38.7	32.0	29.3	29.3
82.5°	50.6	26.0	22.0	20.7	20.7
85°	28.6	14.6	12.7	12.7	12.7
87.5°	10.7	5.4	5.4	4.6	4.6
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7



TEST NUMBER: P921532

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1



TEST NUMBER: P921532  
 CATALOG NUMBER: DFN2DIP-HX2F0-020D060US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.84	6.50	7.00	7.64	9.24	1.83	2.49	2.98	3.62	5.22
	3H	7.48	8.07	8.64	9.22	10.83	2.99	3.57	4.15	4.72	6.33
	4H	8.06	8.62	9.23	9.77	11.39	3.42	3.97	4.59	5.12	6.74
	6H	8.46	8.97	9.63	10.12	11.75	3.71	4.23	4.89	5.38	7.00
	8H	8.57	9.05	9.75	10.22	11.84	3.79	4.28	4.97	5.44	7.06
	12H	8.61	9.08	9.80	10.23	11.88	3.82	4.28	5.00	5.44	7.08
4H	2H	5.83	6.39	7.01	7.54	9.16	2.39	2.95	3.57	4.09	5.71
	3H	7.62	8.08	8.80	9.26	10.89	3.70	4.17	4.88	5.34	6.97
	4H	8.28	8.71	9.47	9.87	11.52	4.23	4.66	5.41	5.82	7.46
	6H	8.77	9.13	9.96	10.32	11.95	4.62	4.98	5.81	6.17	7.80
	8H	8.92	9.27	10.11	10.44	12.09	4.73	5.08	5.92	6.25	7.90
	12H	9.00	9.31	10.20	10.49	12.15	4.78	5.09	5.98	6.28	7.94
8H	4H	8.24	8.58	9.42	9.75	11.41	4.48	4.82	5.67	6.00	7.65
	6H	8.77	9.05	9.97	10.27	11.92	4.97	5.25	6.17	6.47	8.12
	8H	8.97	9.21	10.18	10.41	12.08	5.14	5.39	6.35	6.58	8.25
	12H	9.08	9.30	10.29	10.49	12.19	5.24	5.46	6.46	6.65	8.35
12H	4H	8.18	8.49	9.38	9.67	11.33	4.47	4.78	5.67	5.97	7.63
	6H	8.74	8.99	9.95	10.18	11.85	5.01	5.25	6.22	6.45	8.12
	8H	8.94	9.15	10.15	10.34	12.05	5.20	5.41	6.41	6.60	8.31