

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921779

Luminaire Tested: DFN2DIP-HX3F0-090D080US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P921779  
REPORT IS A COMBINATION OF REPORTS P899284 AND P896089  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-090D080US940-RLLFLL  
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13134.9 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 154  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P921779  
CATALOG NUMBER: DFN2DIP-HX3F0-090D080US940-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P921779

CATALOG NUMBER: DFN2DIP-HX3F0-090D080US940-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58	52
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	66	61	76	68	62	57	59	54	50	50	46	44	42	39	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	42	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	33	29	34	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	21	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3842	3842	3842
5°	3847	3779	3803
10°	3807	3702	3677
15°	3753	3577	3484
20°	3682	3406	3248
25°	3609	3214	3019
30°	3512	3018	2731
35°	3416	2808	2477
40°	3319	2590	2187
45°	3207	2349	1924
50°	3090	2107	1667
55°	2968	1847	1420
60°	2827	1577	1167
65°	2664	1302	1048
70°	2467	1045	945
75°	2219	916	855
80°	1860	760	735
85°	1270	495	540

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3207 cd/sqm



TEST NUMBER: P921779

CATALOG NUMBER: DFN2DIP-HX3F0-090D080US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	310.9	2.4
10°-20°	853.4	6.5
20°-30°	1198.1	9.1
30°-40°	1306.0	9.9
40°-50°	1200.4	9.1
50°-60°	942.7	7.2
60°-70°	613.6	4.7
70°-80°	315.9	2.4
80°-90°	87.1	0.7
90°-100°	139.6	1.1
100°-110°	443.6	3.4
110°-120°	759.1	5.8
120°-130°	998.3	7.6
130°-140°	1120.6	8.5
140°-150°	1098.9	8.4
150°-160°	921.8	7.0
160°-170°	611.3	4.7
170°-180°	213.7	1.6
0°-30°	2362.4	18.0
0°-40°	3668.4	27.9
0°-60°	5811.5	44.2
0°-90°	6828.0	52.0
90°-120°	1342.3	10.2
90°-150°	4560.1	34.7
90°-180°	6307.0	48.0
0°-180°	13134.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3317	3317	3317	3317	3317	
5°	3317	3302	3263	3290	3281	315
15°	3155	3122	3020	2963	2933	889
25°	2864	2768	2570	2446	2401	1317
35°	2468	2314	2050	1861	1795	1544
45°	2017	1816	1501	1288	1216	1558
55°	1534	1300	975	796	738	1371
65°	1036	792	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	148
90°	2	24	67	63	65	13
95°	99	118	122	122	118	111
105°	410	415	419	422	422	432
115°	762	773	769	767	762	753
125°	1108	1125	1120	1113	1111	990
135°	1433	1454	1458	1456	1451	1108
145°	1740	1754	1764	1766	1759	1087
155°	1990	1995	2001	2010	2004	916
165°	2164	2162	2162	2176	2166	611
175°	2252	2247	2242	2256	2244	214
180°	2256	2256	2256	2256	2256	



TEST NUMBER: P921779

CATALOG NUMBER: DFN2DIP-HX3F0-090D080US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3316.9	3316.9	3316.9	3316.9	3316.9
2.5°	3331.9	3316.9	3283.7	3314.0	3308.0
5°	3316.9	3301.9	3262.8	3289.8	3280.9
7.5°	3289.8	3272.0	3230.0	3241.7	3226.7
10°	3253.9	3232.8	3173.0	3163.7	3145.9
12.5°	3208.9	3181.9	3100.7	3082.8	3049.6
15°	3154.8	3121.7	3019.8	2962.7	2932.8
17.5°	3091.7	3043.7	2917.5	2851.6	2803.5
20°	3019.8	2959.6	2809.5	2734.7	2668.4
22.5°	2941.8	2872.6	2698.4	2596.5	2551.6
25°	2863.7	2767.5	2569.5	2446.5	2401.3
27.5°	2770.7	2668.4	2449.4	2308.3	2239.2
30°	2671.7	2557.3	2317.2	2164.4	2083.1
32.5°	2575.4	2437.2	2191.4	2011.2	1936.0
35°	2467.5	2314.3	2050.3	1861.2	1794.9
37.5°	2362.4	2197.2	1918.2	1710.8	1636.0
40°	2251.3	2071.4	1779.9	1566.9	1488.9
42.5°	2137.3	1945.3	1642.0	1419.8	1344.9
45°	2017.2	1816.0	1500.9	1287.5	1215.6
47.5°	1903.2	1690.1	1365.9	1152.5	1086.6
50°	1777.1	1564.0	1233.8	1026.4	963.7
52.5°	1653.9	1428.7	1107.7	909.5	852.6
55°	1533.7	1299.7	975.4	795.6	738.5
57.5°	1410.9	1170.7	858.6	690.5	642.4
60°	1284.7	1044.5	735.4	582.5	534.4
62.5°	1161.8	921.7	630.3	486.3	462.4
65°	1035.6	792.4	522.3	420.4	411.2
67.5°	915.6	672.3	420.4	369.1	360.2
70°	789.5	555.4	348.1	318.2	306.0
72.5°	669.4	447.1	291.1	267.2	261.2
75°	552.2	342.1	240.1	219.1	216.2
77.5°	435.3	243.0	189.1	177.1	171.0
80°	327.1	174.2	143.9	132.2	132.2
82.5°	228.0	117.2	99.1	93.0	93.0
85°	128.9	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.0	21.0
90°	2.1	24.5	66.7	62.6	64.6
92.5°	42.2	57.2	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.3	183.0	190.5	190.5	190.5
100°	241.5	257.1	262.5	262.5	260.5
102.5°	321.7	333.3	340.7	342.8	340.7
105°	409.5	414.9	419.0	422.4	422.4
107.5°	496.5	504.7	504.7	506.0	496.5
110°	580.9	591.7	591.7	591.7	586.3



TEST NUMBER: P921779

CATALOG NUMBER: DFN2DIP-HX3F0-090D080US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	672.0	683.6	681.5	676.1	672.0
115°	761.8	772.7	769.3	767.2	761.8
117.5°	850.9	865.9	856.3	850.9	845.4
120°	940.7	955.6	940.7	940.7	934.5
122.5°	1022.3	1041.3	1031.8	1026.4	1022.3
125°	1108.0	1125.0	1119.5	1113.4	1111.4
127.5°	1191.7	1212.7	1205.2	1197.1	1191.7
130°	1269.9	1294.3	1290.9	1286.9	1279.4
132.5°	1357.6	1376.6	1378.0	1368.5	1363.1
135°	1433.1	1454.2	1458.3	1456.3	1450.8
137.5°	1517.4	1534.5	1537.8	1536.5	1528.3
140°	1591.6	1608.6	1618.1	1618.1	1610.6
142.5°	1667.8	1684.8	1690.2	1692.3	1684.8
145°	1739.9	1753.5	1764.3	1766.4	1758.9
147.5°	1804.5	1821.5	1829.6	1833.1	1825.6
150°	1871.2	1882.7	1890.2	1896.3	1890.2
152.5°	1930.3	1941.9	1951.4	1958.9	1951.4
155°	1989.5	1994.9	2001.1	2010.5	2004.5
157.5°	2040.5	2044.6	2048.0	2061.5	2052.1
160°	2086.1	2090.2	2092.2	2103.7	2095.6
162.5°	2128.2	2128.2	2130.3	2143.2	2133.7
165°	2164.3	2162.2	2162.2	2175.9	2166.3
167.5°	2196.9	2190.8	2190.8	2204.4	2194.9
170°	2221.4	2216.0	2213.9	2227.6	2216.0
172.5°	2238.5	2233.0	2231.0	2244.5	2233.0
175°	2252.0	2246.6	2242.5	2256.1	2244.5
177.5°	2259.5	2254.1	2250.0	2261.6	2250.0
180°	2256.1	2256.1	2256.1	2256.1	2256.1



TEST NUMBER: P921779  
 CATALOG NUMBER: DFN2DIP-HX3F0-090D080US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.96	12.81	12.91	13.77	15.01	7.94	8.79	8.89	9.74	10.99
	3H	13.63	14.39	14.59	15.36	16.63	9.12	9.88	10.08	10.85	12.12
	4H	14.24	14.95	15.21	15.92	17.20	9.57	10.29	10.54	11.26	12.54
	6H	14.65	15.31	15.64	16.29	17.58	9.89	10.55	10.87	11.53	12.82
	8H	14.78	15.40	15.77	16.40	17.68	9.98	10.61	10.97	11.60	12.89
	12H	14.84	15.43	15.83	16.42	17.73	10.02	10.62	11.02	11.60	12.92
4H	2H	11.98	12.70	12.96	13.67	14.95	8.53	9.25	9.51	10.22	11.50
	3H	13.80	14.40	14.79	15.40	16.69	9.88	10.47	10.87	11.47	12.77
	4H	14.49	15.03	15.49	16.03	17.34	10.42	10.97	11.42	11.96	13.28
	6H	15.00	15.47	16.01	16.48	17.80	10.84	11.31	11.85	12.32	13.64
	8H	15.17	15.61	16.18	16.62	17.94	10.97	11.40	11.97	12.41	13.74
	12H	15.26	15.65	16.29	16.68	18.01	11.03	11.42	12.05	12.45	13.78
8H	4H	14.46	14.89	15.47	15.91	17.23	10.70	11.14	11.71	12.15	13.47
	6H	15.02	15.38	16.05	16.43	17.75	11.21	11.57	12.25	12.63	13.95
	8H	15.23	15.54	16.27	16.58	17.93	11.40	11.72	12.44	12.76	14.10
	12H	15.36	15.64	16.41	16.67	18.06	11.52	11.79	12.56	12.83	14.22
12H	4H	14.41	14.80	15.44	15.83	17.16	10.70	11.10	11.73	12.12	13.46
	6H	14.99	15.31	16.03	16.35	17.69	11.26	11.58	12.30	12.62	13.96
	8H	15.21	15.49	16.25	16.52	17.91	11.47	11.75	12.51	12.78	14.17