

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921568

Luminaire Tested: DFN2DIP-HX2F0-040D050US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921568
REPORT IS A COMBINATION OF REPORTS P899186 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D050US940-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6977.6 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921568
CATALOG NUMBER: DFN2DIP-HX2F0-040D050US940-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P921568
 CATALOG NUMBER: DFN2DIP-HX2F0-040D050US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44			44
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37			37
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32			32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28			28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24			24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21			21
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22	19			19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17			17
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15			15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14			14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3473	3473	3473
5°	3473	3410	3434
10°	3434	3335	3316
15°	3381	3217	3137
20°	3313	3057	2920
25°	3243	2880	2711
30°	3151	2698	2448
35°	3061	2505	2216
40°	2969	2305	1953
45°	2863	2085	1714
50°	2752	1863	1481
55°	2636	1627	1258
60°	2502	1381	1030
65°	2347	1133	919
70°	2159	901	823
75°	1922	779	737
80°	1581	630	621
85°	1034	389	434

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2863 cd/sqm



TEST NUMBER: P921568

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	2.0
10°-20°	379.3	5.4
20°-30°	532.5	7.6
30°-40°	580.5	8.3
40°-50°	533.5	7.6
50°-60°	419.0	6.0
60°-70°	272.7	3.9
70°-80°	140.4	2.0
80°-90°	39.8	0.6
90°-100°	87.3	1.3
100°-110°	277.2	4.0
110°-120°	474.5	6.8
120°-130°	624.0	8.9
130°-140°	700.4	10.0
140°-150°	686.8	9.8
150°-160°	576.1	8.3
160°-170°	382.1	5.5
170°-180°	133.5	1.9
0°-30°	1049.9	15.0
0°-40°	1630.4	23.4
0°-60°	2582.9	37.0
0°-90°	3035.8	43.5
90°-120°	838.9	12.0
90°-150°	2850.1	40.8
90°-180°	3942.0	56.5
0°-180°	6977.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	15	42	39	40	7
95°	62	74	76	76	74	69
105°	256	259	262	264	264	270
115°	476	483	481	480	476	471
125°	692	703	700	696	695	619
135°	896	909	911	910	907	692
145°	1087	1096	1103	1104	1099	679
155°	1243	1247	1251	1257	1253	572
165°	1353	1351	1351	1360	1354	382
175°	1408	1404	1402	1410	1403	134
180°	1410	1410	1410	1410	1410	



TEST NUMBER: P921568

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	1.2	15.3	41.6	39.1	40.4
92.5°	26.4	35.7	37.0	38.3	38.3
95°	62.1	74.0	76.1	76.1	74.0
97.5°	103.3	114.3	119.0	119.0	119.0
100°	150.9	160.7	164.1	164.1	162.8
102.5°	201.1	208.3	212.9	214.3	212.9
105°	255.9	259.3	261.9	263.9	263.9
107.5°	310.3	315.4	315.4	316.3	310.3
110°	363.0	369.9	369.9	369.9	366.4



TEST NUMBER: P921568

CATALOG NUMBER: DFN2DIP-HX2F0-040D050US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	420.0	427.2	426.0	422.6	420.0
115°	476.1	483.0	480.8	479.6	476.1
117.5°	531.8	541.2	535.2	531.8	528.4
120°	587.9	597.3	587.9	587.9	584.1
122.5°	638.9	650.9	644.9	641.5	638.9
125°	692.5	703.1	699.7	695.9	694.6
127.5°	744.8	758.0	753.3	748.1	744.8
130°	793.7	809.0	806.8	804.3	799.6
132.5°	848.6	860.4	861.3	855.3	851.9
135°	895.7	908.8	911.4	910.2	906.8
137.5°	948.4	959.0	961.2	960.3	955.2
140°	994.7	1005.4	1011.3	1011.3	1006.7
142.5°	1042.3	1053.0	1056.4	1057.7	1053.0
145°	1087.4	1095.9	1102.7	1104.0	1099.3
147.5°	1127.8	1138.4	1143.5	1145.7	1140.9
150°	1169.5	1176.7	1181.3	1185.2	1181.3
152.5°	1206.5	1213.7	1219.6	1224.3	1219.6
155°	1243.4	1246.8	1250.6	1256.6	1252.8
157.5°	1275.3	1277.8	1280.0	1288.5	1282.5
160°	1303.8	1306.4	1307.6	1314.8	1309.7
162.5°	1330.2	1330.2	1331.4	1339.5	1333.6
165°	1352.7	1351.4	1351.4	1359.9	1354.0
167.5°	1373.1	1369.2	1369.2	1377.8	1371.8
170°	1388.4	1385.0	1383.8	1392.2	1385.0
172.5°	1399.0	1395.6	1394.4	1402.8	1395.6
175°	1407.6	1404.1	1401.6	1410.1	1402.8
177.5°	1412.2	1408.8	1406.2	1413.5	1406.2
180°	1410.1	1410.1	1410.1	1410.1	1410.1



TEST NUMBER: P921568
 CATALOG NUMBER: DFN2DIP-HX2F0-040D050US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.70	11.48	11.71	12.50	13.86	6.68	7.46	7.69	8.48	9.84
	3H	12.34	13.04	13.37	14.07	15.46	7.85	8.54	8.87	9.57	10.96
	4H	12.93	13.59	13.97	14.63	16.02	8.28	8.94	9.32	9.98	11.37
	6H	13.33	13.94	14.38	14.98	16.38	8.59	9.19	9.64	10.23	11.63
	8H	13.45	14.02	14.50	15.08	16.48	8.67	9.25	9.72	10.30	11.70
	12H	13.50	14.05	14.56	15.09	16.51	8.70	9.25	9.76	10.30	11.72
4H	2H	10.70	11.36	11.75	12.40	13.79	7.25	7.91	8.30	8.95	10.34
	3H	12.50	13.05	13.55	14.11	15.51	8.58	9.13	9.63	10.19	11.59
	4H	13.17	13.67	14.23	14.73	16.15	9.11	9.61	10.17	10.67	12.09
	6H	13.66	14.09	14.73	15.17	16.59	9.51	9.94	10.58	11.02	12.44
	8H	13.82	14.22	14.89	15.29	16.73	9.63	10.03	10.70	11.10	12.54
	12H	13.90	14.26	14.99	15.34	16.79	9.68	10.04	10.77	11.13	12.57
8H	4H	13.13	13.53	14.20	14.60	16.04	9.37	9.77	10.44	10.84	12.28
	6H	13.67	14.00	14.76	15.11	16.54	9.87	10.20	10.96	11.31	12.74
	8H	13.87	14.16	14.97	15.25	16.71	10.04	10.33	11.14	11.43	12.88
	12H	13.99	14.24	15.09	15.33	16.82	10.15	10.40	11.25	11.49	12.98
12H	4H	13.08	13.44	14.17	14.53	15.97	9.37	9.73	10.46	10.82	12.26
	6H	13.64	13.93	14.74	15.03	16.48	9.91	10.20	11.01	11.29	12.75
	8H	13.84	14.10	14.94	15.19	16.68	10.10	10.36	11.20	11.45	12.94