

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921600

Luminaire Tested: DFN2DIP-HX2F0-060D030US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921600
REPORT IS A COMBINATION OF REPORTS P899170 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D030US940-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6915.2 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921600

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921600

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5210	5210	5210
5°	5210	5115	5151
10°	5150	5002	4973
15°	5071	4825	4706
20°	4969	4586	4380
25°	4865	4320	4067
30°	4727	4048	3672
35°	4592	3757	3325
40°	4453	3457	2929
45°	4294	3127	2571
50°	4128	2794	2222
55°	3954	2440	1887
60°	3753	2072	1544
65°	3521	1699	1379
70°	3238	1352	1235
75°	2883	1168	1105
80°	2372	946	930
85°	1552	584	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4294 cd/sqm

TEST NUMBER: P921600

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.2	3.0
10°-20°	568.9	8.2
20°-30°	798.7	11.6
30°-40°	870.7	12.6
40°-50°	800.3	11.6
50°-60°	628.5	9.1
60°-70°	409.1	5.9
70°-80°	210.6	3.0
80°-90°	56.2	0.8
90°-100°	52.3	0.8
100°-110°	166.3	2.4
110°-120°	284.7	4.1
120°-130°	374.4	5.4
130°-140°	420.2	6.1
140°-150°	412.1	6.0
150°-160°	345.7	5.0
160°-170°	229.2	3.3
170°-180°	80.1	1.2
0°-30°	1574.9	22.8
0°-40°	2445.6	35.4
0°-60°	3874.3	56.0
0°-90°	4550.1	65.8
90°-120°	503.4	7.3
90°-150°	1710.0	24.7
90°-180°	2365.0	34.2
0°-180°	6915.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2211	2211	2211	2211	2211	
5°	2211	2201	2175	2193	2187	210
15°	2103	2081	2013	1975	1955	593
25°	1909	1845	1713	1631	1601	878
35°	1645	1543	1367	1241	1197	1030
45°	1345	1211	1001	858	810	1039
55°	1022	866	650	530	492	914
65°	690	528	348	280	274	685
75°	368	228	160	146	144	389
85°	86	44	38	38	38	99
90°	1	9	25	24	24	7
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	

TEST NUMBER: P921600

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2211.3	2211.3	2211.3	2211.3	2211.3
2.5°	2221.3	2211.3	2189.1	2209.3	2205.3
5°	2211.3	2201.3	2175.1	2193.3	2187.3
7.5°	2193.3	2181.3	2153.3	2161.1	2151.2
10°	2169.2	2155.2	2115.3	2109.2	2097.2
12.5°	2139.3	2121.2	2067.1	2055.2	2033.1
15°	2103.2	2081.1	2013.1	1975.1	1955.2
17.5°	2061.2	2029.1	1945.0	1901.0	1869.0
20°	2013.1	1973.0	1873.0	1823.1	1779.0
22.5°	1961.1	1915.0	1798.9	1731.0	1701.0
25°	1909.2	1845.0	1713.0	1631.0	1600.9
27.5°	1847.2	1779.0	1632.9	1538.8	1492.8
30°	1781.1	1704.9	1544.8	1442.9	1388.7
32.5°	1717.0	1624.9	1461.0	1340.8	1290.7
35°	1645.0	1542.9	1366.9	1240.7	1196.6
37.5°	1574.9	1464.7	1278.8	1140.6	1090.7
40°	1500.8	1380.9	1186.6	1044.5	992.6
42.5°	1424.9	1296.8	1094.7	946.5	896.6
45°	1344.8	1210.6	1000.7	858.4	810.4
47.5°	1268.8	1126.8	910.6	768.4	724.4
50°	1184.7	1042.7	822.5	684.3	642.5
52.5°	1102.5	952.4	738.4	606.4	568.4
55°	1022.5	866.5	650.3	530.4	492.3
57.5°	940.6	780.4	572.4	460.3	428.2
60°	856.5	696.4	490.3	388.3	356.2
62.5°	774.5	614.5	420.2	324.2	308.3
65°	690.5	528.2	348.2	280.3	274.1
67.5°	610.4	448.2	280.3	246.1	240.1
70°	526.3	370.2	232.0	212.1	204.0
72.5°	446.3	298.1	194.0	178.2	174.1
75°	368.2	228.0	160.1	146.1	144.2
77.5°	290.3	162.0	126.1	118.1	114.0
80°	218.0	116.1	95.9	88.1	88.1
82.5°	152.0	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9

TEST NUMBER: P921600

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1

TEST NUMBER: P921600

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.10	15.08	14.92	15.92	16.95	10.09	11.07	10.90	11.90	12.93
	3H	15.77	16.64	16.60	17.49	18.54	11.27	12.15	12.10	12.99	14.05
	4H	16.37	17.19	17.21	18.04	19.11	11.72	12.54	12.56	13.39	14.46
	6H	16.78	17.54	17.63	18.39	19.47	12.03	12.79	12.89	13.65	14.73
	8H	16.89	17.62	17.76	18.49	19.58	12.12	12.84	12.98	13.72	14.80
	12H	16.95	17.64	17.82	18.51	19.62	12.16	12.85	13.03	13.72	14.82
4H	2H	14.14	14.96	14.99	15.81	16.88	10.69	11.51	11.54	12.36	13.43
	3H	15.95	16.64	16.81	17.52	18.60	12.03	12.72	12.89	13.60	14.68
	4H	16.63	17.25	17.50	18.13	19.24	12.57	13.19	13.44	14.07	15.18
	6H	17.13	17.67	18.02	18.57	19.68	12.98	13.52	13.87	14.42	15.53
	8H	17.29	17.79	18.18	18.69	19.82	13.10	13.60	13.99	14.50	15.63
	12H	17.38	17.83	18.29	18.75	19.88	13.16	13.61	14.07	14.53	15.66
8H	4H	16.60	17.11	17.50	18.00	19.13	12.85	13.35	13.74	14.25	15.37
	6H	17.15	17.56	18.07	18.50	19.63	13.35	13.76	14.27	14.70	15.83
	8H	17.35	17.72	18.28	18.65	19.79	13.52	13.89	14.45	14.83	15.97
	12H	17.48	17.80	18.41	18.72	19.92	13.64	13.96	14.57	14.88	16.08
12H	4H	16.56	17.01	17.47	17.93	19.06	12.85	13.30	13.76	14.22	15.35
	6H	17.12	17.49	18.05	18.42	19.57	13.39	13.76	14.32	14.69	15.83
	8H	17.33	17.66	18.26	18.58	19.78	13.59	13.91	14.52	14.84	16.03