

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924366

Luminaire Tested: DFN2DIP-HX3F0-040D030US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924366
REPORT IS A COMBINATION OF REPORTS P899203 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-040D030US950-FLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6310.7 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924366

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924366

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1720	1720	1720
5°	1722	1695	1706
10°	1707	1671	1682
15°	1681	1642	1645
20°	1647	1603	1608
25°	1612	1556	1564
30°	1569	1512	1509
35°	1528	1461	1450
40°	1478	1409	1395
45°	1428	1357	1337
50°	1373	1302	1271
55°	1315	1238	1211
60°	1250	1163	1141
65°	1179	1085	1059
70°	1089	990	970
75°	963	876	887
80°	812	731	730
85°	576	483	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1428 cd/sqm

TEST NUMBER: P924366

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.8	2.2
10°-20°	393.2	6.2
20°-30°	577.9	9.2
30°-40°	671.2	10.6
40°-50°	670.3	10.6
50°-60°	584.5	9.3
60°-70°	432.1	6.8
70°-80°	244.5	3.9
80°-90°	67.1	1.1
90°-100°	56.0	0.9
100°-110°	178.0	2.8
110°-120°	304.6	4.8
120°-130°	400.5	6.3
130°-140°	449.6	7.1
140°-150°	440.9	7.0
150°-160°	369.8	5.9
160°-170°	245.3	3.9
170°-180°	85.7	1.4
0°-30°	1110.8	17.6
0°-40°	1782.0	28.2
0°-60°	3036.8	48.1
0°-90°	3780.4	59.9
90°-120°	538.5	8.5
90°-150°	1829.5	29.0
90°-180°	2530.0	40.1
0°-180°	6310.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	1	10	27	25	26	6
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P924366

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P924366

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2



TEST NUMBER: P924366

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.98	10.94	10.85	11.83	12.95	9.55	10.51	10.42	11.40	12.52
	3H	11.64	12.50	12.52	13.40	14.54	11.17	12.03	12.05	12.93	14.08
	4H	12.23	13.04	13.12	13.94	15.10	11.76	12.57	12.65	13.47	14.63
	6H	12.62	13.37	13.53	14.28	15.46	12.15	12.90	13.06	13.81	14.99
	8H	12.73	13.44	13.64	14.37	15.54	12.26	12.97	13.17	13.90	15.07
	12H	12.78	13.46	13.70	14.38	15.58	12.30	12.98	13.22	13.90	15.10
4H	2H	10.45	11.26	11.35	12.17	13.32	10.11	10.92	11.01	11.82	12.98
	3H	12.31	12.99	13.23	13.93	15.10	11.93	12.60	12.84	13.54	14.71
	4H	13.03	13.65	13.95	14.58	15.78	12.62	13.24	13.55	14.17	15.37
	6H	13.54	14.07	14.48	15.03	16.23	13.14	13.67	14.07	14.62	15.82
	8H	13.69	14.19	14.63	15.14	16.35	13.28	13.78	14.22	14.73	15.94
	12H	13.76	14.21	14.72	15.18	16.40	13.35	13.80	14.30	14.76	15.98
8H	4H	13.23	13.73	14.17	14.68	15.89	12.87	13.37	13.81	14.32	15.53
	6H	13.85	14.27	14.82	15.26	16.47	13.49	13.91	14.46	14.90	16.11
	8H	14.07	14.44	15.04	15.42	16.65	13.71	14.07	14.68	15.05	16.28
	12H	14.20	14.52	15.18	15.50	16.77	13.82	14.14	14.80	15.12	16.40
12H	4H	13.22	13.67	14.18	14.63	15.85	12.87	13.32	13.83	14.28	15.50
	6H	13.88	14.25	14.86	15.23	16.46	13.53	13.90	14.51	14.88	16.11
	8H	14.12	14.45	15.10	15.42	16.70	13.77	14.09	14.75	15.07	16.34