

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924370

Luminaire Tested: DFN2DIP-HX3F0-040D040US950-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P924370  
REPORT IS A COMBINATION OF REPORTS P899217 AND P896089  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-040D040US950-FLLFLL  
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7155.0 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 64.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P924370  
CATALOG NUMBER: DFN2DIP-HX3F0-040D040US950-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P924370  
 CATALOG NUMBER: DFN2DIP-HX3F0-040D040US950-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1720	1720	1720
5°	1722	1695	1706
10°	1707	1671	1682
15°	1681	1642	1645
20°	1647	1603	1608
25°	1612	1556	1564
30°	1569	1512	1509
35°	1528	1461	1450
40°	1478	1409	1395
45°	1428	1357	1337
50°	1373	1302	1271
55°	1315	1238	1211
60°	1250	1163	1141
65°	1179	1085	1059
70°	1089	990	970
75°	963	876	887
80°	812	731	730
85°	576	483	474

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1428 cd/sqm



TEST NUMBER: P924370

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US950-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.8	2.0
10°-20°	393.2	5.5
20°-30°	577.9	8.1
30°-40°	671.2	9.4
40°-50°	670.3	9.4
50°-60°	584.5	8.2
60°-70°	432.1	6.0
70°-80°	244.5	3.4
80°-90°	67.9	0.9
90°-100°	74.7	1.0
100°-110°	237.3	3.3
110°-120°	406.1	5.7
120°-130°	534.0	7.5
130°-140°	599.4	8.4
140°-150°	587.8	8.2
150°-160°	493.1	6.9
160°-170°	327.0	4.6
170°-180°	114.3	1.6
0°-30°	1110.8	15.5
0°-40°	1782.0	24.9
0°-60°	3036.8	42.4
0°-90°	3781.3	52.8
90°-120°	718.0	10.0
90°-150°	2439.3	34.1
90°-180°	3374.0	47.2
0°-180°	7155.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	1	13	36	34	34	7
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	



TEST NUMBER: P924370

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US950-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7



TEST NUMBER: P924370

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US950-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8



TEST NUMBER: P924370  
 CATALOG NUMBER: DFN2DIP-HX3F0-040D040US950-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.37	10.26	10.30	11.21	12.44	8.94	9.83	9.87	10.78	12.01
	3H	11.03	11.82	11.97	12.78	14.03	10.56	11.35	11.50	12.31	13.57
	4H	11.61	12.36	12.57	13.33	14.59	11.14	11.89	12.10	12.86	14.12
	6H	12.00	12.70	12.97	13.67	14.94	11.53	12.23	12.50	13.20	14.47
	8H	12.11	12.77	13.08	13.75	15.03	11.64	12.30	12.61	13.28	14.56
	12H	12.15	12.78	13.13	13.76	15.06	11.68	12.31	12.66	13.29	14.58
4H	2H	9.83	10.59	10.80	11.55	12.81	9.49	10.24	10.45	11.21	12.47
	3H	11.69	12.32	12.67	13.31	14.59	11.30	11.93	12.28	12.92	14.20
	4H	12.40	12.98	13.38	13.96	15.26	12.00	12.57	12.98	13.56	14.86
	6H	12.91	13.41	13.91	14.42	15.71	12.51	13.00	13.50	14.01	15.31
	8H	13.06	13.52	14.05	14.52	15.84	12.65	13.11	13.65	14.12	15.43
	12H	13.13	13.55	14.14	14.57	15.88	12.71	13.13	13.73	14.15	15.47
8H	4H	12.60	13.06	13.59	14.06	15.38	12.24	12.70	13.24	13.71	15.02
	6H	13.22	13.60	14.24	14.65	15.96	12.86	13.24	13.88	14.29	15.60
	8H	13.44	13.77	14.47	14.81	16.14	13.07	13.41	14.10	14.44	15.77
	12H	13.56	13.86	14.60	14.89	16.26	13.18	13.48	14.22	14.51	15.88
12H	4H	12.58	13.00	13.60	14.02	15.34	12.23	12.65	13.25	13.67	14.99
	6H	13.25	13.59	14.28	14.62	15.95	12.90	13.24	13.93	14.27	15.60
	8H	13.49	13.78	14.52	14.81	16.18	13.13	13.43	14.17	14.46	15.83