

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921607

Luminaire Tested: DFN2DIP-HX2F0-060D050US940-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P921607  
REPORT IS A COMBINATION OF REPORTS P900709 AND P897595  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-060D050US940-FLONL  
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9710.8 lumens  
Efficiency: N/A  
Efficacy: 99.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 97.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P921607  
CATALOG NUMBER: DFN2DIP-HX2F0-060D050US940-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P921607

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US940-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55			
1	99	94	91	87	92	88	84	81	75	73	71	64	62	60	53	52	51	46			
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39			
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33			
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28			
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27	24			
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21			
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19			
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17			
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15			
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4905	4905	4905
5°	4905	4825	4860
10°	4857	4748	4785
15°	4778	4659	4674
20°	4674	4538	4560
25°	4570	4397	4429
30°	4442	4265	4266
35°	4319	4110	4094
40°	4170	3954	3929
45°	4021	3797	3760
50°	3858	3631	3565
55°	3686	3441	3384
60°	3491	3216	3176
65°	3277	2980	2932
70°	3006	2694	2666
75°	2633	2351	2409
80°	2180	1914	1944
85°	1478	1201	1204

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4021 cd/sqm



TEST NUMBER: P921607

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US940-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.9	2.0
10°-20°	551.3	5.7
20°-30°	810.2	8.3
30°-40°	941.0	9.7
40°-50°	939.8	9.7
50°-60°	819.5	8.4
60°-70°	605.8	6.2
70°-80°	342.7	3.5
80°-90°	93.1	1.0
90°-100°	49.6	0.5
100°-110°	185.0	1.9
110°-120°	490.6	5.1
120°-130°	813.6	8.4
130°-140°	864.3	8.9
140°-150°	803.2	8.3
150°-160°	645.8	6.6
160°-170°	416.1	4.3
170°-180°	143.2	1.5
0°-30°	1557.4	16.0
0°-40°	2498.4	25.7
0°-60°	4257.8	43.8
0°-90°	5299.4	54.6
90°-120°	725.2	7.5
90°-150°	3206.2	33.0
90°-180°	4411.0	45.4
0°-180°	9710.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2082	2082	2082	2082	2082	
5°	2082	2074	2052	2068	2064	198
15°	1982	1970	1944	1952	1942	558
25°	1794	1778	1744	1748	1744	825
35°	1548	1528	1495	1483	1473	966
45°	1259	1245	1215	1193	1185	972
55°	953	941	917	893	883	852
65°	643	631	611	592	583	635
75°	336	332	322	310	314	359
85°	82	80	78	72	70	91
90°	1	13	22	27	29	9
95°	71	35	42	48	47	84
105°	331	364	66	78	83	354
115°	626	644	672	168	89	616
125°	885	899	920	928	931	789
135°	1095	1113	1122	1134	1131	846
145°	1271	1270	1288	1296	1290	795
155°	1399	1389	1402	1409	1400	645
165°	1474	1468	1471	1478	1471	416
175°	1508	1500	1502	1510	1499	144
180°	1505	1505	1505	1505	1505	



TEST NUMBER: P921607

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US940-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2081.8	2081.8	2081.8	2081.8	2081.8
2.5°	2093.9	2083.9	2061.8	2081.8	2078.0
5°	2081.8	2073.9	2051.8	2067.8	2064.0
7.5°	2067.8	2055.9	2033.8	2050.0	2045.9
10°	2045.9	2031.9	2007.9	2023.8	2017.9
12.5°	2015.8	2003.9	1979.9	1989.9	1985.8
15°	1981.7	1969.9	1943.8	1951.9	1941.9
17.5°	1939.7	1927.9	1901.8	1911.6	1901.8
20°	1893.6	1881.8	1853.7	1859.7	1851.8
22.5°	1847.8	1829.7	1803.6	1803.6	1799.6
25°	1793.6	1777.7	1743.7	1747.5	1743.7
27.5°	1733.5	1719.5	1693.5	1687.7	1677.7
30°	1673.7	1657.4	1627.5	1621.6	1613.5
32.5°	1609.4	1597.6	1565.5	1553.4	1545.3
35°	1547.5	1527.5	1495.4	1483.3	1473.3
37.5°	1477.4	1459.3	1427.3	1413.2	1403.2
40°	1405.3	1389.2	1357.2	1339.3	1331.2
42.5°	1335.2	1319.1	1287.3	1267.1	1255.2
45°	1259.3	1245.2	1215.0	1193.2	1185.1
47.5°	1185.1	1171.1	1139.1	1117.0	1105.0
50°	1107.0	1097.0	1069.0	1040.9	1030.9
52.5°	1030.9	1016.9	991.0	968.9	954.9
55°	953.0	940.8	916.9	892.9	882.9
57.5°	874.9	864.9	838.7	814.8	806.6
60°	796.7	788.8	760.8	738.7	732.7
62.5°	720.6	706.6	686.6	666.6	658.6
65°	642.7	630.6	610.6	592.5	582.6
67.5°	562.6	552.4	534.6	520.6	512.5
70°	488.5	480.5	462.4	448.4	440.5
72.5°	412.4	404.4	394.4	380.4	374.4
75°	336.2	332.4	322.2	310.3	314.3
77.5°	268.2	260.2	256.1	250.2	244.2
80°	200.3	198.1	194.1	188.2	184.1
82.5°	136.2	136.2	134.2	126.2	126.2
85°	81.9	80.1	78.1	72.0	70.1
87.5°	36.1	32.1	28.0	22.1	20.0
90°	1.1	13.0	21.8	27.3	29.3
92.5°	27.3	22.9	26.1	28.4	29.3
95°	70.7	34.8	42.4	48.0	46.8
97.5°	127.3	38.2	55.5	58.9	59.8
100°	192.8	43.6	62.1	70.7	72.9
102.5°	264.6	262.4	64.3	76.2	79.5
105°	331.0	363.7	66.4	78.4	82.8
107.5°	408.3	435.4	68.7	80.5	85.0
110°	482.4	505.2	190.6	81.7	86.0



TEST NUMBER: P921607

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US940-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	552.1	571.6	553.1	83.8	87.1
115°	626.1	644.5	671.8	167.7	89.3
117.5°	690.3	712.0	730.7	574.8	289.6
120°	762.1	778.5	798.1	811.2	664.1
122.5°	823.0	840.5	862.4	868.9	870.0
125°	885.1	899.4	920.1	927.6	930.9
127.5°	941.7	957.0	973.5	984.3	985.3
130°	995.1	1012.6	1024.5	1036.5	1035.5
132.5°	1049.6	1063.8	1075.7	1085.6	1084.5
135°	1095.4	1112.9	1122.5	1133.5	1131.3
137.5°	1143.2	1156.3	1167.2	1178.1	1174.9
140°	1190.0	1198.8	1210.7	1220.5	1215.1
142.5°	1229.3	1237.0	1251.1	1259.7	1254.3
145°	1270.7	1269.5	1288.0	1295.7	1290.2
147.5°	1306.5	1303.2	1321.8	1327.2	1322.9
150°	1341.4	1333.8	1351.2	1357.7	1352.3
152.5°	1370.7	1362.1	1378.4	1385.0	1377.3
155°	1399.1	1389.4	1402.4	1408.9	1400.3
157.5°	1421.9	1413.3	1423.1	1430.7	1421.9
160°	1441.6	1435.0	1441.6	1448.0	1440.5
162.5°	1458.9	1452.5	1457.9	1465.5	1455.7
165°	1474.2	1467.8	1471.0	1478.5	1471.0
167.5°	1486.2	1479.6	1483.0	1490.6	1480.8
170°	1496.0	1489.4	1491.7	1499.2	1489.4
172.5°	1502.5	1496.0	1498.3	1505.8	1496.0
175°	1508.0	1500.3	1502.5	1510.1	1499.2
177.5°	1510.1	1502.5	1503.7	1511.3	1501.5
180°	1504.7	1504.7	1504.7	1504.7	1504.7



TEST NUMBER: P921607  
 CATALOG NUMBER: DFN2DIP-HX2F0-060D050US940-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.07	13.98	13.99	14.91	16.12	12.65	13.55	13.57	14.49	15.69
	3H	14.71	15.52	15.64	16.47	17.70	14.25	15.06	15.18	16.01	17.24
	4H	15.28	16.05	16.23	17.00	18.24	14.83	15.59	15.77	16.54	17.78
	6H	15.67	16.37	16.62	17.33	18.58	15.21	15.91	16.16	16.87	18.12
	8H	15.76	16.44	16.72	17.41	18.66	15.31	15.98	16.27	16.95	18.20
	12H	15.80	16.44	16.77	17.41	18.68	15.34	15.98	16.31	16.95	18.22
4H	2H	13.53	14.30	14.48	15.25	16.48	13.19	13.96	14.14	14.91	16.15
	3H	15.37	16.01	16.33	16.99	18.24	14.99	15.63	15.95	16.61	17.86
	4H	16.07	16.65	17.04	17.63	18.90	15.67	16.26	16.64	17.23	18.51
	6H	16.56	17.07	17.54	18.06	19.34	16.17	16.67	17.15	17.67	18.94
	8H	16.70	17.17	17.68	18.16	19.45	16.30	16.77	17.29	17.76	19.05
	12H	16.76	17.19	17.76	18.20	19.49	16.36	16.78	17.36	17.79	19.09
8H	4H	16.26	16.73	17.24	17.72	19.01	15.90	16.38	16.89	17.37	18.66
	6H	16.86	17.25	17.87	18.28	19.57	16.51	16.90	17.52	17.93	19.22
	8H	17.06	17.41	18.08	18.43	19.73	16.71	17.05	17.72	18.07	19.38
	12H	17.18	17.48	18.20	18.50	19.85	16.81	17.12	17.83	18.13	19.48
12H	4H	16.24	16.67	17.24	17.67	18.97	15.90	16.32	16.90	17.33	18.62
	6H	16.88	17.23	17.90	18.25	19.55	16.54	16.89	17.56	17.91	19.21
	8H	17.11	17.41	18.13	18.43	19.78	16.76	17.07	17.78	18.08	19.43