

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924417

Luminaire Tested: DFN2DIP-HX3F0-060D030US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924417
REPORT IS A COMBINATION OF REPORTS P900728 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-060D030US950-RLLONL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7698.8 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 79.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924417

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924417

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2740	2740	2740
5°	2743	2695	2713
10°	2715	2640	2623
15°	2676	2551	2485
20°	2626	2429	2316
25°	2574	2293	2154
30°	2505	2153	1948
35°	2437	2003	1767
40°	2367	1848	1560
45°	2287	1676	1372
50°	2204	1503	1189
55°	2117	1318	1013
60°	2016	1125	832
65°	1900	928	747
70°	1760	745	674
75°	1583	653	610
80°	1327	542	524
85°	906	352	385

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2287 cd/sqm

TEST NUMBER: P924417

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.7	2.9
10°-20°	608.7	7.9
20°-30°	854.5	11.1
30°-40°	931.5	12.1
40°-50°	856.2	11.1
50°-60°	672.4	8.7
60°-70°	437.7	5.7
70°-80°	225.3	2.9
80°-90°	59.2	0.8
90°-100°	31.9	0.4
100°-110°	118.7	1.5
110°-120°	314.9	4.1
120°-130°	522.3	6.8
130°-140°	554.8	7.2
140°-150°	515.6	6.7
150°-160°	414.5	5.4
160°-170°	267.1	3.5
170°-180°	91.9	1.2
0°-30°	1684.9	21.9
0°-40°	2616.4	34.0
0°-60°	4144.9	53.8
0°-90°	4867.1	63.2
90°-120°	465.5	6.0
90°-150°	2058.1	26.7
90°-180°	2832.0	36.8
0°-180°	7698.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2366	2366	2366	2366	2366	
5°	2366	2355	2327	2346	2340	224
15°	2250	2226	2154	2113	2092	634
25°	2042	1974	1833	1745	1713	939
35°	1760	1651	1462	1327	1280	1102
45°	1439	1295	1071	918	867	1111
55°	1094	927	696	567	527	978
65°	739	565	372	300	293	732
75°	394	244	171	156	154	417
85°	92	47	41	41	41	106
90°	1	8	14	18	19	7
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	

TEST NUMBER: P924417

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2365.7	2365.7	2365.7	2365.7	2365.7
2.5°	2376.4	2365.7	2342.1	2363.6	2359.3
5°	2365.7	2355.0	2327.1	2346.5	2340.1
7.5°	2346.5	2333.7	2303.7	2312.1	2301.4
10°	2320.7	2305.7	2263.1	2256.5	2243.7
12.5°	2288.7	2269.4	2211.5	2198.8	2175.1
15°	2250.1	2226.4	2153.8	2113.1	2091.7
17.5°	2205.2	2170.8	2080.9	2033.8	1999.6
20°	2153.8	2110.8	2003.9	1950.5	1903.2
22.5°	2098.1	2048.8	1924.6	1851.9	1819.9
25°	2042.5	1973.9	1832.6	1745.0	1712.7
27.5°	1976.2	1903.2	1747.0	1646.3	1597.1
30°	1905.5	1824.0	1652.7	1543.7	1485.8
32.5°	1836.9	1738.4	1563.0	1434.4	1380.8
35°	1759.9	1650.7	1462.4	1327.4	1280.2
37.5°	1685.0	1567.0	1368.1	1220.3	1166.8
40°	1605.7	1477.4	1269.5	1117.5	1061.9
42.5°	1524.4	1387.4	1171.1	1012.6	959.2
45°	1438.7	1295.2	1070.6	918.3	867.0
47.5°	1357.4	1205.5	974.2	822.1	775.0
50°	1267.5	1115.5	880.0	732.1	687.4
52.5°	1179.5	1019.0	790.0	648.7	608.1
55°	1094.0	927.0	695.8	567.4	526.7
57.5°	1006.3	834.9	612.4	492.5	458.1
60°	916.3	745.1	524.5	415.5	381.1
62.5°	828.6	657.4	449.5	346.9	329.8
65°	738.7	565.1	372.5	299.8	293.3
67.5°	653.0	479.5	299.8	263.3	256.9
70°	563.1	396.1	248.2	227.0	218.3
72.5°	477.5	318.9	207.6	190.6	186.2
75°	393.9	243.9	171.2	156.3	154.3
77.5°	310.5	173.3	134.9	126.3	122.0
80°	233.3	124.2	102.7	94.3	94.3
82.5°	162.7	83.6	70.6	66.3	66.3
85°	92.0	47.0	40.6	40.6	40.6
87.5°	34.3	17.1	17.1	15.0	15.0
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2

TEST NUMBER: P924417

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9

TEST NUMBER: P924417

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.76	12.71	12.60	13.57	14.64	7.73	8.69	8.58	9.54	10.62
	3H	13.44	14.29	14.29	15.16	16.26	8.93	9.78	9.78	10.65	11.75
	4H	14.05	14.85	14.92	15.72	16.83	9.38	10.18	10.25	11.06	12.17
	6H	14.47	15.21	15.35	16.09	17.21	9.70	10.44	10.59	11.33	12.45
	8H	14.59	15.30	15.49	16.20	17.32	9.80	10.50	10.69	11.40	12.52
	12H	14.66	15.33	15.55	16.22	17.37	9.84	10.51	10.74	11.40	12.55
4H	2H	11.79	12.59	12.67	13.47	14.58	8.34	9.14	9.22	10.02	11.13
	3H	13.62	14.29	14.51	15.20	16.32	9.70	10.36	10.58	11.27	12.40
	4H	14.31	14.92	15.21	15.82	16.97	10.25	10.85	11.14	11.76	12.91
	6H	14.83	15.35	15.74	16.28	17.43	10.67	11.19	11.58	12.12	13.27
	8H	15.00	15.49	15.92	16.41	17.58	10.80	11.28	11.71	12.20	13.37
	12H	15.10	15.53	16.03	16.48	17.65	10.86	11.30	11.80	12.24	13.41
8H	4H	14.29	14.78	15.20	15.70	16.86	10.53	11.02	11.45	11.94	13.11
	6H	14.85	15.25	15.79	16.22	17.38	11.05	11.45	11.99	12.41	13.58
	8H	15.06	15.42	16.01	16.37	17.56	11.23	11.59	12.19	12.55	13.73
	12H	15.20	15.51	16.15	16.46	17.69	11.35	11.67	12.31	12.62	13.85
12H	4H	14.24	14.68	15.18	15.62	16.80	10.54	10.98	11.47	11.92	13.09
	6H	14.82	15.18	15.78	16.14	17.32	11.09	11.45	12.05	12.41	13.59
	8H	15.05	15.36	16.00	16.31	17.54	11.31	11.62	12.26	12.57	13.80

END OF REPORT