

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924252

Luminaire Tested: DFN2DIP-HX2F0-020D040US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924252
REPORT IS A COMBINATION OF REPORTS P899172 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D040US950-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4998.9 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924252

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924252

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1858	1858	1858
5°	1858	1824	1837
10°	1837	1784	1774
15°	1808	1721	1678
20°	1772	1635	1562
25°	1735	1540	1450
30°	1686	1444	1309
35°	1637	1340	1186
40°	1588	1233	1044
45°	1531	1115	917
50°	1472	997	793
55°	1410	870	673
60°	1339	739	551
65°	1255	606	492
70°	1155	482	441
75°	1028	416	394
80°	847	337	332
85°	552	208	232

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1617 cd/sqm

TEST NUMBER: P924252

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.9	1.5
10°-20°	202.9	4.1
20°-30°	284.8	5.7
30°-40°	310.5	6.2
40°-50°	285.4	5.7
50°-60°	224.1	4.5
60°-70°	145.9	2.9
70°-80°	75.1	1.5
80°-90°	22.6	0.5
90°-100°	74.7	1.5
100°-110°	237.3	4.7
110°-120°	406.1	8.1
120°-130°	534.0	10.7
130°-140°	599.4	12.0
140°-150°	587.8	11.8
150°-160°	493.1	9.9
160°-170°	327.0	6.5
170°-180°	114.3	2.3
0°-30°	561.6	11.2
0°-40°	872.1	17.4
0°-60°	1381.7	27.6
0°-90°	1625.2	32.5
90°-120°	718.0	14.4
90°-150°	2439.3	48.8
90°-180°	3374.0	67.5
0°-180°	4998.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	789	789	789	789	789	
5°	789	785	776	782	780	75
15°	750	742	718	704	697	211
25°	681	658	611	582	571	313
35°	587	550	488	442	427	367
45°	480	432	357	306	289	370
55°	365	309	232	189	176	326
65°	246	188	124	100	98	244
75°	131	81	57	52	51	139
85°	31	16	14	14	14	35
90°	1	13	36	34	34	5
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	

TEST NUMBER: P924252

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	788.6	788.6	788.6	788.6	788.6
2.5°	792.1	788.6	780.7	787.9	786.5
5°	788.6	785.0	775.7	782.2	780.0
7.5°	782.2	777.9	767.9	770.7	767.1
10°	773.6	768.5	754.3	752.1	747.9
12.5°	762.9	756.4	737.2	733.0	725.0
15°	750.0	742.1	717.9	704.3	697.3
17.5°	735.1	723.6	693.7	677.9	666.6
20°	717.9	703.6	668.0	650.2	634.4
22.5°	699.4	683.0	641.6	617.3	606.6
25°	680.9	658.0	610.8	581.7	570.9
27.5°	658.7	634.4	582.3	548.7	532.3
30°	635.2	608.0	550.9	514.6	495.2
32.5°	612.3	579.5	521.0	478.1	460.3
35°	586.6	550.3	487.5	442.5	426.7
37.5°	561.6	522.3	456.0	406.8	388.9
40°	535.2	492.5	423.2	372.5	353.9
42.5°	508.1	462.5	390.4	337.5	319.8
45°	479.6	431.7	356.9	306.1	289.0
47.5°	452.5	401.8	324.7	274.0	258.3
50°	422.5	371.9	293.4	244.0	229.2
52.5°	393.1	339.6	263.3	216.3	202.7
55°	364.6	309.0	231.9	189.2	175.5
57.5°	335.4	278.3	204.2	164.2	152.7
60°	305.5	248.3	174.9	138.5	127.1
62.5°	276.2	219.1	149.9	115.6	109.9
65°	246.2	188.4	124.2	100.0	97.8
67.5°	217.7	159.8	100.0	87.8	85.7
70°	187.7	132.0	82.7	75.7	72.8
72.5°	159.1	106.3	69.2	63.5	62.1
75°	131.3	81.3	57.0	52.1	51.4
77.5°	103.5	57.8	44.9	42.1	40.6
80°	77.8	41.4	34.2	31.4	31.4
82.5°	54.2	27.9	23.6	22.1	22.1
85°	30.6	15.6	13.5	13.5	13.5
87.5°	11.4	5.7	5.7	5.0	5.0
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7

TEST NUMBER: P924252

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8

TEST NUMBER: P924252

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US950-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.26	7.97	8.36	9.06	10.56	3.25	3.95	4.34	5.04	6.55
	3H	8.90	9.53	10.01	10.64	12.16	4.41	5.04	5.52	6.14	7.66
	4H	9.49	10.09	10.61	11.19	12.72	4.84	5.44	5.96	6.54	8.07
	6H	9.88	10.43	11.01	11.54	13.08	5.14	5.69	6.27	6.80	8.33
	8H	10.00	10.52	11.13	11.64	13.17	5.22	5.74	6.35	6.86	8.39
	12H	10.04	10.54	11.18	11.65	13.21	5.25	5.75	6.38	6.86	8.41
4H	2H	7.26	7.86	8.38	8.96	10.49	3.81	4.41	4.94	5.51	7.04
	3H	9.05	9.55	10.18	10.68	12.21	5.13	5.63	6.26	6.76	8.30
	4H	9.72	10.17	10.85	11.29	12.85	5.66	6.12	6.79	7.23	8.79
	6H	10.20	10.59	11.34	11.73	13.28	6.05	6.44	7.19	7.58	9.13
	8H	10.36	10.72	11.50	11.86	13.42	6.17	6.53	7.31	7.67	9.23
	12H	10.43	10.77	11.59	11.91	13.48	6.22	6.55	7.37	7.69	9.26
8H	4H	9.67	10.04	10.81	11.17	12.73	5.91	6.28	7.05	7.41	8.98
	6H	10.21	10.51	11.37	11.68	13.24	6.40	6.70	7.56	7.88	9.44
	8H	10.40	10.67	11.57	11.82	13.41	6.58	6.84	7.75	8.00	9.58
	12H	10.52	10.75	11.69	11.90	13.52	6.68	6.91	7.85	8.06	9.68
12H	4H	9.62	9.95	10.77	11.09	12.66	5.91	6.24	7.07	7.38	8.96
	6H	10.18	10.44	11.34	11.60	13.18	6.45	6.71	7.61	7.86	9.45
	8H	10.38	10.61	11.55	11.76	13.38	6.64	6.87	7.80	8.02	9.63

END OF REPORT