

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924260

Luminaire Tested: DFN2DIP-HX2F0-020D060US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924260
REPORT IS A COMBINATION OF REPORTS P899192 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D060US950-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6687.5 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924260

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924260

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1858	1858	1858
5°	1858	1824	1837
10°	1837	1784	1774
15°	1808	1721	1678
20°	1772	1635	1562
25°	1735	1540	1450
30°	1686	1444	1309
35°	1637	1340	1186
40°	1588	1233	1044
45°	1531	1115	917
50°	1472	997	793
55°	1410	870	673
60°	1339	739	551
65°	1255	606	492
70°	1155	482	441
75°	1028	416	394
80°	847	337	332
85°	552	208	232

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2428 cd/sqm

TEST NUMBER: P924260

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.9	1.1
10°-20°	202.9	3.0
20°-30°	284.8	4.3
30°-40°	310.5	4.6
40°-50°	285.4	4.3
50°-60°	224.1	3.4
60°-70°	145.9	2.2
70°-80°	75.1	1.1
80°-90°	24.3	0.4
90°-100°	112.0	1.7
100°-110°	355.9	5.3
110°-120°	609.1	9.1
120°-130°	801.1	12.0
130°-140°	899.2	13.4
140°-150°	881.7	13.2
150°-160°	739.6	11.1
160°-170°	490.5	7.3
170°-180°	171.4	2.6
0°-30°	561.6	8.4
0°-40°	872.1	13.0
0°-60°	1381.7	20.7
0°-90°	1626.9	24.3
90°-120°	1077.0	16.1
90°-150°	3659.0	54.7
90°-180°	5061.0	75.7
0°-180°	6687.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	789	789	789	789	789	
5°	789	785	776	782	780	75
15°	750	742	718	704	697	211
25°	681	658	611	582	571	313
35°	587	550	488	442	427	367
45°	480	432	357	306	289	370
55°	365	309	232	189	176	326
65°	246	188	124	100	98	244
75°	131	81	57	52	51	139
85°	31	16	14	14	14	35
90°	2	20	54	50	52	7
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	

TEST NUMBER: P924260

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	788.6	788.6	788.6	788.6	788.6
2.5°	792.1	788.6	780.7	787.9	786.5
5°	788.6	785.0	775.7	782.2	780.0
7.5°	782.2	777.9	767.9	770.7	767.1
10°	773.6	768.5	754.3	752.1	747.9
12.5°	762.9	756.4	737.2	733.0	725.0
15°	750.0	742.1	717.9	704.3	697.3
17.5°	735.1	723.6	693.7	677.9	666.6
20°	717.9	703.6	668.0	650.2	634.4
22.5°	699.4	683.0	641.6	617.3	606.6
25°	680.9	658.0	610.8	581.7	570.9
27.5°	658.7	634.4	582.3	548.7	532.3
30°	635.2	608.0	550.9	514.6	495.2
32.5°	612.3	579.5	521.0	478.1	460.3
35°	586.6	550.3	487.5	442.5	426.7
37.5°	561.6	522.3	456.0	406.8	388.9
40°	535.2	492.5	423.2	372.5	353.9
42.5°	508.1	462.5	390.4	337.5	319.8
45°	479.6	431.7	356.9	306.1	289.0
47.5°	452.5	401.8	324.7	274.0	258.3
50°	422.5	371.9	293.4	244.0	229.2
52.5°	393.1	339.6	263.3	216.3	202.7
55°	364.6	309.0	231.9	189.2	175.5
57.5°	335.4	278.3	204.2	164.2	152.7
60°	305.5	248.3	174.9	138.5	127.1
62.5°	276.2	219.1	149.9	115.6	109.9
65°	246.2	188.4	124.2	100.0	97.8
67.5°	217.7	159.8	100.0	87.8	85.7
70°	187.7	132.0	82.7	75.7	72.8
72.5°	159.1	106.3	69.2	63.5	62.1
75°	131.3	81.3	57.0	52.1	51.4
77.5°	103.5	57.8	44.9	42.1	40.6
80°	77.8	41.4	34.2	31.4	31.4
82.5°	54.2	27.9	23.6	22.1	22.1
85°	30.6	15.6	13.5	13.5	13.5
87.5°	11.4	5.7	5.7	5.0	5.0
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4

TEST NUMBER: P924260

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3

TEST NUMBER: P924260

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US950-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.08	6.73	7.23	7.87	9.47	2.06	2.72	3.22	3.86	5.46
	3H	7.72	8.30	8.88	9.45	11.06	3.22	3.81	4.38	4.96	6.57
	4H	8.30	8.86	9.47	10.00	11.62	3.65	4.21	4.82	5.36	6.97
	6H	8.69	9.20	9.87	10.35	11.98	3.95	4.46	5.13	5.61	7.24
	8H	8.80	9.29	9.98	10.45	12.07	4.02	4.51	5.20	5.68	7.30
	12H	8.85	9.31	10.03	10.47	12.11	4.05	4.52	5.24	5.68	7.32
4H	2H	6.07	6.63	7.25	7.77	9.39	2.62	3.18	3.80	4.33	5.94
	3H	7.85	8.32	9.04	9.49	11.12	3.94	4.40	5.12	5.57	7.20
	4H	8.52	8.95	9.70	10.11	11.76	4.46	4.89	5.65	6.05	7.70
	6H	9.00	9.37	10.19	10.55	12.19	4.85	5.22	6.04	6.40	8.04
	8H	9.16	9.50	10.35	10.68	12.33	4.97	5.31	6.16	6.48	8.14
	12H	9.23	9.54	10.43	10.73	12.39	5.02	5.33	6.22	6.51	8.17
8H	4H	8.47	8.81	9.66	9.99	11.64	4.71	5.06	5.90	6.23	7.88
	6H	9.00	9.28	10.21	10.50	12.15	5.20	5.48	6.41	6.70	8.35
	8H	9.20	9.45	10.41	10.64	12.31	5.38	5.62	6.59	6.82	8.49
	12H	9.32	9.53	10.53	10.72	12.43	5.48	5.69	6.69	6.88	8.58
12H	4H	8.41	8.72	9.62	9.91	11.57	4.71	5.02	5.91	6.20	7.86
	6H	8.98	9.22	10.19	10.42	12.09	5.24	5.49	6.45	6.68	8.35
	8H	9.17	9.39	10.39	10.58	12.28	5.43	5.65	6.64	6.84	8.54

END OF REPORT