

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924286

Luminaire Tested: DFN2DIP-HX2F0-040D030US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924286
REPORT IS A COMBINATION OF REPORTS P899165 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D030US950-FLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6310.7 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924286
CATALOG NUMBER: DFN2DIP-HX2F0-040D030US950-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P924286

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60		
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55	50		
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46	42		
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	36		
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31		
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27		
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23		
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21		
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	19		
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17		
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3498	3498	3498
5°	3498	3441	3466
10°	3465	3387	3413
15°	3408	3323	3333
20°	3334	3237	3252
25°	3259	3136	3159
30°	3168	3042	3043
35°	3081	2932	2920
40°	2974	2820	2802
45°	2868	2708	2681
50°	2751	2590	2543
55°	2629	2454	2413
60°	2490	2293	2265
65°	2337	2126	2092
70°	2144	1922	1902
75°	1878	1677	1719
80°	1554	1365	1387
85°	1056	856	858

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2868 cd/sqm



TEST NUMBER: P924286

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.8	2.2
10°-20°	393.2	6.2
20°-30°	577.9	9.2
30°-40°	671.2	10.6
40°-50°	670.3	10.6
50°-60°	584.5	9.3
60°-70°	432.1	6.8
70°-80°	244.5	3.9
80°-90°	67.1	1.1
90°-100°	56.0	0.9
100°-110°	178.0	2.8
110°-120°	304.6	4.8
120°-130°	400.5	6.3
130°-140°	449.6	7.1
140°-150°	440.9	7.0
150°-160°	369.8	5.9
160°-170°	245.3	3.9
170°-180°	85.7	1.4
0°-30°	1110.8	17.6
0°-40°	1782.0	28.2
0°-60°	3036.8	48.1
0°-90°	3780.4	59.9
90°-120°	538.5	8.5
90°-150°	1829.5	29.0
90°-180°	2530.0	40.1
0°-180°	6310.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	1	10	27	25	26	6
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	



TEST NUMBER: P924286

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3



TEST NUMBER: P924286

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2



TEST NUMBER: P924286
 CATALOG NUMBER: DFN2DIP-HX2F0-040D030US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.35	13.31	13.22	14.20	15.32	11.93	12.89	12.80	13.78	14.90
	3H	13.99	14.85	14.87	15.75	16.90	13.53	14.39	14.41	15.29	16.44
	4H	14.57	15.38	15.47	16.29	17.45	14.11	14.92	15.01	15.83	16.99
	6H	14.96	15.70	15.86	16.62	17.79	14.50	15.25	15.40	16.16	17.33
	8H	15.05	15.77	15.97	16.70	17.87	14.60	15.31	15.51	16.24	17.41
	12H	15.10	15.78	16.02	16.70	17.89	14.63	15.31	15.55	16.24	17.43
4H	2H	12.82	13.63	13.72	14.53	15.69	12.48	13.29	13.38	14.19	15.35
	3H	14.66	15.34	15.57	16.28	17.45	14.28	14.96	15.19	15.89	17.06
	4H	15.36	15.98	16.28	16.91	18.11	14.97	15.58	15.89	16.52	17.71
	6H	15.86	16.39	16.79	17.35	18.54	15.46	16.00	16.40	16.95	18.15
	8H	16.00	16.50	16.93	17.44	18.66	15.60	16.10	16.54	17.05	18.26
	12H	16.06	16.51	17.02	17.48	18.70	15.66	16.11	16.62	17.07	18.29
8H	4H	15.55	16.05	16.49	17.00	18.21	15.20	15.70	16.14	16.65	17.86
	6H	16.16	16.57	17.12	17.56	18.77	15.81	16.22	16.77	17.21	18.42
	8H	16.36	16.73	17.34	17.71	18.94	16.01	16.37	16.98	17.35	18.58
	12H	16.48	16.81	17.46	17.78	19.06	16.11	16.44	17.09	17.41	18.69
12H	4H	15.54	15.99	16.50	16.96	18.18	15.20	15.65	16.15	16.61	17.83
	6H	16.18	16.55	17.16	17.53	18.76	15.84	16.21	16.82	17.19	18.42
	8H	16.41	16.73	17.39	17.71	18.99	16.07	16.39	17.04	17.36	18.64