

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924336

Luminaire Tested: DFN2DIP-HX2F0-060D050US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924336
REPORT IS A COMBINATION OF REPORTS P899190 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D050US950-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9086.9 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 97.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924336
CATALOG NUMBER: DFN2DIP-HX2F0-060D050US950-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P924336

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US950-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54		
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46		
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39		
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34		
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33	30		
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26		
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	23		
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21		
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19		
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17		
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5574	5574	5574
5°	5574	5472	5510
10°	5510	5352	5321
15°	5425	5162	5034
20°	5316	4906	4686
25°	5204	4621	4351
30°	5057	4331	3928
35°	4912	4020	3557
40°	4765	3699	3134
45°	4594	3345	2751
50°	4417	2989	2377
55°	4231	2611	2019
60°	4015	2217	1652
65°	3767	1818	1476
70°	3465	1446	1321
75°	3085	1249	1183
80°	2539	1013	996
85°	1661	624	697

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4594 cd/sqm



TEST NUMBER: P924336

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.7	2.4
10°-20°	608.7	6.7
20°-30°	854.5	9.4
30°-40°	931.5	10.3
40°-50°	856.2	9.4
50°-60°	672.4	7.4
60°-70°	437.7	4.8
70°-80°	225.3	2.5
80°-90°	61.8	0.7
90°-100°	93.4	1.0
100°-110°	296.6	3.3
110°-120°	507.6	5.6
120°-130°	667.5	7.3
130°-140°	749.3	8.2
140°-150°	734.8	8.1
150°-160°	616.4	6.8
160°-170°	408.8	4.5
170°-180°	142.9	1.6
0°-30°	1684.9	18.5
0°-40°	2616.4	28.8
0°-60°	4144.9	45.6
0°-90°	4869.7	53.6
90°-120°	897.5	9.9
90°-150°	3049.2	33.6
90°-180°	4217.0	46.4
0°-180°	9086.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2366	2366	2366	2366	2366	
5°	2366	2355	2327	2346	2340	224
15°	2250	2226	2154	2113	2092	634
25°	2042	1974	1833	1745	1713	939
35°	1760	1651	1462	1327	1280	1102
45°	1439	1295	1071	918	867	1111
55°	1094	927	696	567	527	978
65°	739	565	372	300	293	732
75°	394	244	171	156	154	417
85°	92	47	41	41	41	106
90°	1	16	45	42	43	9
95°	66	79	81	81	79	74
105°	274	277	280	282	282	289
115°	509	517	514	513	509	504
125°	741	752	749	744	743	662
135°	958	972	975	974	970	741
145°	1163	1172	1180	1181	1176	727
155°	1330	1334	1338	1344	1340	612
165°	1447	1446	1446	1455	1449	408
175°	1506	1502	1500	1509	1501	143
180°	1509	1509	1509	1509	1509	



TEST NUMBER: P924336

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2365.7	2365.7	2365.7	2365.7	2365.7
2.5°	2376.4	2365.7	2342.1	2363.6	2359.3
5°	2365.7	2355.0	2327.1	2346.5	2340.1
7.5°	2346.5	2333.7	2303.7	2312.1	2301.4
10°	2320.7	2305.7	2263.1	2256.5	2243.7
12.5°	2288.7	2269.4	2211.5	2198.8	2175.1
15°	2250.1	2226.4	2153.8	2113.1	2091.7
17.5°	2205.2	2170.8	2080.9	2033.8	1999.6
20°	2153.8	2110.8	2003.9	1950.5	1903.2
22.5°	2098.1	2048.8	1924.6	1851.9	1819.9
25°	2042.5	1973.9	1832.6	1745.0	1712.7
27.5°	1976.2	1903.2	1747.0	1646.3	1597.1
30°	1905.5	1824.0	1652.7	1543.7	1485.8
32.5°	1836.9	1738.4	1563.0	1434.4	1380.8
35°	1759.9	1650.7	1462.4	1327.4	1280.2
37.5°	1685.0	1567.0	1368.1	1220.3	1166.8
40°	1605.7	1477.4	1269.5	1117.5	1061.9
42.5°	1524.4	1387.4	1171.1	1012.6	959.2
45°	1438.7	1295.2	1070.6	918.3	867.0
47.5°	1357.4	1205.5	974.2	822.1	775.0
50°	1267.5	1115.5	880.0	732.1	687.4
52.5°	1179.5	1019.0	790.0	648.7	608.1
55°	1094.0	927.0	695.8	567.4	526.7
57.5°	1006.3	834.9	612.4	492.5	458.1
60°	916.3	745.1	524.5	415.5	381.1
62.5°	828.6	657.4	449.5	346.9	329.8
65°	738.7	565.1	372.5	299.8	293.3
67.5°	653.0	479.5	299.8	263.3	256.9
70°	563.1	396.1	248.2	227.0	218.3
72.5°	477.5	318.9	207.6	190.6	186.2
75°	393.9	243.9	171.2	156.3	154.3
77.5°	310.5	173.3	134.9	126.3	122.0
80°	233.3	124.2	102.7	94.3	94.3
82.5°	162.7	83.6	70.6	66.3	66.3
85°	92.0	47.0	40.6	40.6	40.6
87.5°	34.3	17.1	17.1	15.0	15.0
90°	1.3	16.4	44.6	41.9	43.2
92.5°	28.2	38.2	39.6	40.9	40.9
95°	66.4	79.2	81.4	81.4	79.2
97.5°	110.5	122.3	127.4	127.4	127.4
100°	161.4	171.9	175.5	175.5	174.2
102.5°	215.1	222.9	227.8	229.2	227.8
105°	273.8	277.4	280.2	282.4	282.4
107.5°	332.0	337.4	337.4	338.4	332.0
110°	388.4	395.7	395.7	395.7	392.0



TEST NUMBER: P924336

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US950-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	449.3	457.1	455.7	452.1	449.3
115°	509.3	516.7	514.4	513.1	509.3
117.5°	569.0	579.0	572.6	569.0	565.3
120°	629.0	639.0	629.0	629.0	624.9
122.5°	683.5	696.3	689.9	686.3	683.5
125°	740.9	752.2	748.6	744.5	743.2
127.5°	796.8	810.9	805.9	800.4	796.8
130°	849.2	865.5	863.2	860.5	855.5
132.5°	907.8	920.5	921.5	915.1	911.5
135°	958.3	972.3	975.1	973.7	970.1
137.5°	1014.7	1026.0	1028.3	1027.4	1021.9
140°	1064.2	1075.6	1081.9	1081.9	1077.0
142.5°	1115.1	1126.6	1130.2	1131.5	1126.6
145°	1163.4	1172.5	1179.7	1181.1	1176.1
147.5°	1206.6	1218.0	1223.4	1225.7	1220.6
150°	1251.2	1258.9	1263.9	1268.0	1263.9
152.5°	1290.8	1298.5	1304.8	1309.8	1304.8
155°	1330.3	1333.9	1338.0	1344.4	1340.3
157.5°	1364.4	1367.1	1369.4	1378.5	1372.1
160°	1394.8	1397.6	1398.9	1406.7	1401.2
162.5°	1423.1	1423.1	1424.4	1433.1	1426.7
165°	1447.2	1445.8	1445.8	1454.9	1448.6
167.5°	1469.0	1464.9	1464.9	1474.0	1467.6
170°	1485.4	1481.8	1480.4	1489.5	1481.8
172.5°	1496.7	1493.1	1491.8	1500.8	1493.1
175°	1505.9	1502.2	1499.5	1508.6	1500.8
177.5°	1510.8	1507.2	1504.5	1512.2	1504.5
180°	1508.6	1508.6	1508.6	1508.6	1508.6



TEST NUMBER: P924336
 CATALOG NUMBER: DFN2DIP-HX2F0-060D050US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.31	14.17	14.24	15.11	16.33	9.29	10.15	10.22	11.10	12.32
	3H	14.96	15.73	15.91	16.69	17.93	10.46	11.23	11.41	12.19	13.43
	4H	15.55	16.28	16.51	17.24	18.50	10.90	11.63	11.86	12.59	13.85
	6H	15.96	16.63	16.93	17.59	18.86	11.21	11.88	12.18	12.85	14.11
	8H	16.07	16.71	17.05	17.69	18.96	11.30	11.93	12.27	12.91	14.18
	12H	16.13	16.73	17.11	17.71	19.00	11.33	11.94	12.31	12.91	14.20
4H	2H	13.33	14.05	14.29	15.01	16.27	9.88	10.60	10.84	11.56	12.82
	3H	15.13	15.73	16.10	16.72	17.99	11.21	11.81	12.18	12.80	14.07
	4H	15.80	16.35	16.78	17.34	18.63	11.74	12.29	12.73	13.28	14.57
	6H	16.30	16.77	17.29	17.78	19.07	12.15	12.62	13.14	13.63	14.92
	8H	16.46	16.90	17.45	17.90	19.20	12.27	12.71	13.26	13.71	15.01
	12H	16.54	16.94	17.55	17.95	19.26	12.32	12.72	13.34	13.74	15.05
8H	4H	15.77	16.21	16.76	17.21	18.52	12.01	12.45	13.01	13.45	14.76
	6H	16.31	16.67	17.33	17.71	19.02	12.51	12.87	13.53	13.91	15.22
	8H	16.51	16.83	17.54	17.86	19.18	12.68	13.01	13.71	14.03	15.36
	12H	16.63	16.91	17.66	17.94	19.30	12.79	13.07	13.82	14.10	15.46
12H	4H	15.72	16.12	16.73	17.14	18.45	12.01	12.41	13.03	13.43	14.74
	6H	16.28	16.60	17.31	17.63	18.95	12.55	12.87	13.58	13.90	15.22
	8H	16.49	16.77	17.52	17.79	19.16	12.75	13.03	13.78	14.05	15.42