

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902519

Luminaire Tested: DFN2DIP-HX3F0-030D030US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902519
REPORT IS A COMBINATION OF REPORTS P900721 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-030D030US830-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5598.7 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902519

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902519

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1274	1274	1274
5°	1276	1256	1264
10°	1265	1238	1247
15°	1246	1217	1219
20°	1220	1188	1191
25°	1195	1153	1159
30°	1163	1120	1118
35°	1132	1082	1074
40°	1095	1044	1033
45°	1058	1005	991
50°	1017	965	942
55°	975	918	897
60°	926	862	846
65°	874	804	785
70°	807	734	719
75°	714	649	657
80°	602	541	541
85°	428	358	351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1058 cd/sqm

TEST NUMBER: P902519

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.8
10°-20°	291.4	5.2
20°-30°	428.2	7.6
30°-40°	497.3	8.9
40°-50°	496.7	8.9
50°-60°	433.1	7.7
60°-70°	320.2	5.7
70°-80°	181.1	3.2
80°-90°	49.5	0.9
90°-100°	31.5	0.6
100°-110°	117.3	2.1
110°-120°	311.1	5.6
120°-130°	516.0	9.2
130°-140°	548.1	9.8
140°-150°	509.4	9.1
150°-160°	409.6	7.3
160°-170°	263.9	4.7
170°-180°	90.8	1.6
0°-30°	823.1	14.7
0°-40°	1320.4	23.6
0°-60°	2250.3	40.2
0°-90°	2801.0	50.0
90°-120°	459.9	8.2
90°-150°	2033.4	36.3
90°-180°	2798.0	50.0
0°-180°	5598.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1100	1096	1084	1093	1091	104
15°	1047	1041	1027	1032	1026	295
25°	948	940	922	924	922	436
35°	818	807	790	784	779	511
45°	666	658	642	631	626	514
55°	504	497	485	472	467	450
65°	340	333	323	313	308	336
75°	178	176	170	164	166	190
85°	43	42	41	38	37	48
90°	1	8	14	17	19	5
95°	45	22	27	30	30	53
105°	210	231	42	50	52	224
115°	397	409	426	106	57	391
125°	561	570	584	588	590	501
135°	695	706	712	719	718	537
145°	806	805	817	822	818	504
155°	887	881	889	894	888	409
165°	935	931	933	938	933	264
175°	956	952	953	958	951	91
180°	954	954	954	954	954	

TEST NUMBER: P902519

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1100.2	1100.2	1100.2	1100.2	1100.2
2.5°	1106.6	1101.4	1089.7	1100.2	1098.3
5°	1100.2	1096.1	1084.4	1092.9	1090.8
7.5°	1092.9	1086.6	1074.9	1083.5	1081.3
10°	1081.3	1073.8	1061.2	1069.6	1066.5
12.5°	1065.4	1059.0	1046.4	1051.6	1049.5
15°	1047.4	1041.1	1027.3	1031.5	1026.2
17.5°	1025.1	1018.9	1005.0	1010.3	1005.0
20°	1000.8	994.5	979.7	982.8	978.6
22.5°	976.6	967.0	953.2	953.2	951.0
25°	947.9	939.5	921.5	923.6	921.5
27.5°	916.2	908.7	895.0	891.9	886.6
30°	884.5	876.0	860.2	857.0	852.7
32.5°	850.6	844.3	827.4	821.0	816.7
35°	817.8	807.3	790.3	783.9	778.6
37.5°	780.8	771.3	754.3	746.9	741.6
40°	742.7	734.2	717.3	707.8	703.6
42.5°	705.7	697.2	680.3	669.7	663.4
45°	665.5	658.1	642.2	630.6	626.3
47.5°	626.3	619.0	602.0	590.3	584.0
50°	585.0	579.8	565.0	550.2	544.9
52.5°	544.9	537.4	523.8	512.1	504.6
55°	503.7	497.3	484.6	471.9	466.7
57.5°	462.3	457.0	443.3	430.6	426.3
60°	421.0	416.9	402.1	390.4	387.3
62.5°	380.9	373.4	362.9	352.3	348.1
65°	339.7	333.3	322.7	313.2	307.9
67.5°	297.4	292.0	282.5	275.1	270.9
70°	258.2	253.9	244.4	237.0	232.8
72.5°	218.0	213.7	208.4	201.0	197.9
75°	177.7	175.7	170.3	164.0	166.2
77.5°	141.8	137.5	135.3	132.2	129.1
80°	105.8	104.7	102.5	99.4	97.4
82.5°	71.9	71.9	71.0	66.6	66.6
85°	43.4	42.3	41.3	38.1	37.0
87.5°	19.0	17.0	14.8	11.7	10.6
90°	0.7	8.3	13.8	17.3	18.6
92.5°	17.3	14.5	16.6	18.0	18.6
95°	44.9	22.1	26.9	30.4	29.7
97.5°	80.8	24.2	35.2	37.3	38.0
100°	122.2	27.6	39.4	44.9	46.3
102.5°	167.8	166.5	40.7	48.3	50.4
105°	209.9	230.6	42.1	49.7	52.5
107.5°	258.9	276.2	43.5	51.1	53.9
110°	305.9	320.4	120.8	51.8	54.6

TEST NUMBER: P902519

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.2	362.5	350.8	53.2	55.2
115°	397.0	408.8	426.0	106.3	56.6
117.5°	437.8	451.6	463.4	364.6	183.7
120°	483.3	493.7	506.1	514.4	421.2
122.5°	522.0	533.1	547.0	551.0	551.8
125°	561.4	570.3	583.5	588.3	590.4
127.5°	597.3	606.9	617.4	624.2	624.9
130°	631.1	642.2	649.8	657.3	656.8
132.5°	665.6	674.7	682.2	688.4	687.8
135°	694.7	705.8	711.9	718.9	717.5
137.5°	725.0	733.3	740.3	747.2	745.1
140°	754.7	760.3	767.8	774.0	770.6
142.5°	779.7	784.5	793.4	798.9	795.5
145°	805.9	805.1	816.9	821.7	818.2
147.5°	828.6	826.5	838.3	841.7	839.0
150°	850.7	845.9	857.0	861.0	857.6
152.5°	869.3	863.8	874.2	878.4	873.5
155°	887.3	881.2	889.4	893.5	888.1
157.5°	901.8	896.4	902.6	907.4	901.8
160°	914.3	910.1	914.3	918.4	913.5
162.5°	925.3	921.1	924.6	929.4	923.2
165°	934.9	930.9	932.9	937.7	932.9
167.5°	942.5	938.4	940.5	945.4	939.1
170°	948.8	944.6	946.0	950.8	944.6
172.5°	952.9	948.8	950.2	955.0	948.8
175°	956.3	951.5	952.9	957.7	950.8
177.5°	957.7	952.9	953.7	958.5	952.3
180°	954.3	954.3	954.3	954.3	954.3

TEST NUMBER: P902519

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.07	8.93	9.03	9.91	11.18	7.65	8.51	8.60	9.48	10.75
	3H	9.73	10.50	10.69	11.48	12.77	9.26	10.03	10.23	11.01	12.31
	4H	10.31	11.04	11.29	12.03	13.33	9.84	10.57	10.82	11.56	12.86
	6H	10.70	11.38	11.70	12.37	13.68	10.23	10.91	11.23	11.90	13.21
	8H	10.80	11.45	11.80	12.45	13.76	10.34	10.98	11.33	11.98	13.30
	12H	10.85	11.46	11.85	12.46	13.80	10.38	10.99	11.38	11.99	13.32
4H	2H	8.53	9.26	9.52	10.25	11.55	8.19	8.92	9.18	9.91	11.21
	3H	10.39	11.00	11.39	12.01	13.33	10.00	10.61	11.00	11.63	12.94
	4H	11.10	11.66	12.10	12.66	14.00	10.70	11.26	11.70	12.26	13.60
	6H	11.61	12.09	12.62	13.12	14.45	11.20	11.68	12.22	12.71	14.05
	8H	11.75	12.20	12.77	13.22	14.58	11.34	11.79	12.36	12.82	14.17
	12H	11.82	12.23	12.86	13.27	14.62	11.40	11.81	12.44	12.85	14.21
8H	4H	11.29	11.74	12.31	12.76	14.12	10.93	11.38	11.95	12.41	13.76
	6H	11.91	12.28	12.96	13.35	14.70	11.55	11.93	12.60	12.99	14.34
	8H	12.13	12.46	13.18	13.51	14.87	11.76	12.09	12.81	13.14	14.51
	12H	12.26	12.54	13.31	13.59	15.00	11.88	12.16	12.93	13.21	14.62
12H	4H	11.28	11.68	12.31	12.72	14.08	10.93	11.33	11.96	12.37	13.73
	6H	11.94	12.27	12.99	13.32	14.69	11.59	11.92	12.64	12.97	14.34
	8H	12.18	12.47	13.23	13.51	14.92	11.82	12.11	12.88	13.16	14.57