

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926874

Luminaire Tested: DFN2DIP-HX4F0-040D040US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926874
REPORT IS A COMBINATION OF REPORTS P900820 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D040US830-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6936.8 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 63.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926874

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926874

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1159	1159	1159
5°	1160	1140	1148
10°	1149	1118	1110
15°	1133	1081	1053
20°	1113	1030	982
25°	1091	973	913
30°	1063	915	827
35°	1035	852	751
40°	1006	787	663
45°	973	715	584
50°	938	642	507
55°	903	564	432
60°	861	483	356
65°	813	400	320
70°	756	322	290
75°	683	284	264
80°	578	239	229
85°	404	160	173

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 973 cd/sqm

TEST NUMBER: P926874

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	2.1
10°-20°	400.9	5.8
20°-30°	562.8	8.1
30°-40°	613.5	8.8
40°-50°	563.9	8.1
50°-60°	442.8	6.4
60°-70°	288.3	4.2
70°-80°	148.4	2.1
80°-90°	40.1	0.6
90°-100°	41.9	0.6
100°-110°	156.4	2.3
110°-120°	414.8	6.0
120°-130°	688.0	9.9
130°-140°	730.8	10.5
140°-150°	679.2	9.8
150°-160°	546.0	7.9
160°-170°	351.9	5.1
170°-180°	121.1	1.7
0°-30°	1109.7	16.0
0°-40°	1723.2	24.8
0°-60°	2730.0	39.4
0°-90°	3206.8	46.2
90°-120°	613.1	8.8
90°-150°	2711.1	39.1
90°-180°	3730.0	53.8
0°-180°	6936.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1545	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	720	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	1	11	18	23	25	6
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	667
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	

TEST NUMBER: P926874

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.1	1558.1	1558.1	1558.1	1558.1
2.5°	1565.2	1558.1	1542.6	1556.8	1553.9
5°	1558.1	1551.1	1532.7	1545.4	1541.3
7.5°	1545.4	1537.0	1517.3	1522.8	1515.8
10°	1528.5	1518.7	1490.5	1486.1	1477.8
12.5°	1507.4	1494.7	1456.5	1448.2	1432.6
15°	1482.0	1466.4	1418.6	1391.8	1377.7
17.5°	1452.4	1429.8	1370.5	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.6	1253.5
22.5°	1381.9	1349.5	1267.6	1219.7	1198.7
25°	1345.2	1300.1	1207.0	1149.3	1128.0
27.5°	1301.6	1253.5	1150.6	1084.3	1051.8
30°	1255.0	1201.3	1088.5	1016.7	978.6
32.5°	1209.9	1144.9	1029.4	944.8	909.4
35°	1159.2	1087.2	963.1	874.3	843.2
37.5°	1109.8	1032.1	901.0	803.7	768.5
40°	1057.6	973.0	836.2	736.1	699.4
42.5°	1004.0	913.8	771.3	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.5	482.2	452.7
52.5°	776.9	671.2	520.4	427.2	400.5
55°	720.5	610.6	458.2	373.7	346.9
57.5°	662.8	549.9	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.0	228.5	217.2
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.5	56.2	66.3	69.9
107.5°	345.2	368.2	58.1	68.1	71.8
110°	407.9	427.1	161.2	69.1	72.7

TEST NUMBER: P926874

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.0	141.8	75.6
117.5°	583.7	602.1	617.8	486.0	244.9
120°	644.5	658.2	674.8	686.0	561.6
122.5°	695.9	710.7	729.2	734.7	735.6
125°	748.4	760.5	777.9	784.4	787.2
127.5°	796.3	809.2	823.1	832.3	833.2
130°	841.5	856.3	866.3	876.4	875.6
132.5°	887.5	899.5	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.4	956.6
137.5°	966.6	977.7	987.0	996.1	993.4
140°	1006.2	1013.7	1023.7	1032.0	1027.4
142.5°	1039.5	1045.9	1057.9	1065.1	1060.6
145°	1074.4	1073.5	1089.1	1095.6	1090.9
147.5°	1104.7	1102.0	1117.6	1122.2	1118.7
150°	1134.2	1127.8	1142.6	1148.1	1143.4
152.5°	1159.1	1151.7	1165.5	1171.1	1164.6
155°	1183.0	1174.8	1185.9	1191.3	1184.0
157.5°	1202.3	1195.0	1203.4	1209.8	1202.3
160°	1218.9	1213.4	1218.9	1224.4	1218.0
162.5°	1233.6	1228.2	1232.8	1239.2	1230.9
165°	1246.6	1241.1	1243.8	1250.2	1243.8
167.5°	1256.7	1251.1	1254.0	1260.4	1252.1
170°	1265.0	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.0	1266.9	1273.3	1265.0
175°	1275.0	1268.6	1270.5	1276.9	1267.8
177.5°	1276.9	1270.5	1271.4	1277.9	1269.6
180°	1272.4	1272.4	1272.4	1272.4	1272.4

TEST NUMBER: P926874

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.30	8.10	8.29	9.10	10.43	3.27	4.07	4.26	5.07	6.40
	3H	8.97	9.69	9.98	10.70	12.05	4.46	5.17	5.46	6.18	7.53
	4H	9.58	10.26	10.60	11.27	12.63	4.91	5.58	5.93	6.60	7.95
	6H	10.00	10.62	11.03	11.64	13.01	5.23	5.85	6.26	6.87	8.24
	8H	10.13	10.72	11.16	11.75	13.12	5.32	5.91	6.35	6.95	8.31
	12H	10.19	10.75	11.23	11.78	13.17	5.36	5.93	6.40	6.95	8.34
4H	2H	7.31	7.99	8.34	9.00	10.36	3.86	4.54	4.89	5.55	6.91
	3H	9.14	9.70	10.17	10.74	12.11	5.21	5.77	6.24	6.82	8.19
	4H	9.83	10.35	10.87	11.38	12.77	5.76	6.27	6.80	7.31	8.70
	6H	10.34	10.79	11.40	11.84	13.23	6.18	6.62	7.23	7.68	9.07
	8H	10.52	10.93	11.57	11.98	13.39	6.31	6.72	7.36	7.77	9.17
	12H	10.61	10.99	11.68	12.05	13.46	6.37	6.74	7.44	7.81	9.22
8H	4H	9.80	10.21	10.85	11.26	12.66	6.04	6.45	7.09	7.50	8.90
	6H	10.36	10.70	11.44	11.80	13.20	6.56	6.90	7.63	7.99	9.39
	8H	10.58	10.88	11.66	11.96	13.37	6.75	7.05	7.83	8.12	9.54
	12H	10.72	10.98	11.80	12.05	13.51	6.87	7.13	7.95	8.20	9.66
12H	4H	9.75	10.12	10.82	11.19	12.59	6.04	6.41	7.11	7.48	8.89
	6H	10.34	10.64	11.42	11.71	13.13	6.61	6.91	7.69	7.98	9.40
	8H	10.56	10.82	11.64	11.89	13.35	6.82	7.08	7.90	8.15	9.61

END OF REPORT