

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926877

Luminaire Tested: DFN2DIP-HX4F0-040D050US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926877
REPORT IS A COMBINATION OF REPORTS P899318 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D050US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7375.1 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926877

CATALOG NUMBER: DFN2DIP-HX4F0-040D050US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926877

CATALOG NUMBER: DFN2DIP-HX4F0-040D050US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1159	1159	1159
5°	1160	1140	1148
10°	1149	1118	1110
15°	1133	1081	1053
20°	1113	1030	982
25°	1091	973	913
30°	1063	915	827
35°	1035	852	751
40°	1006	787	663
45°	973	715	584
50°	938	642	507
55°	903	564	432
60°	861	483	356
65°	813	400	320
70°	756	322	290
75°	683	284	264
80°	578	239	229
85°	404	160	173

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1124 cd/sqm

TEST NUMBER: P926877

CATALOG NUMBER: DFN2DIP-HX4F0-040D050US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	2.0
10°-20°	400.9	5.4
20°-30°	562.8	7.6
30°-40°	613.5	8.3
40°-50°	563.9	7.6
50°-60°	442.8	6.0
60°-70°	288.3	3.9
70°-80°	148.4	2.0
80°-90°	42.1	0.6
90°-100°	92.2	1.3
100°-110°	293.0	4.0
110°-120°	501.5	6.8
120°-130°	659.5	8.9
130°-140°	740.3	10.0
140°-150°	725.9	9.8
150°-160°	608.9	8.3
160°-170°	403.8	5.5
170°-180°	141.2	1.9
0°-30°	1109.7	15.0
0°-40°	1723.2	23.4
0°-60°	2730.0	37.0
0°-90°	3208.7	43.5
90°-120°	886.7	12.0
90°-150°	3012.4	40.8
90°-180°	4166.0	56.5
0°-180°	7375.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1545	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	720	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	1	16	44	41	43	7
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1437	1431	403
175°	1488	1484	1481	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P926877

CATALOG NUMBER: DFN2DIP-HX4F0-040D050US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.1	1558.1	1558.1	1558.1	1558.1
2.5°	1565.2	1558.1	1542.6	1556.8	1553.9
5°	1558.1	1551.1	1532.7	1545.4	1541.3
7.5°	1545.4	1537.0	1517.3	1522.8	1515.8
10°	1528.5	1518.7	1490.5	1486.1	1477.8
12.5°	1507.4	1494.7	1456.5	1448.2	1432.6
15°	1482.0	1466.4	1418.6	1391.8	1377.7
17.5°	1452.4	1429.8	1370.5	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.6	1253.5
22.5°	1381.9	1349.5	1267.6	1219.7	1198.7
25°	1345.2	1300.1	1207.0	1149.3	1128.0
27.5°	1301.6	1253.5	1150.6	1084.3	1051.8
30°	1255.0	1201.3	1088.5	1016.7	978.6
32.5°	1209.9	1144.9	1029.4	944.8	909.4
35°	1159.2	1087.2	963.1	874.3	843.2
37.5°	1109.8	1032.1	901.0	803.7	768.5
40°	1057.6	973.0	836.2	736.1	699.4
42.5°	1004.0	913.8	771.3	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.5	482.2	452.7
52.5°	776.9	671.2	520.4	427.2	400.5
55°	720.5	610.6	458.2	373.7	346.9
57.5°	662.8	549.9	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.0	228.5	217.2
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	390.9	390.9	390.9	387.3

TEST NUMBER: P926877

CATALOG NUMBER: DFN2DIP-HX4F0-040D050US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.2	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.5
120°	621.4	631.3	621.4	621.4	617.3
122.5°	675.3	687.9	681.6	678.0	675.3
125°	731.9	743.2	739.6	735.5	734.2
127.5°	787.2	801.1	796.2	790.8	787.2
130°	838.9	855.0	852.8	850.1	845.1
132.5°	896.9	909.4	910.4	904.0	900.5
135°	946.7	960.6	963.3	962.0	958.4
137.5°	1002.4	1013.7	1015.9	1015.0	1009.6
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.3	1165.5	1166.9	1161.9
147.5°	1192.1	1203.3	1208.7	1210.9	1205.9
150°	1236.1	1243.7	1248.6	1252.7	1248.6
152.5°	1275.2	1282.8	1289.1	1294.1	1289.1
155°	1314.2	1317.8	1321.9	1328.2	1324.1
157.5°	1348.0	1350.6	1352.9	1361.9	1355.6
160°	1378.0	1380.8	1382.1	1389.7	1384.3
162.5°	1405.9	1405.9	1407.2	1415.8	1409.5
165°	1429.8	1428.4	1428.4	1437.4	1431.1
167.5°	1451.3	1447.2	1447.2	1456.3	1449.9
170°	1467.5	1463.9	1462.6	1471.5	1463.9
172.5°	1478.7	1475.1	1473.8	1482.7	1475.1
175°	1487.7	1484.1	1481.4	1490.4	1482.7
177.5°	1492.6	1489.1	1486.3	1494.0	1486.3
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P926877

CATALOG NUMBER: DFN2DIP-HX4F0-040D050US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.02	7.80	8.04	8.82	10.18	2.99	3.77	4.01	4.79	6.16
	3H	8.69	9.39	9.72	10.42	11.81	4.18	4.88	5.21	5.91	7.29
	4H	9.30	9.96	10.34	10.99	12.39	4.63	5.29	5.67	6.32	7.71
	6H	9.72	10.33	10.77	11.37	12.77	4.95	5.56	6.00	6.59	8.00
	8H	9.85	10.42	10.90	11.48	12.88	5.04	5.62	6.09	6.67	8.07
	12H	9.91	10.46	10.97	11.50	12.92	5.08	5.63	6.14	6.68	8.10
4H	2H	7.03	7.69	8.08	8.72	10.12	3.58	4.24	4.63	5.28	6.67
	3H	8.86	9.41	9.91	10.47	11.87	4.93	5.48	5.98	6.54	7.94
	4H	9.55	10.05	10.61	11.10	12.53	5.48	5.98	6.54	7.03	8.46
	6H	10.06	10.49	11.13	11.57	12.99	5.90	6.33	6.96	7.40	8.82
	8H	10.24	10.64	11.31	11.71	13.14	6.02	6.43	7.09	7.49	8.93
	12H	10.33	10.69	11.42	11.78	13.22	6.09	6.45	7.17	7.53	8.98
8H	4H	9.51	9.92	10.58	10.98	12.42	5.75	6.16	6.82	7.22	8.66
	6H	10.08	10.41	11.17	11.52	12.95	6.27	6.60	7.37	7.72	9.15
	8H	10.30	10.59	11.39	11.68	13.13	6.46	6.76	7.56	7.85	9.30
	12H	10.43	10.69	11.54	11.78	13.27	6.58	6.84	7.69	7.93	9.42
12H	4H	9.46	9.83	10.55	10.91	12.35	5.76	6.12	6.84	7.20	8.64
	6H	10.05	10.35	11.15	11.44	12.89	6.32	6.61	7.42	7.71	9.16
	8H	10.27	10.53	11.38	11.62	13.11	6.53	6.79	7.63	7.88	9.37

END OF REPORT