

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926900

Luminaire Tested: DFN2DIP-HX4F0-040D110US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926900
REPORT IS A COMBINATION OF REPORTS P900945 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US830-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13996.1 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 120.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926900

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926900

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	88	85	81	82	79	76	73	62	59	58	45	44	43	31	30	29
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1091	1091	1091
5°	1093	1076	1083
10°	1084	1061	1068
15°	1068	1044	1045
20°	1046	1020	1022
25°	1025	991	995
30°	998	964	960
35°	973	932	924
40°	942	900	889
45°	911	868	854
50°	877	834	813
55°	841	795	775
60°	801	749	732
65°	757	701	681
70°	701	643	626
75°	624	573	576
80°	531	484	479
85°	385	329	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1796 cd/sqm

TEST NUMBER: P926900

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	1.0
10°-20°	388.5	2.8
20°-30°	570.9	4.1
30°-40°	663.1	4.7
40°-50°	662.2	4.7
50°-60°	577.4	4.1
60°-70°	426.9	3.0
70°-80°	241.5	1.7
80°-90°	69.9	0.5
90°-100°	115.4	0.8
100°-110°	430.1	3.1
110°-120°	1140.7	8.2
120°-130°	1891.9	13.5
130°-140°	2009.6	14.4
140°-150°	1867.7	13.3
150°-160°	1501.6	10.7
160°-170°	967.6	6.9
170°-180°	333.0	2.4
0°-30°	1097.4	7.8
0°-40°	1760.5	12.6
0°-60°	3000.2	21.4
0°-90°	3738.4	26.7
90°-120°	1686.2	12.0
90°-150°	7455.4	53.3
90°-180°	10258.0	73.3
0°-180°	13996.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	2	30	50	63	68	13
95°	164	81	99	112	109	195
105°	770	846	155	182	192	822
115°	1456	1499	1562	390	208	1433
125°	2058	2091	2139	2157	2165	1836
135°	2547	2588	2610	2636	2631	1968
145°	2955	2952	2995	3013	3000	1848
155°	3253	3231	3261	3276	3256	1499
165°	3428	3413	3420	3438	3420	968
175°	3506	3489	3494	3512	3486	334
180°	3499	3499	3499	3499	3499	

TEST NUMBER: P926900

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1466.9	1466.9	1466.9	1466.9	1466.9
2.5°	1475.5	1468.4	1452.9	1466.9	1464.3
5°	1466.9	1461.3	1445.8	1457.0	1454.4
7.5°	1457.0	1448.6	1433.1	1444.5	1441.6
10°	1441.6	1431.8	1414.9	1426.1	1421.9
12.5°	1420.3	1412.0	1395.1	1402.2	1399.2
15°	1396.4	1388.0	1369.6	1375.3	1368.3
17.5°	1366.8	1358.4	1340.0	1347.0	1340.0
20°	1334.3	1325.9	1306.2	1310.4	1304.9
22.5°	1302.0	1289.2	1270.9	1270.9	1268.0
25°	1263.8	1252.6	1228.6	1231.4	1228.6
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1167.9	1146.8	1142.6	1136.9
32.5°	1134.1	1125.7	1103.1	1094.6	1088.9
35°	1090.4	1076.3	1053.7	1045.2	1038.2
37.5°	1041.0	1028.3	1005.6	995.8	988.8
40°	990.3	978.9	956.3	943.7	938.1
42.5°	940.9	929.5	907.1	892.8	884.4
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.6	787.1	778.7
50°	780.0	772.9	753.2	733.5	726.4
52.5°	726.4	716.6	698.3	682.7	672.9
55°	671.5	663.0	646.1	629.1	622.1
57.5°	616.4	609.4	590.9	574.1	568.4
60°	561.4	555.8	536.1	520.5	516.3
62.5°	507.8	497.9	483.9	469.7	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.5	325.8	315.9	310.4
72.5°	290.7	284.9	277.9	268.0	263.8
75°	236.9	234.2	227.0	218.7	221.5
77.5°	189.0	183.3	180.5	176.2	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	95.9	95.9	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	2.5	30.3	50.5	63.4	68.2
92.5°	63.4	53.3	60.7	65.9	68.2
95°	164.5	80.9	98.6	111.5	108.9
97.5°	296.1	88.7	128.9	136.8	139.2
100°	448.3	101.3	144.3	164.5	169.6
102.5°	615.1	610.3	149.4	177.1	184.9
105°	769.6	845.7	154.6	182.2	192.5
107.5°	949.5	1012.5	159.7	187.3	197.5
110°	1121.7	1174.6	443.2	190.0	199.9

TEST NUMBER: P926900

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1283.8	1329.1	1286.1	194.8	202.6
115°	1455.7	1498.7	1562.2	389.9	207.7
117.5°	1605.2	1655.7	1699.0	1336.7	673.4
120°	1772.3	1810.2	1855.9	1886.2	1544.4
122.5°	1913.9	1954.5	2005.3	2020.3	2023.1
125°	2058.2	2091.3	2139.4	2157.1	2164.6
127.5°	2189.9	2225.3	2263.5	2288.8	2291.2
130°	2314.0	2354.6	2382.3	2410.3	2407.9
132.5°	2440.6	2473.7	2501.4	2524.2	2521.8
135°	2547.1	2587.6	2610.2	2635.8	2630.6
137.5°	2658.3	2688.7	2714.2	2739.5	2731.9
140°	2767.2	2787.5	2815.2	2838.1	2825.4
142.5°	2858.5	2876.2	2909.0	2929.2	2916.6
145°	2954.7	2952.0	2995.0	3012.8	3000.2
147.5°	3038.1	3030.5	3073.5	3086.1	3076.2
150°	3119.2	3101.5	3142.0	3157.1	3144.5
152.5°	3187.4	3167.3	3205.2	3220.5	3202.8
155°	3253.3	3230.7	3261.0	3276.1	3256.0
157.5°	3306.5	3286.3	3309.2	3326.9	3306.5
160°	3352.2	3336.8	3352.2	3367.2	3349.5
162.5°	3392.4	3377.4	3390.1	3407.8	3385.0
165°	3428.0	3412.9	3420.4	3438.1	3420.4
167.5°	3455.9	3440.6	3448.4	3466.1	3443.3
170°	3478.8	3463.4	3468.5	3486.3	3463.4
172.5°	3493.8	3478.8	3483.9	3501.6	3478.8
175°	3506.4	3488.7	3493.8	3511.6	3486.3
177.5°	3511.6	3493.8	3496.5	3514.2	3491.4
180°	3498.9	3498.9	3498.9	3498.9	3498.9

TEST NUMBER: P926900

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.89	5.57	6.02	6.70	8.27	4.46	5.14	5.59	6.27	7.84
	3H	6.54	7.15	7.68	8.28	9.87	6.06	6.68	7.21	7.81	9.40
	4H	7.12	7.70	8.27	8.83	10.42	6.64	7.23	7.80	8.36	9.95
	6H	7.51	8.04	8.67	9.18	10.78	7.03	7.57	8.19	8.71	10.31
	8H	7.61	8.12	8.77	9.27	10.86	7.13	7.64	8.30	8.80	10.39
	12H	7.65	8.14	8.82	9.28	10.90	7.17	7.65	8.34	8.80	10.42
4H	2H	5.33	5.91	6.49	7.05	8.64	4.99	5.57	6.15	6.70	8.29
	3H	7.18	7.67	8.35	8.83	10.43	6.79	7.27	7.95	8.43	10.04
	4H	7.89	8.34	9.06	9.48	11.11	7.48	7.93	8.65	9.08	10.70
	6H	8.39	8.78	9.57	9.95	11.56	7.99	8.37	9.16	9.54	11.15
	8H	8.54	8.90	9.71	10.06	11.69	8.13	8.49	9.30	9.65	11.28
	12H	8.61	8.93	9.79	10.10	11.74	8.18	8.51	9.37	9.68	11.31
8H	4H	8.07	8.43	9.24	9.59	11.22	7.71	8.07	8.88	9.23	10.86
	6H	8.70	8.99	9.89	10.20	11.82	8.33	8.63	9.52	9.83	11.46
	8H	8.92	9.17	10.11	10.36	12.00	8.55	8.80	9.74	9.99	11.63
	12H	9.04	9.27	10.24	10.45	12.12	8.66	8.88	9.86	10.06	11.74
12H	4H	8.05	8.37	9.24	9.55	11.18	7.70	8.02	8.88	9.19	10.83
	6H	8.73	8.98	9.92	10.17	11.81	8.37	8.63	9.57	9.81	11.46
	8H	8.96	9.19	10.16	10.37	12.04	8.60	8.83	9.80	10.01	11.69

END OF REPORT