

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926921

Luminaire Tested: DFN2DIP-HX4F0-050D070US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926921
REPORT IS A COMBINATION OF REPORTS P899356 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D070US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9844.5 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926921

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926921

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1448	1448	1448
5°	1451	1425	1434
10°	1436	1398	1388
15°	1417	1352	1316
20°	1391	1288	1227
25°	1364	1217	1142
30°	1328	1144	1033
35°	1293	1065	938
40°	1257	984	829
45°	1216	893	730
50°	1173	802	633
55°	1128	705	540
60°	1076	603	445
65°	1017	500	401
70°	944	403	363
75°	854	356	330
80°	722	299	286
85°	505	200	216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1574 cd/sqm

TEST NUMBER: P926921

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	1.9
10°-20°	501.1	5.1
20°-30°	703.5	7.1
30°-40°	766.9	7.8
40°-50°	704.9	7.2
50°-60°	553.6	5.6
60°-70°	360.3	3.7
70°-80°	185.5	1.9
80°-90°	53.3	0.5
90°-100°	129.1	1.3
100°-110°	410.2	4.2
110°-120°	702.0	7.1
120°-130°	923.3	9.4
130°-140°	1036.4	10.5
140°-150°	1016.3	10.3
150°-160°	852.5	8.7
160°-170°	565.4	5.7
170°-180°	197.6	2.0
0°-30°	1387.2	14.1
0°-40°	2154.1	21.9
0°-60°	3412.5	34.7
0°-90°	4011.6	40.7
90°-120°	1241.4	12.6
90°-150°	4217.4	42.8
90°-180°	5833.0	59.3
0°-180°	9844.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1852	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1184	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	2	23	62	58	60	10
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	704	715	712	710	704	697
125°	1025	1040	1035	1030	1028	916
135°	1325	1345	1349	1347	1342	1024
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2086	2076	198
180°	2086	2086	2086	2086	2086	

TEST NUMBER: P926921

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.7	1947.7	1947.7	1947.7	1947.7
2.5°	1956.4	1947.7	1928.3	1946.0	1942.4
5°	1947.7	1938.9	1915.9	1931.7	1926.6
7.5°	1931.7	1921.3	1896.6	1903.6	1894.7
10°	1910.6	1898.3	1863.1	1857.8	1847.2
12.5°	1884.2	1868.4	1820.7	1810.3	1790.8
15°	1852.5	1833.1	1773.2	1739.8	1722.1
17.5°	1815.4	1787.3	1713.2	1674.4	1646.2
20°	1773.2	1737.9	1649.8	1605.8	1566.9
22.5°	1727.4	1686.8	1584.5	1524.7	1498.3
25°	1681.5	1625.1	1508.8	1436.6	1410.0
27.5°	1626.9	1566.9	1438.3	1355.4	1314.9
30°	1568.8	1501.7	1360.7	1270.9	1223.2
32.5°	1512.3	1431.2	1286.8	1181.0	1136.8
35°	1448.9	1359.0	1203.9	1092.8	1054.0
37.5°	1387.2	1290.2	1126.4	1004.6	960.7
40°	1322.0	1216.3	1045.1	920.1	874.3
42.5°	1255.0	1142.2	964.2	833.6	789.7
45°	1184.5	1066.3	881.3	756.1	713.8
47.5°	1117.5	992.5	802.1	676.8	638.1
50°	1043.5	918.4	724.5	602.7	565.9
52.5°	971.2	838.9	650.4	534.1	500.7
55°	900.7	763.1	572.8	467.1	433.6
57.5°	828.5	687.5	504.1	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.8	241.5
67.5°	537.6	394.8	246.8	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.3
75°	324.3	200.8	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.5	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.0	459.2
110°	537.2	547.3	547.3	547.3	542.2

TEST NUMBER: P926921

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.2	630.3	625.3	621.5
115°	704.5	714.6	711.5	709.6	704.5
117.5°	786.9	800.7	792.0	786.9	781.9
120°	869.9	883.8	869.9	869.9	864.3
122.5°	945.4	963.0	954.3	949.2	945.4
125°	1024.7	1040.4	1035.4	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.4	1197.1	1194.0	1190.2	1183.2
132.5°	1255.6	1273.2	1274.4	1265.7	1260.6
135°	1325.4	1344.9	1348.7	1346.7	1341.7
137.5°	1403.4	1419.1	1422.2	1421.0	1413.5
140°	1472.0	1487.7	1496.5	1496.5	1489.6
142.5°	1542.4	1558.1	1563.1	1565.0	1558.1
145°	1609.1	1621.7	1631.8	1633.6	1626.8
147.5°	1668.9	1684.6	1692.2	1695.3	1688.4
150°	1730.5	1741.2	1748.1	1753.8	1748.1
152.5°	1785.2	1795.9	1804.7	1811.7	1804.7
155°	1839.9	1844.9	1850.7	1859.5	1853.8
157.5°	1887.2	1890.9	1894.0	1906.7	1897.8
160°	1929.3	1933.1	1935.0	1945.6	1938.1
162.5°	1968.3	1968.3	1970.2	1982.1	1973.3
165°	2001.6	1999.7	1999.7	2012.3	2003.5
167.5°	2031.8	2026.2	2026.2	2038.7	2030.0
170°	2054.5	2049.5	2047.6	2060.1	2049.5
172.5°	2070.2	2065.1	2063.2	2075.9	2065.1
175°	2082.7	2077.7	2074.0	2086.5	2075.9
177.5°	2089.7	2084.6	2080.9	2091.6	2080.9
180°	2086.5	2086.5	2086.5	2086.5	2086.5

TEST NUMBER: P926921

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.50	8.26	8.54	9.30	10.70	3.48	4.24	4.52	5.28	6.68
	3H	9.18	9.86	10.23	10.91	12.32	4.66	5.34	5.71	6.39	7.81
	4H	9.78	10.43	10.84	11.48	12.90	5.11	5.75	6.17	6.81	8.23
	6H	10.20	10.79	11.27	11.85	13.29	5.43	6.02	6.50	7.08	8.52
	8H	10.33	10.89	11.40	11.96	13.39	5.52	6.08	6.59	7.15	8.59
	12H	10.39	10.92	11.46	11.99	13.44	5.56	6.10	6.64	7.16	8.62
4H	2H	7.51	8.16	8.58	9.21	10.64	4.06	4.71	5.13	5.76	7.19
	3H	9.34	9.87	10.41	10.95	12.39	5.41	5.94	6.48	7.02	8.46
	4H	10.03	10.52	11.11	11.59	13.05	5.96	6.45	7.04	7.52	8.98
	6H	10.54	10.96	11.63	12.05	13.51	6.37	6.79	7.46	7.89	9.34
	8H	10.71	11.11	11.80	12.19	13.66	6.50	6.89	7.59	7.98	9.45
	12H	10.81	11.16	11.91	12.26	13.74	6.57	6.92	7.67	8.02	9.49
8H	4H	9.99	10.38	11.08	11.47	12.94	6.23	6.62	7.32	7.71	9.18
	6H	10.56	10.88	11.67	12.01	13.47	6.75	7.07	7.86	8.20	9.67
	8H	10.77	11.06	11.89	12.17	13.65	6.94	7.23	8.06	8.34	9.82
	12H	10.91	11.16	12.03	12.26	13.79	7.06	7.31	8.18	8.41	9.94
12H	4H	9.94	10.29	11.04	11.39	12.87	6.23	6.59	7.34	7.69	9.16
	6H	10.53	10.81	11.65	11.92	13.41	6.80	7.08	7.92	8.19	9.68
	8H	10.75	11.00	11.87	12.10	13.63	7.01	7.26	8.13	8.36	9.89

END OF REPORT