

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926922

Luminaire Tested: DFN2DIP-HX4F0-050D070US830-RLLONL

Issue Date: 12/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P926922  
REPORT IS A COMBINATION OF REPORTS P900876 AND P896187  
Test Lab: INNOVATION CENTER  
Issue Date: 12/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-050D070US830-RLONL  
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10537.2 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 95.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9957  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P926922  
CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P926922

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				38
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	40	40	39	33				33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28				28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				24
4	73	63	55	50	66	57	51	46	47	42	39	38	34	32	29	27	25	21				21
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19				19
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20	16				16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	18	15				15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13				13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12				12
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11				11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1448	1448	1448
5°	1451	1425	1434
10°	1436	1398	1388
15°	1417	1352	1316
20°	1391	1288	1227
25°	1364	1217	1142
30°	1328	1144	1033
35°	1293	1065	938
40°	1257	984	829
45°	1216	893	730
50°	1173	802	633
55°	1128	705	540
60°	1076	603	445
65°	1017	500	401
70°	944	403	363
75°	854	356	330
80°	722	299	286
85°	505	200	216

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1216 cd/sqm



TEST NUMBER: P926922

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.5	1.7
10°-20°	501.1	4.8
20°-30°	703.5	6.7
30°-40°	766.9	7.3
40°-50°	704.9	6.7
50°-60°	553.6	5.3
60°-70°	360.3	3.4
70°-80°	185.5	1.8
80°-90°	51.3	0.5
90°-100°	73.4	0.7
100°-110°	273.7	2.6
110°-120°	725.9	6.9
120°-130°	1203.9	11.4
130°-140°	1278.9	12.1
140°-150°	1188.6	11.3
150°-160°	955.6	9.1
160°-170°	615.7	5.8
170°-180°	211.9	2.0
0°-30°	1387.2	13.2
0°-40°	2154.1	20.4
0°-60°	3412.5	32.4
0°-90°	4009.6	38.1
90°-120°	1073.0	10.2
90°-150°	4744.3	45.0
90°-180°	6528.0	62.0
0°-180°	10537.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1852	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1184	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	2	19	32	40	43	10
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1361	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2181	2172	2177	2188	2177	616
175°	2231	2220	2223	2235	2219	212
180°	2227	2227	2227	2227	2227	



TEST NUMBER: P926922

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1947.7	1947.7	1947.7	1947.7	1947.7
2.5°	1956.4	1947.7	1928.3	1946.0	1942.4
5°	1947.7	1938.9	1915.9	1931.7	1926.6
7.5°	1931.7	1921.3	1896.6	1903.6	1894.7
10°	1910.6	1898.3	1863.1	1857.8	1847.2
12.5°	1884.2	1868.4	1820.7	1810.3	1790.8
15°	1852.5	1833.1	1773.2	1739.8	1722.1
17.5°	1815.4	1787.3	1713.2	1674.4	1646.2
20°	1773.2	1737.9	1649.8	1605.8	1566.9
22.5°	1727.4	1686.8	1584.5	1524.7	1498.3
25°	1681.5	1625.1	1508.8	1436.6	1410.0
27.5°	1626.9	1566.9	1438.3	1355.4	1314.9
30°	1568.8	1501.7	1360.7	1270.9	1223.2
32.5°	1512.3	1431.2	1286.8	1181.0	1136.8
35°	1448.9	1359.0	1203.9	1092.8	1054.0
37.5°	1387.2	1290.2	1126.4	1004.6	960.7
40°	1322.0	1216.3	1045.1	920.1	874.3
42.5°	1255.0	1142.2	964.2	833.6	789.7
45°	1184.5	1066.3	881.3	756.1	713.8
47.5°	1117.5	992.5	802.1	676.8	638.1
50°	1043.5	918.4	724.5	602.7	565.9
52.5°	971.2	838.9	650.4	534.1	500.7
55°	900.7	763.1	572.8	467.1	433.6
57.5°	828.5	687.5	504.1	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.8	241.5
67.5°	537.6	394.8	246.8	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.3
75°	324.3	200.8	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	1.5	19.3	32.1	40.3	43.4
92.5°	40.3	33.8	38.6	41.9	43.4
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.1	644.4	101.6	119.2	125.7
110°	713.8	747.5	282.0	120.9	127.2



TEST NUMBER: P926922

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.7	994.1	248.2	132.2
117.5°	1021.5	1053.6	1081.1	850.6	428.6
120°	1127.8	1151.9	1181.0	1200.4	982.8
122.5°	1217.9	1243.7	1276.1	1285.7	1287.4
125°	1309.8	1330.8	1361.4	1372.8	1377.5
127.5°	1393.6	1416.1	1440.4	1456.5	1458.0
130°	1472.6	1498.4	1516.0	1533.8	1532.3
132.5°	1553.1	1574.2	1591.8	1606.3	1604.8
135°	1620.8	1646.6	1661.1	1677.3	1674.1
137.5°	1691.6	1711.0	1727.2	1743.3	1738.5
140°	1760.9	1773.9	1791.5	1806.0	1798.0
142.5°	1819.0	1830.3	1851.2	1864.0	1856.0
145°	1880.3	1878.6	1905.9	1917.2	1909.2
147.5°	1933.3	1928.5	1955.9	1963.9	1957.6
150°	1984.9	1973.7	1999.5	2009.0	2001.0
152.5°	2028.4	2015.5	2039.7	2049.4	2038.2
155°	2070.3	2055.9	2075.2	2084.8	2072.0
157.5°	2104.1	2091.3	2105.8	2117.1	2104.1
160°	2133.3	2123.5	2133.3	2142.8	2131.5
162.5°	2158.9	2149.3	2157.3	2168.6	2154.1
165°	2181.4	2171.9	2176.6	2187.9	2176.6
167.5°	2199.2	2189.4	2194.4	2205.7	2191.2
170°	2213.7	2204.0	2207.2	2218.6	2204.0
172.5°	2223.4	2213.7	2217.0	2228.3	2213.7
175°	2231.4	2220.1	2223.4	2234.6	2218.6
177.5°	2234.6	2223.4	2225.1	2236.4	2221.8
180°	2226.6	2226.6	2226.6	2226.6	2226.6



TEST NUMBER: P926922  
 CATALOG NUMBER: DFN2DIP-HX4F0-050D070US830-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.21	7.95	8.27	9.01	10.44	3.18	3.92	4.24	4.98	6.41
	3H	8.88	9.54	9.95	10.61	12.06	4.36	5.03	5.43	6.09	7.55
	4H	9.48	10.11	10.56	11.18	12.64	4.81	5.44	5.89	6.51	7.97
	6H	9.90	10.48	10.99	11.55	13.02	5.13	5.71	6.22	6.78	8.25
	8H	10.03	10.57	11.12	11.66	13.13	5.22	5.77	6.31	6.86	8.32
	12H	10.08	10.61	11.18	11.69	13.18	5.26	5.78	6.36	6.86	8.35
4H	2H	7.21	7.84	8.30	8.91	10.37	3.76	4.39	4.85	5.46	6.92
	3H	9.04	9.56	10.13	10.65	12.13	5.11	5.63	6.20	6.73	8.20
	4H	9.73	10.20	10.82	11.29	12.78	5.65	6.13	6.75	7.22	8.71
	6H	10.24	10.65	11.34	11.76	13.24	6.07	6.48	7.18	7.59	9.08
	8H	10.41	10.79	11.52	11.90	13.40	6.20	6.58	7.31	7.68	9.19
	12H	10.50	10.85	11.63	11.96	13.47	6.26	6.61	7.38	7.72	9.23
8H	4H	9.69	10.07	10.79	11.17	12.67	5.93	6.31	7.03	7.41	8.92
	6H	10.25	10.57	11.38	11.71	13.21	6.45	6.76	7.57	7.91	9.41
	8H	10.47	10.74	11.60	11.87	13.39	6.64	6.91	7.77	8.04	9.56
	12H	10.60	10.85	11.74	11.97	13.52	6.76	7.00	7.89	8.12	9.68
12H	4H	9.64	9.98	10.76	11.10	12.60	5.93	6.28	7.05	7.39	8.90
	6H	10.23	10.50	11.36	11.63	13.15	6.50	6.77	7.63	7.90	9.42
	8H	10.44	10.69	11.58	11.81	13.36	6.70	6.95	7.84	8.07	9.62