

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926938

Luminaire Tested: DFN2DIP-HX4F0-050D110US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926938
REPORT IS A COMBINATION OF REPORTS P900948 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D110US830-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14269.5 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 130.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926938

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US830-RLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926938

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	48	63	55	49	44	43	39	35	33	30	28	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	24	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1448	1448	1448
5°	1451	1425	1434
10°	1436	1398	1388
15°	1417	1352	1316
20°	1391	1288	1227
25°	1364	1217	1142
30°	1328	1144	1033
35°	1293	1065	938
40°	1257	984	829
45°	1216	893	730
50°	1173	802	633
55°	1128	705	540
60°	1076	603	445
65°	1017	500	401
70°	944	403	363
75°	854	356	330
80°	722	299	286
85°	505	200	216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1796 cd/sqm

TEST NUMBER: P926938

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US830-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	1.3
10°-20°	501.1	3.5
20°-30°	703.5	4.9
30°-40°	766.9	5.4
40°-50°	704.9	4.9
50°-60°	553.6	3.9
60°-70°	360.3	2.5
70°-80°	185.5	1.3
80°-90°	53.5	0.4
90°-100°	115.4	0.8
100°-110°	430.1	3.0
110°-120°	1140.7	8.0
120°-130°	1891.9	13.3
130°-140°	2009.6	14.1
140°-150°	1867.7	13.1
150°-160°	1501.6	10.5
160°-170°	967.6	6.8
170°-180°	333.0	2.3
0°-30°	1387.2	9.7
0°-40°	2154.1	15.1
0°-60°	3412.5	23.9
0°-90°	4011.8	28.1
90°-120°	1686.2	11.8
90°-150°	7455.4	52.2
90°-180°	10258.0	71.9
0°-180°	14269.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1852	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1184	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	2	30	50	63	68	13
95°	164	81	99	112	109	195
105°	770	846	155	182	192	822
115°	1456	1499	1562	390	208	1433
125°	2058	2091	2139	2157	2165	1836
135°	2547	2588	2610	2636	2631	1968
145°	2955	2952	2995	3013	3000	1848
155°	3253	3231	3261	3276	3256	1499
165°	3428	3413	3420	3438	3420	968
175°	3506	3489	3494	3512	3486	334
180°	3499	3499	3499	3499	3499	

TEST NUMBER: P926938

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US830-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.7	1947.7	1947.7	1947.7	1947.7
2.5°	1956.4	1947.7	1928.3	1946.0	1942.4
5°	1947.7	1938.9	1915.9	1931.7	1926.6
7.5°	1931.7	1921.3	1896.6	1903.6	1894.7
10°	1910.6	1898.3	1863.1	1857.8	1847.2
12.5°	1884.2	1868.4	1820.7	1810.3	1790.8
15°	1852.5	1833.1	1773.2	1739.8	1722.1
17.5°	1815.4	1787.3	1713.2	1674.4	1646.2
20°	1773.2	1737.9	1649.8	1605.8	1566.9
22.5°	1727.4	1686.8	1584.5	1524.7	1498.3
25°	1681.5	1625.1	1508.8	1436.6	1410.0
27.5°	1626.9	1566.9	1438.3	1355.4	1314.9
30°	1568.8	1501.7	1360.7	1270.9	1223.2
32.5°	1512.3	1431.2	1286.8	1181.0	1136.8
35°	1448.9	1359.0	1203.9	1092.8	1054.0
37.5°	1387.2	1290.2	1126.4	1004.6	960.7
40°	1322.0	1216.3	1045.1	920.1	874.3
42.5°	1255.0	1142.2	964.2	833.6	789.7
45°	1184.5	1066.3	881.3	756.1	713.8
47.5°	1117.5	992.5	802.1	676.8	638.1
50°	1043.5	918.4	724.5	602.7	565.9
52.5°	971.2	838.9	650.4	534.1	500.7
55°	900.7	763.1	572.8	467.1	433.6
57.5°	828.5	687.5	504.1	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.8	241.5
67.5°	537.6	394.8	246.8	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.3
75°	324.3	200.8	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	2.5	30.3	50.5	63.4	68.2
92.5°	63.4	53.3	60.7	65.9	68.2
95°	164.5	80.9	98.6	111.5	108.9
97.5°	296.1	88.7	128.9	136.8	139.2
100°	448.3	101.3	144.3	164.5	169.6
102.5°	615.1	610.3	149.4	177.1	184.9
105°	769.6	845.7	154.6	182.2	192.5
107.5°	949.5	1012.5	159.7	187.3	197.5
110°	1121.7	1174.6	443.2	190.0	199.9

TEST NUMBER: P926938

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1283.8	1329.1	1286.1	194.8	202.6
115°	1455.7	1498.7	1562.2	389.9	207.7
117.5°	1605.2	1655.7	1699.0	1336.7	673.4
120°	1772.3	1810.2	1855.9	1886.2	1544.4
122.5°	1913.9	1954.5	2005.3	2020.3	2023.1
125°	2058.2	2091.3	2139.4	2157.1	2164.6
127.5°	2189.9	2225.3	2263.5	2288.8	2291.2
130°	2314.0	2354.6	2382.3	2410.3	2407.9
132.5°	2440.6	2473.7	2501.4	2524.2	2521.8
135°	2547.1	2587.6	2610.2	2635.8	2630.6
137.5°	2658.3	2688.7	2714.2	2739.5	2731.9
140°	2767.2	2787.5	2815.2	2838.1	2825.4
142.5°	2858.5	2876.2	2909.0	2929.2	2916.6
145°	2954.7	2952.0	2995.0	3012.8	3000.2
147.5°	3038.1	3030.5	3073.5	3086.1	3076.2
150°	3119.2	3101.5	3142.0	3157.1	3144.5
152.5°	3187.4	3167.3	3205.2	3220.5	3202.8
155°	3253.3	3230.7	3261.0	3276.1	3256.0
157.5°	3306.5	3286.3	3309.2	3326.9	3306.5
160°	3352.2	3336.8	3352.2	3367.2	3349.5
162.5°	3392.4	3377.4	3390.1	3407.8	3385.0
165°	3428.0	3412.9	3420.4	3438.1	3420.4
167.5°	3455.9	3440.6	3448.4	3466.1	3443.3
170°	3478.8	3463.4	3468.5	3486.3	3463.4
172.5°	3493.8	3478.8	3483.9	3501.6	3478.8
175°	3506.4	3488.7	3493.8	3511.6	3486.3
177.5°	3511.6	3493.8	3496.5	3514.2	3491.4
180°	3498.9	3498.9	3498.9	3498.9	3498.9

TEST NUMBER: P926938

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.94	6.62	7.07	7.73	9.29	1.91	2.59	3.04	3.71	5.26
	3H	7.60	8.21	8.74	9.34	10.91	3.09	3.70	4.23	4.82	6.39
	4H	8.21	8.78	9.35	9.91	11.48	3.53	4.11	4.68	5.24	6.81
	6H	8.62	9.15	9.78	10.28	11.87	3.85	4.38	5.00	5.51	7.09
	8H	8.74	9.25	9.90	10.39	11.97	3.94	4.44	5.09	5.58	7.16
	12H	8.80	9.28	9.96	10.42	12.02	3.98	4.45	5.14	5.59	7.19
4H	2H	5.94	6.51	7.09	7.64	9.22	2.49	3.06	3.64	4.19	5.77
	3H	7.75	8.23	8.91	9.39	10.97	3.83	4.31	4.98	5.46	7.05
	4H	8.44	8.88	9.60	10.02	11.63	4.37	4.81	5.53	5.95	7.56
	6H	8.95	9.32	10.11	10.49	12.09	4.78	5.16	5.95	6.32	7.92
	8H	9.12	9.47	10.29	10.63	12.24	4.91	5.26	6.07	6.42	8.03
	12H	9.21	9.53	10.39	10.70	12.31	4.97	5.29	6.15	6.45	8.07
8H	4H	8.40	8.75	9.56	9.90	11.52	4.64	4.99	5.80	6.15	7.76
	6H	8.96	9.25	10.14	10.45	12.06	5.15	5.44	6.34	6.64	8.25
	8H	9.18	9.43	10.37	10.60	12.24	5.35	5.60	6.54	6.77	8.41
	12H	9.31	9.53	10.50	10.70	12.37	5.46	5.68	6.65	6.86	8.52
12H	4H	8.34	8.66	9.52	9.83	11.45	4.64	4.96	5.82	6.12	7.74
	6H	8.93	9.19	10.12	10.36	11.99	5.20	5.46	6.39	6.63	8.26
	8H	9.15	9.37	10.34	10.54	12.21	5.41	5.63	6.60	6.80	8.47

END OF REPORT