

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926963

Luminaire Tested: DFN2DIP-HX4F0-060D090US830-FLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926963
REPORT IS A COMBINATION OF REPORTS P899393 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D090US830-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13105.5 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 122.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926963

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926963

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	30	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1636	1636	1636
5°	1639	1613	1624
10°	1626	1592	1602
15°	1602	1566	1568
20°	1570	1530	1533
25°	1538	1486	1492
30°	1498	1446	1441
35°	1460	1398	1386
40°	1413	1350	1334
45°	1366	1302	1281
50°	1315	1251	1219
55°	1262	1193	1163
60°	1201	1123	1098
65°	1136	1051	1021
70°	1052	964	939
75°	935	859	863
80°	796	725	718
85°	577	494	478

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2022 cd/sqm

TEST NUMBER: P926963

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.1	1.6
10°-20°	582.7	4.4
20°-30°	856.3	6.5
30°-40°	994.6	7.6
40°-50°	993.4	7.6
50°-60°	866.2	6.6
60°-70°	640.3	4.9
70°-80°	362.3	2.8
80°-90°	103.2	0.8
90°-100°	166.0	1.3
100°-110°	527.5	4.0
110°-120°	902.7	6.9
120°-130°	1187.1	9.1
130°-140°	1332.5	10.2
140°-150°	1306.6	10.0
150°-160°	1096.1	8.4
160°-170°	726.9	5.5
170°-180°	254.1	1.9
0°-30°	1646.2	12.6
0°-40°	2640.7	20.1
0°-60°	4500.3	34.3
0°-90°	5606.1	42.8
90°-120°	1596.1	12.2
90°-150°	5422.3	41.4
90°-180°	7499.0	57.2
0°-180°	13105.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2200	2200	2200	2200	2200	
5°	2200	2192	2169	2186	2182	209
15°	2095	2082	2054	2063	2052	590
25°	1896	1879	1843	1847	1843	872
35°	1636	1614	1581	1568	1557	1021
45°	1331	1316	1284	1261	1253	1027
55°	1007	994	969	944	933	901
65°	679	666	645	626	616	672
75°	355	351	340	328	332	379
85°	87	85	83	76	74	97
90°	2	29	79	74	77	13
95°	118	141	145	145	141	131
105°	487	493	498	502	502	514
115°	906	919	915	912	906	896
125°	1318	1338	1331	1324	1322	1177
135°	1704	1729	1734	1732	1725	1317
145°	2069	2085	2098	2100	2092	1293
155°	2366	2372	2379	2391	2384	1089
165°	2574	2571	2571	2587	2576	726
175°	2678	2671	2666	2683	2669	254
180°	2683	2683	2683	2683	2683	

TEST NUMBER: P926963

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2200.4	2200.4	2200.4	2200.4	2200.4
2.5°	2213.2	2202.6	2179.2	2200.4	2196.3
5°	2200.4	2192.1	2168.7	2185.6	2181.5
7.5°	2185.6	2173.0	2149.7	2166.7	2162.5
10°	2162.5	2147.7	2122.2	2139.1	2132.8
12.5°	2130.6	2118.0	2092.6	2103.2	2098.9
15°	2094.6	2082.1	2054.5	2063.0	2052.5
17.5°	2050.2	2037.7	2010.1	2020.5	2010.1
20°	2001.5	1989.0	1959.3	1965.6	1957.3
22.5°	1953.0	1933.9	1906.3	1906.3	1902.1
25°	1895.7	1879.0	1843.0	1847.0	1843.0
27.5°	1832.2	1817.4	1790.0	1783.8	1773.2
30°	1769.0	1751.8	1720.3	1713.9	1705.4
32.5°	1701.1	1688.6	1654.7	1641.8	1633.4
35°	1635.6	1614.5	1580.6	1567.8	1557.2
37.5°	1561.5	1542.4	1508.6	1493.7	1483.1
40°	1485.4	1468.3	1434.5	1415.6	1407.1
42.5°	1411.3	1394.2	1360.6	1339.3	1326.7
45°	1331.0	1316.1	1284.3	1261.2	1252.6
47.5°	1252.6	1237.8	1203.9	1180.6	1167.9
50°	1170.0	1159.5	1129.9	1100.2	1089.6
52.5°	1089.6	1074.8	1047.4	1024.1	1009.3
55°	1007.2	994.4	969.1	943.7	933.2
57.5°	924.7	914.1	886.5	861.2	852.6
60°	842.0	833.7	804.1	780.8	774.5
62.5°	761.6	746.8	725.7	704.6	696.1
65°	679.3	666.5	645.4	626.3	615.7
67.5°	594.6	583.9	565.0	550.2	541.7
70°	516.3	507.8	488.7	473.9	465.6
72.5°	435.9	427.4	416.9	402.1	395.8
75°	355.3	351.4	340.5	328.0	332.2
77.5°	283.5	275.0	270.7	264.5	258.2
80°	211.7	209.4	205.2	198.9	194.6
82.5°	143.9	143.9	141.8	133.4	133.4
85°	86.6	84.6	82.6	76.1	74.1
87.5°	38.2	33.9	29.6	23.4	21.1
90°	2.5	29.1	79.3	74.4	76.8
92.5°	50.1	68.0	70.4	72.8	72.8
95°	118.1	140.7	144.8	144.8	140.7
97.5°	196.5	217.5	226.5	226.5	226.5
100°	287.1	305.7	312.2	312.2	309.8
102.5°	382.6	396.3	405.2	407.6	405.2
105°	486.9	493.3	498.2	502.3	502.3
107.5°	590.4	600.1	600.1	601.7	590.4
110°	690.7	703.7	703.7	703.7	697.2

TEST NUMBER: P926963

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	799.1	812.8	810.4	804.0	799.1
115°	905.8	918.7	914.7	912.3	905.8
117.5°	1011.8	1029.6	1018.3	1011.8	1005.3
120°	1118.6	1136.3	1118.6	1118.6	1111.2
122.5°	1215.5	1238.3	1226.9	1220.4	1215.5
125°	1317.5	1337.7	1331.3	1323.9	1321.6
127.5°	1417.0	1442.0	1433.2	1423.5	1417.0
130°	1510.0	1539.1	1535.0	1530.1	1521.3
132.5°	1614.3	1636.9	1638.5	1627.2	1620.8
135°	1704.0	1729.1	1734.0	1731.6	1725.2
137.5°	1804.3	1824.6	1828.6	1827.0	1817.3
140°	1892.5	1912.7	1924.0	1924.0	1915.2
142.5°	1983.1	2003.3	2009.8	2012.2	2003.3
145°	2068.9	2085.0	2097.9	2100.4	2091.5
147.5°	2145.7	2165.9	2175.6	2179.6	2170.8
150°	2225.0	2238.7	2247.6	2254.8	2247.6
152.5°	2295.3	2309.0	2320.3	2329.3	2320.3
155°	2365.7	2372.1	2379.4	2390.7	2383.5
157.5°	2426.3	2431.2	2435.2	2451.3	2440.0
160°	2480.5	2485.4	2487.8	2501.5	2491.8
162.5°	2530.6	2530.6	2533.1	2548.4	2537.1
165°	2573.5	2571.0	2571.0	2587.3	2575.9
167.5°	2612.3	2605.1	2605.1	2621.2	2609.9
170°	2641.5	2634.9	2632.6	2648.7	2634.9
172.5°	2661.6	2655.2	2652.8	2669.0	2655.2
175°	2677.8	2671.3	2666.5	2682.7	2669.0
177.5°	2686.7	2680.3	2675.4	2689.1	2675.4
180°	2682.7	2682.7	2682.7	2682.7	2682.7

TEST NUMBER: P926963

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.27	9.07	9.29	10.10	11.47	7.84	8.64	8.86	9.67	11.04
	3H	9.93	10.65	10.96	11.68	13.07	9.46	10.18	10.49	11.21	12.60
	4H	10.52	11.20	11.56	12.23	13.63	10.04	10.72	11.08	11.76	13.16
	6H	10.91	11.54	11.96	12.58	13.99	10.44	11.06	11.49	12.11	13.52
	8H	11.02	11.61	12.07	12.67	14.08	10.54	11.14	11.60	12.20	13.60
	12H	11.06	11.63	12.12	12.68	14.11	10.58	11.15	11.64	12.20	13.63
4H	2H	8.73	9.41	9.78	10.45	11.84	8.39	9.06	9.43	10.10	11.50
	3H	10.59	11.16	11.64	12.22	13.63	10.20	10.77	11.25	11.83	13.24
	4H	11.30	11.82	12.36	12.88	14.31	10.90	11.42	11.96	12.47	13.91
	6H	11.82	12.26	12.89	13.34	14.77	11.41	11.85	12.48	12.93	14.36
	8H	11.96	12.38	13.03	13.45	14.90	11.55	11.97	12.62	13.04	14.49
	12H	12.04	12.41	13.12	13.50	14.95	11.61	11.99	12.70	13.08	14.53
8H	4H	11.50	11.91	12.57	12.99	14.43	11.14	11.55	12.21	12.62	14.07
	6H	12.13	12.47	13.22	13.58	15.03	11.76	12.11	12.86	13.22	14.66
	8H	12.35	12.65	13.45	13.75	15.21	11.98	12.28	13.08	13.38	14.84
	12H	12.48	12.74	13.58	13.83	15.33	12.09	12.36	13.20	13.45	14.95
12H	4H	11.48	11.86	12.57	12.94	14.39	11.13	11.50	12.21	12.59	14.04
	6H	12.16	12.46	13.26	13.56	15.02	11.80	12.11	12.90	13.20	14.66
	8H	12.40	12.66	13.50	13.75	15.25	12.04	12.30	13.14	13.40	14.90