

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902615

Luminaire Tested: DFN2DIP-HX3F0-070D030US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902615
REPORT IS A COMBINATION OF REPORTS P900729 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D030US830-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9331.2 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 92.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902615

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902615

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24
9	53	40	33	27	50	39	32	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2974	2974	2974
5°	2977	2930	2950
10°	2952	2889	2909
15°	2907	2839	2845
20°	2847	2771	2779
25°	2787	2690	2704
30°	2713	2614	2608
35°	2642	2525	2507
40°	2555	2436	2411
45°	2468	2346	2312
50°	2374	2251	2199
55°	2274	2141	2093
60°	2162	2011	1973
65°	2039	1877	1831
70°	1882	1712	1677
75°	1666	1515	1533
80°	1404	1264	1263
85°	996	836	819

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2468 cd/sqm

TEST NUMBER: P902615

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.6	2.6
10°-20°	679.9	7.3
20°-30°	999.1	10.7
30°-40°	1160.4	12.4
40°-50°	1159.0	12.4
50°-60°	1010.6	10.8
60°-70°	747.1	8.0
70°-80°	422.7	4.5
80°-90°	113.2	1.2
90°-100°	31.5	0.3
100°-110°	117.3	1.3
110°-120°	311.1	3.3
120°-130°	516.0	5.5
130°-140°	548.1	5.9
140°-150°	509.4	5.5
150°-160°	409.6	4.4
160°-170°	263.9	2.8
170°-180°	90.8	1.0
0°-30°	1920.6	20.6
0°-40°	3081.0	33.0
0°-60°	5250.6	56.3
0°-90°	6533.5	70.0
90°-120°	459.9	4.9
90°-150°	2033.4	21.8
90°-180°	2798.0	30.0
0°-180°	9331.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2567	2567	2567	2567	2567	
5°	2567	2558	2530	2550	2545	244
15°	2444	2429	2397	2407	2395	688
25°	2212	2192	2150	2155	2150	1018
35°	1908	1884	1844	1829	1817	1192
45°	1553	1536	1498	1471	1461	1198
55°	1175	1160	1131	1101	1089	1051
65°	793	778	753	731	718	784
75°	415	410	397	383	388	443
85°	101	99	96	89	86	113
90°	1	8	14	17	19	9
95°	45	22	27	30	30	53
105°	210	231	42	50	52	224
115°	397	409	426	106	57	391
125°	561	570	584	588	590	501
135°	695	706	712	719	718	537
145°	806	805	817	822	818	504
155°	887	881	889	894	888	409
165°	935	931	933	938	933	264
175°	956	952	953	958	951	91
180°	954	954	954	954	954	

TEST NUMBER: P902615

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2567.2	2567.2	2567.2	2567.2	2567.2
2.5°	2582.2	2569.8	2542.6	2567.2	2562.5
5°	2567.2	2557.6	2530.3	2550.0	2545.2
7.5°	2550.0	2535.3	2508.0	2528.0	2523.0
10°	2523.0	2505.7	2476.1	2495.8	2488.4
12.5°	2485.8	2471.2	2441.6	2453.8	2448.8
15°	2443.9	2429.2	2397.0	2407.0	2394.6
17.5°	2392.0	2377.4	2345.1	2357.5	2345.1
20°	2335.1	2320.5	2285.9	2293.3	2283.6
22.5°	2278.6	2256.4	2224.1	2224.1	2219.1
25°	2211.9	2192.2	2150.3	2155.0	2150.3
27.5°	2137.7	2120.4	2088.5	2081.1	2068.8
30°	2063.9	2043.9	2007.0	1999.7	1989.7
32.5°	1984.7	1970.1	1930.5	1915.6	1905.6
35°	1908.3	1883.7	1844.1	1829.2	1816.8
37.5°	1821.8	1799.6	1760.0	1742.8	1730.4
40°	1733.1	1713.2	1673.6	1651.6	1641.6
42.5°	1646.6	1626.7	1587.4	1562.5	1547.8
45°	1552.8	1535.6	1498.4	1471.4	1461.4
47.5°	1461.4	1444.2	1404.6	1377.3	1362.7
50°	1365.1	1352.7	1318.1	1283.6	1271.3
52.5°	1271.3	1254.1	1222.1	1194.9	1177.5
55°	1175.2	1160.3	1130.7	1101.1	1088.7
57.5°	1078.8	1066.5	1034.3	1004.7	994.8
60°	982.4	972.7	938.2	911.0	903.6
62.5°	888.6	871.4	846.8	822.2	812.2
65°	792.6	777.6	753.0	730.8	718.4
67.5°	693.8	681.3	659.2	642.0	632.0
70°	602.4	592.5	570.1	552.9	543.2
72.5°	508.6	498.7	486.4	469.1	461.8
75°	414.6	409.9	397.3	382.7	387.7
77.5°	330.8	320.8	315.8	308.5	301.2
80°	246.9	244.4	239.4	232.1	227.1
82.5°	167.9	167.9	165.5	155.6	155.6
85°	101.1	98.8	96.4	88.8	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	0.7	8.3	13.8	17.3	18.6
92.5°	17.3	14.5	16.6	18.0	18.6
95°	44.9	22.1	26.9	30.4	29.7
97.5°	80.8	24.2	35.2	37.3	38.0
100°	122.2	27.6	39.4	44.9	46.3
102.5°	167.8	166.5	40.7	48.3	50.4
105°	209.9	230.6	42.1	49.7	52.5
107.5°	258.9	276.2	43.5	51.1	53.9
110°	305.9	320.4	120.8	51.8	54.6

TEST NUMBER: P902615

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.2	362.5	350.8	53.2	55.2
115°	397.0	408.8	426.0	106.3	56.6
117.5°	437.8	451.6	463.4	364.6	183.7
120°	483.3	493.7	506.1	514.4	421.2
122.5°	522.0	533.1	547.0	551.0	551.8
125°	561.4	570.3	583.5	588.3	590.4
127.5°	597.3	606.9	617.4	624.2	624.9
130°	631.1	642.2	649.8	657.3	656.8
132.5°	665.6	674.7	682.2	688.4	687.8
135°	694.7	705.8	711.9	718.9	717.5
137.5°	725.0	733.3	740.3	747.2	745.1
140°	754.7	760.3	767.8	774.0	770.6
142.5°	779.7	784.5	793.4	798.9	795.5
145°	805.9	805.1	816.9	821.7	818.2
147.5°	828.6	826.5	838.3	841.7	839.0
150°	850.7	845.9	857.0	861.0	857.6
152.5°	869.3	863.8	874.2	878.4	873.5
155°	887.3	881.2	889.4	893.5	888.1
157.5°	901.8	896.4	902.6	907.4	901.8
160°	914.3	910.1	914.3	918.4	913.5
162.5°	925.3	921.1	924.6	929.4	923.2
165°	934.9	930.9	932.9	937.7	932.9
167.5°	942.5	938.4	940.5	945.4	939.1
170°	948.8	944.6	946.0	950.8	944.6
172.5°	952.9	948.8	950.2	955.0	948.8
175°	956.3	951.5	952.9	957.7	950.8
177.5°	957.7	952.9	953.7	958.5	952.3
180°	954.3	954.3	954.3	954.3	954.3

TEST NUMBER: P902615

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US830-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.69	13.76	13.45	14.55	15.50	12.26	13.33	13.02	14.12	15.07
	3H	14.35	15.32	15.13	16.12	17.10	13.89	14.85	14.66	15.65	16.63
	4H	14.95	15.86	15.74	16.66	17.66	14.48	15.39	15.27	16.19	17.19
	6H	15.35	16.19	16.16	17.01	18.01	14.88	15.72	15.69	16.54	17.54
	8H	15.46	16.26	16.28	17.09	18.10	14.99	15.79	15.81	16.62	17.63
	12H	15.51	16.28	16.33	17.10	18.14	15.04	15.80	15.86	16.63	17.66
4H	2H	13.17	14.08	13.97	14.89	15.88	12.83	13.74	13.63	14.54	15.54
	3H	15.05	15.81	15.86	16.65	17.66	14.66	15.42	15.47	16.26	17.27
	4H	15.76	16.46	16.59	17.29	18.33	15.36	16.05	16.19	16.89	17.93
	6H	16.28	16.88	17.12	17.74	18.79	15.88	16.48	16.72	17.34	18.38
	8H	16.43	16.99	17.28	17.85	18.91	16.03	16.59	16.87	17.44	18.50
	12H	16.51	17.02	17.38	17.90	18.96	16.10	16.60	16.96	17.48	18.54
8H	4H	15.97	16.53	16.82	17.39	18.45	15.62	16.18	16.46	17.03	18.09
	6H	16.60	17.07	17.48	17.97	19.02	16.25	16.71	17.12	17.61	18.67
	8H	16.82	17.23	17.71	18.13	19.20	16.46	16.87	17.34	17.76	18.84
	12H	16.96	17.32	17.85	18.21	19.33	16.58	16.94	17.47	17.83	18.96
12H	4H	15.97	16.47	16.83	17.35	18.41	15.62	16.12	16.48	17.00	18.06
	6H	16.63	17.05	17.52	17.94	19.02	16.29	16.70	17.17	17.59	18.67
	8H	16.88	17.24	17.77	18.13	19.26	16.53	16.89	17.41	17.78	18.90