

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926992

Luminaire Tested: DFN2DIP-HX4F0-070D070US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926992
REPORT IS A COMBINATION OF REPORTS P900879 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D070US830-FLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13063.0 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 118.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926992
CATALOG NUMBER: DFN2DIP-HX4F0-070D070US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P926992
 CATALOG NUMBER: DFN2DIP-HX4F0-070D070US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1909	1909	1909
5°	1912	1882	1895
10°	1897	1857	1869
15°	1869	1827	1829
20°	1831	1785	1789
25°	1794	1734	1741
30°	1747	1687	1681
35°	1703	1631	1617
40°	1648	1575	1557
45°	1594	1519	1494
50°	1534	1460	1423
55°	1472	1392	1357
60°	1402	1311	1281
65°	1325	1227	1192
70°	1227	1124	1096
75°	1091	1002	1008
80°	928	846	838
85°	674	577	557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1594 cd/sqm



TEST NUMBER: P926992

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.6	1.8
10°-20°	679.8	5.2
20°-30°	999.1	7.6
30°-40°	1160.4	8.9
40°-50°	1158.9	8.9
50°-60°	1010.5	7.7
60°-70°	747.0	5.7
70°-80°	422.7	3.2
80°-90°	115.5	0.9
90°-100°	73.4	0.6
100°-110°	273.7	2.1
110°-120°	725.9	5.6
120°-130°	1203.9	9.2
130°-140°	1278.9	9.8
140°-150°	1188.6	9.1
150°-160°	955.6	7.3
160°-170°	615.7	4.7
170°-180°	211.9	1.6
0°-30°	1920.5	14.7
0°-40°	3080.9	23.6
0°-60°	5250.3	40.2
0°-90°	6535.5	50.0
90°-120°	1073.0	8.2
90°-150°	4744.3	36.3
90°-180°	6528.0	50.0
0°-180°	13063.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2567	2567	2567	2567	2567	
5°	2567	2558	2530	2550	2545	244
15°	2444	2429	2397	2407	2394	688
25°	2212	2192	2150	2155	2150	1018
35°	1908	1884	1844	1829	1817	1192
45°	1553	1536	1498	1471	1461	1198
55°	1175	1160	1131	1101	1089	1051
65°	792	778	753	731	718	784
75°	415	410	397	383	388	443
85°	101	99	96	89	86	113
90°	2	19	32	40	43	12
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1361	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2181	2172	2177	2188	2177	616
175°	2231	2220	2223	2235	2219	212
180°	2227	2227	2227	2227	2227	



TEST NUMBER: P926992

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2567.1	2567.1	2567.1	2567.1	2567.1
2.5°	2582.1	2569.7	2542.5	2567.1	2562.4
5°	2567.1	2557.5	2530.2	2549.8	2545.1
7.5°	2549.8	2535.1	2507.9	2527.9	2522.9
10°	2522.9	2505.5	2475.9	2495.6	2488.3
12.5°	2485.7	2471.0	2441.5	2453.7	2448.7
15°	2443.8	2429.1	2396.9	2406.9	2394.5
17.5°	2391.9	2377.3	2345.0	2357.4	2345.0
20°	2335.0	2320.4	2285.8	2293.2	2283.5
22.5°	2278.5	2256.3	2224.0	2224.0	2219.0
25°	2211.8	2192.1	2150.2	2154.9	2150.2
27.5°	2137.6	2120.3	2088.4	2081.0	2068.7
30°	2063.8	2043.8	2007.0	1999.6	1989.6
32.5°	1984.6	1970.0	1930.4	1915.5	1905.5
35°	1908.2	1883.6	1844.0	1829.1	1816.8
37.5°	1821.8	1799.5	1759.9	1742.7	1730.3
40°	1733.0	1713.1	1673.5	1651.5	1641.6
42.5°	1646.5	1626.7	1587.4	1562.5	1547.8
45°	1552.8	1535.5	1498.3	1471.3	1461.3
47.5°	1461.3	1444.1	1404.5	1377.3	1362.7
50°	1365.0	1352.7	1318.1	1283.6	1271.2
52.5°	1271.2	1254.0	1222.0	1194.8	1177.5
55°	1175.1	1160.2	1130.6	1101.0	1088.7
57.5°	1078.8	1066.4	1034.2	1004.6	994.7
60°	982.4	972.7	938.2	910.9	903.6
62.5°	888.6	871.3	846.7	822.1	812.2
65°	792.5	777.6	753.0	730.7	718.4
67.5°	693.8	681.2	659.2	641.9	631.9
70°	602.4	592.5	570.1	552.9	543.2
72.5°	508.6	498.7	486.3	469.1	461.7
75°	414.6	409.9	397.3	382.7	387.7
77.5°	330.8	320.8	315.8	308.5	301.2
80°	246.9	244.4	239.4	232.0	227.0
82.5°	167.9	167.9	165.5	155.6	155.6
85°	101.1	98.8	96.4	88.8	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	1.5	19.3	32.1	40.3	43.4
92.5°	40.3	33.8	38.6	41.9	43.4
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.1	644.4	101.6	119.2	125.7
110°	713.8	747.5	282.0	120.9	127.2



TEST NUMBER: P926992

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.7	994.1	248.2	132.2
117.5°	1021.5	1053.6	1081.1	850.6	428.6
120°	1127.8	1151.9	1181.0	1200.4	982.8
122.5°	1217.9	1243.7	1276.1	1285.7	1287.4
125°	1309.8	1330.8	1361.4	1372.8	1377.5
127.5°	1393.6	1416.1	1440.4	1456.5	1458.0
130°	1472.6	1498.4	1516.0	1533.8	1532.3
132.5°	1553.1	1574.2	1591.8	1606.3	1604.8
135°	1620.8	1646.6	1661.1	1677.3	1674.1
137.5°	1691.6	1711.0	1727.2	1743.3	1738.5
140°	1760.9	1773.9	1791.5	1806.0	1798.0
142.5°	1819.0	1830.3	1851.2	1864.0	1856.0
145°	1880.3	1878.6	1905.9	1917.2	1909.2
147.5°	1933.3	1928.5	1955.9	1963.9	1957.6
150°	1984.9	1973.7	1999.5	2009.0	2001.0
152.5°	2028.4	2015.5	2039.7	2049.4	2038.2
155°	2070.3	2055.9	2075.2	2084.8	2072.0
157.5°	2104.1	2091.3	2105.8	2117.1	2104.1
160°	2133.3	2123.5	2133.3	2142.8	2131.5
162.5°	2158.9	2149.3	2157.3	2168.6	2154.1
165°	2181.4	2171.9	2176.6	2187.9	2176.6
167.5°	2199.2	2189.4	2194.4	2205.7	2191.2
170°	2213.7	2204.0	2207.2	2218.6	2204.0
172.5°	2223.4	2213.7	2217.0	2228.3	2213.7
175°	2231.4	2220.1	2223.4	2234.6	2218.6
177.5°	2234.6	2223.4	2225.1	2236.4	2221.8
180°	2226.6	2226.6	2226.6	2226.6	2226.6



TEST NUMBER: P926992
 CATALOG NUMBER: DFN2DIP-HX4F0-070D070US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.52	10.38	10.48	11.36	12.63	9.09	9.95	10.05	10.92	12.19
	3H	11.18	11.96	12.15	12.94	14.23	10.71	11.48	11.68	12.46	13.76
	4H	11.77	12.50	12.75	13.49	14.79	11.30	12.03	12.28	13.01	14.32
	6H	12.17	12.85	13.16	13.84	15.15	11.70	12.37	12.69	13.36	14.67
	8H	12.28	12.92	13.28	13.93	15.24	11.80	12.44	12.80	13.45	14.76
	12H	12.33	12.94	13.33	13.94	15.27	11.84	12.45	12.85	13.46	14.79
4H	2H	9.98	10.72	10.97	11.70	13.00	9.64	10.37	10.63	11.36	12.66
	3H	11.85	12.46	12.85	13.48	14.79	11.46	12.07	12.46	13.08	14.40
	4H	12.57	13.13	13.57	14.13	15.47	12.16	12.72	13.17	13.73	15.07
	6H	13.08	13.56	14.10	14.59	15.93	12.67	13.15	13.69	14.18	15.52
	8H	13.23	13.68	14.25	14.71	16.06	12.82	13.27	13.84	14.29	15.64
	12H	13.31	13.71	14.34	14.75	16.11	12.88	13.29	13.92	14.33	15.69
8H	4H	12.76	13.21	13.78	14.24	15.59	12.40	12.85	13.42	13.88	15.23
	6H	13.40	13.77	14.44	14.83	16.18	13.03	13.40	14.08	14.47	15.82
	8H	13.62	13.95	14.67	15.00	16.36	13.25	13.58	14.30	14.63	15.99
	12H	13.75	14.04	14.80	15.08	16.49	13.37	13.65	14.42	14.70	16.11
12H	4H	12.75	13.16	13.79	14.19	15.55	12.40	12.80	13.43	13.84	15.20
	6H	13.43	13.75	14.48	14.81	16.17	13.07	13.40	14.12	14.45	15.82
	8H	13.67	13.96	14.72	15.00	16.41	13.31	13.60	14.37	14.65	16.06