

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926997

Luminaire Tested: DFN2DIP-HX4F0-070D080US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926997
REPORT IS A COMBINATION OF REPORTS P899378 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D080US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12280.7 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926997
CATALOG NUMBER: DFN2DIP-HX4F0-070D080US830-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P926997

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46	46	46	46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45	39	39	39	39
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38	34	34	34	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29	29	29	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25	25	25	25
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20	18	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15	15	15	15
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2027	2027	2027
5°	2031	1996	2008
10°	2011	1957	1943
15°	1983	1892	1842
20°	1947	1803	1718
25°	1910	1703	1599
30°	1859	1601	1447
35°	1810	1491	1313
40°	1760	1377	1160
45°	1702	1251	1022
50°	1642	1123	887
55°	1579	987	757
60°	1507	844	623
65°	1423	700	561
70°	1322	564	508
75°	1195	498	462
80°	1011	419	401
85°	707	280	302

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1798 cd/sqm



TEST NUMBER: P926997

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.6	2.1
10°-20°	701.5	5.7
20°-30°	984.9	8.0
30°-40°	1073.7	8.7
40°-50°	986.8	8.0
50°-60°	775.0	6.3
60°-70°	504.4	4.1
70°-80°	259.7	2.1
80°-90°	73.0	0.6
90°-100°	147.6	1.2
100°-110°	468.9	3.8
110°-120°	802.3	6.5
120°-130°	1055.2	8.6
130°-140°	1184.4	9.6
140°-150°	1161.5	9.5
150°-160°	974.3	7.9
160°-170°	646.1	5.3
170°-180°	225.8	1.8
0°-30°	1942.0	15.8
0°-40°	3015.7	24.6
0°-60°	4777.5	38.9
0°-90°	5614.6	45.7
90°-120°	1418.8	11.6
90°-150°	4819.9	39.2
90°-180°	6666.0	54.3
0°-180°	12280.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2727	2727	2727	2727	2727	
5°	2727	2714	2682	2704	2697	259
15°	2594	2566	2482	2436	2411	731
25°	2354	2275	2112	2011	1974	1083
35°	2028	1902	1686	1530	1476	1270
45°	1658	1493	1234	1058	999	1281
55°	1261	1068	802	654	607	1127
65°	851	651	429	346	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	122
90°	2	26	70	66	68	12
95°	105	125	129	129	125	117
105°	433	438	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1533	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2285	2285	2300	2290	645
175°	2380	2374	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	



TEST NUMBER: P926997

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.7	2726.7	2726.7	2726.7	2726.7
2.5°	2739.0	2726.7	2699.5	2724.4	2719.4
5°	2726.7	2714.4	2682.3	2704.5	2697.2
7.5°	2704.5	2689.8	2655.3	2664.9	2652.7
10°	2674.9	2657.7	2608.4	2600.8	2586.1
12.5°	2638.0	2615.7	2549.0	2534.3	2507.0
15°	2593.5	2566.2	2482.5	2435.6	2411.0
17.5°	2541.6	2502.1	2398.5	2344.2	2304.7
20°	2482.5	2433.0	2309.7	2248.1	2193.7
22.5°	2418.4	2361.5	2218.3	2134.5	2097.6
25°	2354.2	2275.1	2112.2	2011.2	1974.1
27.5°	2277.7	2193.7	2013.6	1897.6	1840.8
30°	2196.3	2102.3	1904.9	1779.3	1712.5
32.5°	2117.2	2003.7	1801.5	1653.3	1591.5
35°	2028.4	1902.5	1685.6	1530.1	1475.6
37.5°	1942.1	1806.2	1576.9	1406.4	1344.9
40°	1850.7	1702.8	1463.2	1288.1	1223.9
42.5°	1757.0	1599.1	1349.8	1167.1	1105.6
45°	1658.3	1492.8	1233.9	1058.5	999.3
47.5°	1564.6	1389.4	1122.9	947.5	893.3
50°	1460.9	1285.8	1014.2	843.8	792.3
52.5°	1359.6	1174.4	910.5	747.7	700.8
55°	1260.9	1068.4	801.9	654.0	607.2
57.5°	1159.8	962.4	705.8	567.6	528.1
60°	1056.2	858.7	604.5	478.9	439.3
62.5°	955.0	757.7	518.1	399.8	380.1
65°	851.4	651.4	429.4	345.6	338.0
67.5°	752.7	552.7	345.6	303.4	296.1
70°	649.0	456.5	286.1	261.5	251.6
72.5°	550.3	367.6	239.3	219.7	214.7
75°	454.0	281.1	197.4	180.1	177.8
77.5°	357.9	199.7	155.5	145.5	140.6
80°	268.9	143.2	118.4	108.7	108.7
82.5°	187.5	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.5	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	613.9	625.4	625.4	625.4	619.7



TEST NUMBER: P926997

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.5	720.4	714.6	710.3
115°	805.2	816.7	813.1	810.9	805.2
117.5°	899.3	915.2	905.1	899.3	893.6
120°	994.2	1010.1	994.2	994.2	987.7
122.5°	1080.5	1100.7	1090.6	1084.8	1080.5
125°	1171.1	1189.1	1183.3	1176.8	1174.7
127.5°	1259.6	1281.8	1273.9	1265.3	1259.6
130°	1342.2	1368.0	1364.5	1360.2	1352.3
132.5°	1435.0	1455.0	1456.5	1446.5	1440.7
135°	1514.7	1537.0	1541.4	1539.2	1533.4
137.5°	1603.9	1621.9	1625.4	1624.0	1615.4
140°	1682.3	1700.2	1710.3	1710.3	1702.3
142.5°	1762.8	1780.8	1786.5	1788.7	1780.8
145°	1839.0	1853.3	1864.8	1867.0	1859.1
147.5°	1907.2	1925.2	1933.8	1937.5	1929.6
150°	1977.7	1989.9	1997.8	2004.3	1997.8
152.5°	2040.2	2052.5	2062.6	2070.5	2062.6
155°	2102.8	2108.6	2115.1	2125.1	2118.6
157.5°	2156.7	2161.1	2164.6	2179.0	2169.0
160°	2204.9	2209.2	2211.4	2223.5	2215.0
162.5°	2249.5	2249.5	2251.6	2265.3	2255.2
165°	2287.5	2285.4	2285.4	2299.8	2289.7
167.5°	2322.0	2315.6	2315.6	2330.0	2319.9
170°	2348.0	2342.2	2340.0	2354.5	2342.2
172.5°	2366.0	2360.2	2358.0	2372.4	2360.2
175°	2380.3	2374.5	2370.2	2384.6	2372.4
177.5°	2388.2	2382.5	2378.1	2390.4	2378.1
180°	2384.6	2384.6	2384.6	2384.6	2384.6



TEST NUMBER: P926997
 CATALOG NUMBER: DFN2DIP-HX4F0-070D080US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.19	9.98	10.19	10.99	12.32	5.16	5.96	6.16	6.96	8.30
	3H	10.86	11.58	11.87	12.59	13.95	6.35	7.06	7.36	8.08	9.43
	4H	11.47	12.15	12.49	13.16	14.53	6.80	7.47	7.82	8.49	9.85
	6H	11.89	12.51	12.92	13.53	14.91	7.12	7.74	8.15	8.76	10.14
	8H	12.02	12.61	13.06	13.65	15.02	7.21	7.80	8.25	8.84	10.21
	12H	12.08	12.64	13.12	13.67	15.07	7.25	7.81	8.30	8.85	10.24
4H	2H	9.20	9.88	10.23	10.89	12.26	5.75	6.43	6.78	7.45	8.81
	3H	11.03	11.59	12.07	12.64	14.01	7.10	7.66	8.14	8.71	10.08
	4H	11.72	12.23	12.77	13.27	14.67	7.65	8.16	8.69	9.20	10.60
	6H	12.24	12.68	13.29	13.74	15.13	8.07	8.51	9.12	9.57	10.97
	8H	12.41	12.82	13.47	13.88	15.28	8.20	8.61	9.25	9.66	11.07
	12H	12.50	12.88	13.58	13.94	15.36	8.26	8.63	9.34	9.70	11.12
8H	4H	11.69	12.10	12.74	13.15	14.56	7.93	8.34	8.98	9.39	10.80
	6H	12.25	12.59	13.33	13.69	15.09	8.45	8.79	9.53	9.88	11.29
	8H	12.47	12.77	13.55	13.85	15.27	8.64	8.94	9.72	10.02	11.44
	12H	12.61	12.87	13.70	13.94	15.41	8.76	9.02	9.85	10.10	11.56
12H	4H	11.64	12.01	12.71	13.08	14.49	7.93	8.30	9.00	9.37	10.78
	6H	12.23	12.53	13.31	13.61	15.03	8.50	8.80	9.58	9.88	11.30
	8H	12.45	12.71	13.54	13.79	15.25	8.71	8.97	9.80	10.04	11.51