

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927022

Luminaire Tested: DFN2DIP-HX4F0-080D050US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927022
REPORT IS A COMBINATION OF REPORTS P900846 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D050US830-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11074.4 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 114.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927022
CATALOG NUMBER: DFN2DIP-HX4F0-080D050US830-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P927022

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58	58	58	58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50	50	50	50
2	92	84	79	74	85	79	74	69	69	65	62	59	57	54	51	49	47	43	43	43	43
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	43	41	37	37	37	37
4	77	67	59	53	72	62	56	50	55	49	45	48	44	40	41	38	35	32	32	32	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28	28	28	28
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28	25	25	25	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25	22	22	22	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23	20	20	20	20
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	27	23	20	18	18	18	18
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19	17	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2317	2317	2317
5°	2321	2281	2295
10°	2298	2236	2221
15°	2267	2162	2105
20°	2225	2061	1964
25°	2182	1947	1827
30°	2125	1830	1653
35°	2069	1704	1501
40°	2012	1574	1326
45°	1945	1430	1168
50°	1877	1284	1013
55°	1805	1128	865
60°	1722	965	712
65°	1627	799	641
70°	1511	645	580
75°	1366	569	528
80°	1156	478	458
85°	808	320	345

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1945 cd/sqm



TEST NUMBER: P927022

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	2.6
10°-20°	801.8	7.2
20°-30°	1125.7	10.2
30°-40°	1227.0	11.1
40°-50°	1127.8	10.2
50°-60°	885.7	8.0
60°-70°	576.5	5.2
70°-80°	296.8	2.7
80°-90°	78.5	0.7
90°-100°	52.5	0.5
100°-110°	195.5	1.8
110°-120°	518.5	4.7
120°-130°	860.0	7.8
130°-140°	913.5	8.2
140°-150°	849.0	7.7
150°-160°	682.6	6.2
160°-170°	439.8	4.0
170°-180°	151.4	1.4
0°-30°	2219.5	20.0
0°-40°	3446.5	31.1
0°-60°	5460.0	49.3
0°-90°	6411.8	57.9
90°-120°	766.4	6.9
90°-150°	3388.8	30.6
90°-180°	4663.0	42.1
0°-180°	11074.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3065	3091	3082	295
15°	2964	2933	2837	2784	2755	835
25°	2690	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	1	14	23	29	31	10
95°	75	37	45	51	50	89
105°	350	384	70	83	88	374
115°	662	681	710	177	94	651
125°	936	951	972	980	984	834
135°	1158	1176	1186	1198	1196	894
145°	1343	1342	1361	1370	1364	840
155°	1479	1468	1482	1489	1480	681
165°	1558	1551	1555	1563	1555	440
175°	1594	1586	1588	1596	1585	152
180°	1590	1590	1590	1590	1590	



TEST NUMBER: P927022

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.3	3116.3	3116.3	3116.3	3116.3
2.5°	3130.3	3116.3	3085.2	3113.5	3107.9
5°	3116.3	3102.2	3065.4	3090.8	3082.4
7.5°	3090.8	3074.1	3034.6	3045.7	3031.6
10°	3057.0	3037.3	2981.0	2972.4	2955.6
12.5°	3014.9	2989.4	2913.1	2896.3	2865.2
15°	2964.0	2932.9	2837.1	2783.6	2755.4
17.5°	2904.7	2859.5	2741.1	2679.2	2633.9
20°	2837.1	2780.6	2639.7	2569.3	2507.0
22.5°	2763.8	2698.8	2535.2	2439.5	2397.2
25°	2690.5	2600.2	2414.0	2298.6	2256.1
27.5°	2603.1	2507.0	2301.2	2168.7	2103.8
30°	2510.1	2402.6	2177.1	2033.4	1957.1
32.5°	2419.7	2289.9	2058.9	1889.5	1818.9
35°	2318.3	2174.3	1926.3	1748.6	1686.3
37.5°	2219.5	2064.3	1802.2	1607.3	1537.0
40°	2115.2	1946.1	1672.3	1472.1	1398.8
42.5°	2008.0	1827.6	1542.7	1333.9	1263.5
45°	1895.2	1706.1	1410.2	1209.7	1142.1
47.5°	1788.1	1587.9	1283.3	1082.8	1020.9
50°	1669.5	1469.5	1159.2	964.4	905.4
52.5°	1553.8	1342.2	1040.6	854.6	801.0
55°	1441.0	1221.1	916.5	747.4	693.9
57.5°	1325.5	1099.9	806.7	648.7	603.5
60°	1207.0	981.4	690.9	547.2	502.1
62.5°	1091.5	865.9	592.2	456.9	434.5
65°	973.0	744.4	490.7	395.0	386.2
67.5°	860.2	631.7	395.0	346.7	338.5
70°	741.7	521.9	327.0	298.9	287.6
72.5°	628.9	420.1	273.5	251.1	245.3
75°	518.8	321.4	225.6	205.8	203.2
77.5°	409.0	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.2	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	1.1	13.8	23.0	28.8	31.0
92.5°	28.8	24.2	27.6	30.0	31.0
95°	74.7	36.8	44.9	50.7	49.5
97.5°	134.6	40.3	58.6	62.2	63.2
100°	203.8	46.1	65.6	74.7	77.1
102.5°	279.6	277.4	68.0	80.5	84.1
105°	349.9	384.4	70.2	82.8	87.5
107.5°	431.6	460.2	72.6	85.1	89.8
110°	509.9	533.9	201.4	86.3	90.9



TEST NUMBER: P927022

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US830-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	583.5	604.1	584.6	88.6	92.1
115°	661.7	681.2	710.1	177.3	94.4
117.5°	729.6	752.6	772.3	607.5	306.1
120°	805.6	822.8	843.5	857.4	702.0
122.5°	869.9	888.4	911.5	918.4	919.6
125°	935.5	950.6	972.5	980.5	984.0
127.5°	995.4	1011.5	1028.9	1040.3	1041.5
130°	1051.8	1070.3	1082.8	1095.6	1094.5
132.5°	1109.4	1124.4	1136.9	1147.4	1146.3
135°	1157.8	1176.2	1186.4	1198.1	1195.7
137.5°	1208.3	1222.1	1233.7	1245.2	1241.8
140°	1257.8	1267.1	1279.6	1290.0	1284.3
142.5°	1299.3	1307.4	1322.3	1331.5	1325.7
145°	1343.1	1341.8	1361.3	1369.5	1363.7
147.5°	1381.0	1377.5	1397.1	1402.8	1398.3
150°	1417.8	1409.8	1428.2	1435.1	1429.3
152.5°	1448.8	1439.7	1456.9	1463.9	1455.8
155°	1478.8	1468.5	1482.3	1489.2	1480.0
157.5°	1502.9	1493.8	1504.1	1512.2	1502.9
160°	1523.7	1516.8	1523.7	1530.5	1522.5
162.5°	1542.0	1535.2	1540.9	1549.0	1538.6
165°	1558.1	1551.4	1554.7	1562.8	1554.7
167.5°	1570.9	1563.9	1567.5	1575.5	1565.1
170°	1581.2	1574.3	1576.6	1584.6	1574.3
172.5°	1588.1	1581.2	1583.6	1591.6	1581.2
175°	1593.9	1585.8	1588.1	1596.1	1584.6
177.5°	1596.1	1588.1	1589.3	1597.3	1587.0
180°	1590.4	1590.4	1590.4	1590.4	1590.4



TEST NUMBER: P927022
 CATALOG NUMBER: DFN2DIP-HX4F0-080D050US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.77	11.67	11.67	12.58	13.74	6.75	7.65	7.64	8.56	9.71
	3H	12.46	13.26	13.36	14.18	15.36	7.94	8.75	8.85	9.67	10.85
	4H	13.07	13.83	13.99	14.75	15.95	8.40	9.16	9.32	10.08	11.27
	6H	13.50	14.20	14.43	15.13	16.33	8.72	9.42	9.66	10.35	11.56
	8H	13.63	14.29	14.57	15.24	16.44	8.82	9.48	9.76	10.43	11.63
	12H	13.69	14.32	14.63	15.26	16.49	8.86	9.50	9.81	10.44	11.66
4H	2H	10.80	11.56	11.73	12.48	13.68	7.35	8.11	8.28	9.03	10.23
	3H	12.64	13.27	13.58	14.22	15.43	8.71	9.34	9.65	10.30	11.50
	4H	13.33	13.91	14.28	14.86	16.09	9.26	9.84	10.21	10.79	12.02
	6H	13.85	14.35	14.81	15.32	16.55	9.69	10.18	10.65	11.15	12.39
	8H	14.03	14.49	14.99	15.46	16.70	9.82	10.28	10.78	11.25	12.49
	12H	14.13	14.55	15.11	15.53	16.78	9.89	10.30	10.87	11.29	12.54
8H	4H	13.31	13.77	14.27	14.74	15.98	9.55	10.01	10.51	10.98	12.22
	6H	13.88	14.26	14.86	15.27	16.51	10.07	10.45	11.06	11.46	12.70
	8H	14.09	14.43	15.09	15.43	16.69	10.26	10.60	11.26	11.60	12.86
	12H	14.24	14.53	15.24	15.52	16.83	10.39	10.68	11.39	11.67	12.98
12H	4H	13.26	13.68	14.24	14.66	15.91	9.56	9.97	10.54	10.96	12.21
	6H	13.85	14.19	14.85	15.19	16.45	10.12	10.46	11.12	11.46	12.72
	8H	14.08	14.37	15.08	15.36	16.67	10.34	10.63	11.34	11.62	12.93