

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927032

Luminaire Tested: DFN2DIP-HX4F0-080D080US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927032
REPORT IS A COMBINATION OF REPORTS P900899 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D080US830-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14929.2 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 135
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927032

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927032

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2181	2181	2181
5°	2185	2151	2166
10°	2168	2123	2137
15°	2136	2088	2091
20°	2093	2039	2044
25°	2050	1982	1990
30°	1997	1928	1921
35°	1946	1864	1848
40°	1884	1800	1779
45°	1822	1736	1708
50°	1753	1668	1626
55°	1682	1591	1550
60°	1602	1498	1464
65°	1514	1402	1362
70°	1402	1285	1252
75°	1247	1145	1151
80°	1062	967	958
85°	771	659	637

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1822 cd/sqm

TEST NUMBER: P927032

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	1.8
10°-20°	776.9	5.2
20°-30°	1141.8	7.6
30°-40°	1326.1	8.9
40°-50°	1324.5	8.9
50°-60°	1154.9	7.7
60°-70°	853.7	5.7
70°-80°	483.0	3.2
80°-90°	132.0	0.9
90°-100°	83.9	0.6
100°-110°	312.8	2.1
110°-120°	829.6	5.6
120°-130°	1375.9	9.2
130°-140°	1461.6	9.8
140°-150°	1358.3	9.1
150°-160°	1092.1	7.3
160°-170°	703.7	4.7
170°-180°	242.2	1.6
0°-30°	2194.9	14.7
0°-40°	3521.0	23.6
0°-60°	6000.4	40.2
0°-90°	7469.1	50.0
90°-120°	1226.3	8.2
90°-150°	5422.1	36.3
90°-180°	7460.0	50.0
0°-180°	14929.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	278
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2457	2463	2457	1163
35°	2181	2153	2107	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	895
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	2	22	37	46	50	14
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2500	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	

TEST NUMBER: P927032

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2933.8	2933.8	2933.8	2933.8	2933.8
2.5°	2950.9	2936.8	2905.7	2933.8	2928.4
5°	2933.8	2922.8	2891.7	2914.1	2908.7
7.5°	2914.1	2897.3	2866.2	2889.0	2883.3
10°	2883.3	2863.5	2829.7	2852.1	2843.8
12.5°	2840.8	2824.0	2790.2	2804.2	2798.6
15°	2792.9	2776.1	2739.3	2750.7	2736.6
17.5°	2733.6	2716.9	2680.0	2694.1	2680.0
20°	2668.7	2651.9	2612.4	2620.8	2609.7
22.5°	2604.0	2578.6	2541.7	2541.7	2536.1
25°	2527.7	2505.3	2457.4	2462.8	2457.4
27.5°	2443.0	2423.3	2386.7	2378.3	2364.3
30°	2358.6	2335.8	2293.7	2285.3	2273.9
32.5°	2268.2	2251.4	2206.2	2189.1	2177.8
35°	2180.8	2152.7	2107.4	2090.4	2076.3
37.5°	2082.0	2056.5	2011.4	1991.6	1977.6
40°	1980.6	1957.8	1912.6	1887.5	1876.0
42.5°	1881.8	1859.0	1814.1	1785.7	1769.0
45°	1774.6	1754.8	1712.3	1681.5	1670.2
47.5°	1670.2	1650.4	1605.2	1574.1	1557.3
50°	1560.0	1546.0	1506.4	1466.9	1452.9
52.5°	1452.9	1433.1	1396.6	1365.5	1345.7
55°	1343.0	1325.9	1292.2	1258.3	1244.2
57.5°	1232.9	1218.8	1182.0	1148.2	1136.7
60°	1122.7	1111.7	1072.1	1041.0	1032.6
62.5°	1015.5	995.8	967.7	939.6	928.2
65°	905.7	888.7	860.5	835.1	821.0
67.5°	792.8	778.5	753.3	733.6	722.2
70°	688.4	677.0	651.6	631.9	620.7
72.5°	581.2	569.9	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.0	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.1	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.7	134.5
105°	559.8	615.1	112.3	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.8	854.3	322.3	138.2	145.4

TEST NUMBER: P927032

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	933.6	966.6	935.4	141.7	147.4
115°	1058.7	1090.0	1136.1	283.6	151.1
117.5°	1167.4	1204.1	1235.6	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.8	1123.2
122.5°	1391.9	1421.5	1458.4	1469.4	1471.3
125°	1496.9	1520.9	1555.9	1568.8	1574.3
127.5°	1592.6	1618.5	1646.3	1664.5	1666.3
130°	1682.9	1712.4	1732.6	1753.0	1751.2
132.5°	1775.0	1799.0	1819.2	1835.8	1834.0
135°	1852.4	1881.9	1898.3	1917.0	1913.2
137.5°	1933.4	1955.4	1974.0	1992.4	1986.9
140°	2012.4	2027.3	2047.5	2064.1	2054.8
142.5°	2079.0	2091.8	2115.6	2130.3	2121.1
145°	2148.9	2146.9	2178.2	2191.1	2181.9
147.5°	2209.5	2204.0	2235.2	2244.5	2237.2
150°	2268.5	2255.6	2285.1	2296.0	2286.9
152.5°	2318.2	2303.5	2331.0	2342.2	2329.3
155°	2366.1	2349.7	2371.7	2382.6	2368.0
157.5°	2404.7	2390.1	2406.7	2419.6	2404.7
160°	2438.0	2426.8	2438.0	2448.9	2436.0
162.5°	2467.3	2456.3	2465.5	2478.4	2461.8
165°	2493.1	2482.2	2487.6	2500.5	2487.6
167.5°	2513.4	2502.2	2507.9	2520.8	2504.2
170°	2530.0	2518.8	2522.6	2535.5	2518.8
172.5°	2541.0	2530.0	2533.7	2546.6	2530.0
175°	2550.1	2537.2	2541.0	2553.8	2535.5
177.5°	2553.8	2541.0	2542.9	2555.8	2539.2
180°	2544.7	2544.7	2544.7	2544.7	2544.7

TEST NUMBER: P927032

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US830-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.99	10.85	10.94	11.82	13.09	9.55	10.42	10.51	11.39	12.66
	3H	11.65	12.42	12.61	13.40	14.69	11.17	11.95	12.14	12.93	14.22
	4H	12.24	12.97	13.22	13.95	15.25	11.76	12.49	12.74	13.48	14.78
	6H	12.64	13.31	13.63	14.30	15.61	12.16	12.83	13.15	13.82	15.14
	8H	12.74	13.38	13.74	14.39	15.70	12.27	12.91	13.26	13.91	15.23
	12H	12.79	13.40	13.79	14.40	15.74	12.31	12.92	13.31	13.92	15.26
4H	2H	10.45	11.18	11.44	12.16	13.47	10.10	10.83	11.09	11.82	13.12
	3H	12.32	12.93	13.31	13.94	15.26	11.92	12.53	12.92	13.55	14.86
	4H	13.03	13.59	14.04	14.60	15.93	12.62	13.18	13.63	14.19	15.53
	6H	13.55	14.03	14.56	15.06	16.39	13.14	13.62	14.15	14.65	15.98
	8H	13.70	14.15	14.71	15.17	16.52	13.28	13.73	14.30	14.76	16.11
	12H	13.77	14.18	14.81	15.22	16.57	13.35	13.75	14.38	14.79	16.15
8H	4H	13.23	13.68	14.25	14.70	16.05	12.87	13.32	13.89	14.34	15.69
	6H	13.86	14.23	14.90	15.30	16.65	13.50	13.87	14.54	14.93	16.28
	8H	14.08	14.41	15.13	15.46	16.83	13.71	14.04	14.76	15.09	16.46
	12H	14.21	14.50	15.27	15.55	16.96	13.83	14.12	14.88	15.16	16.57
12H	4H	13.21	13.62	14.25	14.66	16.01	12.86	13.27	13.90	14.31	15.66
	6H	13.89	14.22	14.94	15.27	16.64	13.54	13.87	14.59	14.92	16.28
	8H	14.13	14.42	15.19	15.47	16.88	13.78	14.06	14.83	15.11	16.52