

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927044

Luminaire Tested: DFN2DIP-HX4F0-080D110US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927044
REPORT IS A COMBINATION OF REPORTS P900953 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D110US830-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17728.4 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 163.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927044

CATALOG NUMBER: DFN2DIP-HX4F0-080D110US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927044

CATALOG NUMBER: DFN2DIP-HX4F0-080D110US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	65	58	53	53	49	45	43	40	37	34	31	30
4	73	62	54	49	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2181	2181	2181
5°	2185	2151	2166
10°	2168	2123	2137
15°	2136	2088	2091
20°	2093	2039	2044
25°	2050	1982	1990
30°	1997	1928	1921
35°	1946	1864	1848
40°	1884	1800	1779
45°	1822	1736	1708
50°	1753	1668	1626
55°	1682	1591	1550
60°	1602	1498	1464
65°	1514	1402	1362
70°	1402	1285	1252
75°	1247	1145	1151
80°	1062	967	958
85°	771	659	637

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1822 cd/sqm

TEST NUMBER: P927044

CATALOG NUMBER: DFN2DIP-HX4F0-080D110US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	1.6
10°-20°	776.9	4.4
20°-30°	1141.8	6.4
30°-40°	1326.1	7.5
40°-50°	1324.5	7.5
50°-60°	1154.9	6.5
60°-70°	853.7	4.8
70°-80°	483.0	2.7
80°-90°	133.7	0.8
90°-100°	115.4	0.7
100°-110°	430.1	2.4
110°-120°	1140.7	6.4
120°-130°	1891.9	10.7
130°-140°	2009.6	11.3
140°-150°	1867.7	10.5
150°-160°	1501.6	8.5
160°-170°	967.6	5.5
170°-180°	333.0	1.9
0°-30°	2194.9	12.4
0°-40°	3521.0	19.9
0°-60°	6000.4	33.8
0°-90°	7470.8	42.1
90°-120°	1686.2	9.5
90°-150°	7455.4	42.1
90°-180°	10258.0	57.9
0°-180°	17728.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	278
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2457	2463	2457	1163
35°	2181	2153	2107	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	895
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	2	30	50	63	68	16
95°	164	81	99	112	109	195
105°	770	846	155	182	192	822
115°	1456	1499	1562	390	208	1433
125°	2058	2091	2139	2157	2165	1836
135°	2547	2588	2610	2636	2631	1968
145°	2955	2952	2995	3013	3000	1848
155°	3253	3231	3261	3276	3256	1499
165°	3428	3413	3420	3438	3420	968
175°	3506	3489	3494	3512	3486	334
180°	3499	3499	3499	3499	3499	

TEST NUMBER: P927044

CATALOG NUMBER: DFN2DIP-HX4F0-080D110US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2933.8	2933.8	2933.8	2933.8	2933.8
2.5°	2950.9	2936.8	2905.7	2933.8	2928.4
5°	2933.8	2922.8	2891.7	2914.1	2908.7
7.5°	2914.1	2897.3	2866.2	2889.0	2883.3
10°	2883.3	2863.5	2829.7	2852.1	2843.8
12.5°	2840.8	2824.0	2790.2	2804.2	2798.6
15°	2792.9	2776.1	2739.3	2750.7	2736.6
17.5°	2733.6	2716.9	2680.0	2694.1	2680.0
20°	2668.7	2651.9	2612.4	2620.8	2609.7
22.5°	2604.0	2578.6	2541.7	2541.7	2536.1
25°	2527.7	2505.3	2457.4	2462.8	2457.4
27.5°	2443.0	2423.3	2386.7	2378.3	2364.3
30°	2358.6	2335.8	2293.7	2285.3	2273.9
32.5°	2268.2	2251.4	2206.2	2189.1	2177.8
35°	2180.8	2152.7	2107.4	2090.4	2076.3
37.5°	2082.0	2056.5	2011.4	1991.6	1977.6
40°	1980.6	1957.8	1912.6	1887.5	1876.0
42.5°	1881.8	1859.0	1814.1	1785.7	1769.0
45°	1774.6	1754.8	1712.3	1681.5	1670.2
47.5°	1670.2	1650.4	1605.2	1574.1	1557.3
50°	1560.0	1546.0	1506.4	1466.9	1452.9
52.5°	1452.9	1433.1	1396.6	1365.5	1345.7
55°	1343.0	1325.9	1292.2	1258.3	1244.2
57.5°	1232.9	1218.8	1182.0	1148.2	1136.7
60°	1122.7	1111.7	1072.1	1041.0	1032.6
62.5°	1015.5	995.8	967.7	939.6	928.2
65°	905.7	888.7	860.5	835.1	821.0
67.5°	792.8	778.5	753.3	733.6	722.2
70°	688.4	677.0	651.6	631.9	620.7
72.5°	581.2	569.9	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.0	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	2.5	30.3	50.5	63.4	68.2
92.5°	63.4	53.3	60.7	65.9	68.2
95°	164.5	80.9	98.6	111.5	108.9
97.5°	296.1	88.7	128.9	136.8	139.2
100°	448.3	101.3	144.3	164.5	169.6
102.5°	615.1	610.3	149.4	177.1	184.9
105°	769.6	845.7	154.6	182.2	192.5
107.5°	949.5	1012.5	159.7	187.3	197.5
110°	1121.7	1174.6	443.2	190.0	199.9

TEST NUMBER: P927044

CATALOG NUMBER: DFN2DIP-HX4F0-080D110US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1283.8	1329.1	1286.1	194.8	202.6
115°	1455.7	1498.7	1562.2	389.9	207.7
117.5°	1605.2	1655.7	1699.0	1336.7	673.4
120°	1772.3	1810.2	1855.9	1886.2	1544.4
122.5°	1913.9	1954.5	2005.3	2020.3	2023.1
125°	2058.2	2091.3	2139.4	2157.1	2164.6
127.5°	2189.9	2225.3	2263.5	2288.8	2291.2
130°	2314.0	2354.6	2382.3	2410.3	2407.9
132.5°	2440.6	2473.7	2501.4	2524.2	2521.8
135°	2547.1	2587.6	2610.2	2635.8	2630.6
137.5°	2658.3	2688.7	2714.2	2739.5	2731.9
140°	2767.2	2787.5	2815.2	2838.1	2825.4
142.5°	2858.5	2876.2	2909.0	2929.2	2916.6
145°	2954.7	2952.0	2995.0	3012.8	3000.2
147.5°	3038.1	3030.5	3073.5	3086.1	3076.2
150°	3119.2	3101.5	3142.0	3157.1	3144.5
152.5°	3187.4	3167.3	3205.2	3220.5	3202.8
155°	3253.3	3230.7	3261.0	3276.1	3256.0
157.5°	3306.5	3286.3	3309.2	3326.9	3306.5
160°	3352.2	3336.8	3352.2	3367.2	3349.5
162.5°	3392.4	3377.4	3390.1	3407.8	3385.0
165°	3428.0	3412.9	3420.4	3438.1	3420.4
167.5°	3455.9	3440.6	3448.4	3466.1	3443.3
170°	3478.8	3463.4	3468.5	3486.3	3463.4
172.5°	3493.8	3478.8	3483.9	3501.6	3478.8
175°	3506.4	3488.7	3493.8	3511.6	3486.3
177.5°	3511.6	3493.8	3496.5	3514.2	3491.4
180°	3498.9	3498.9	3498.9	3498.9	3498.9

TEST NUMBER: P927044

CATALOG NUMBER: DFN2DIP-HX4F0-080D110US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.21	10.00	10.23	11.04	12.41	8.78	9.57	9.80	10.60	11.98
	3H	10.87	11.58	11.90	12.62	14.02	10.39	11.11	11.43	12.14	13.54
	4H	11.45	12.13	12.50	13.17	14.57	10.98	11.65	12.02	12.69	14.10
	6H	11.85	12.47	12.90	13.52	14.93	11.37	11.99	12.43	13.04	14.46
	8H	11.95	12.54	13.01	13.61	15.02	11.48	12.07	12.54	13.13	14.54
	12H	12.00	12.56	13.06	13.62	15.05	11.52	12.08	12.58	13.13	14.57
4H	2H	9.66	10.34	10.71	11.38	12.79	9.32	9.99	10.37	11.04	12.44
	3H	11.53	12.09	12.58	13.16	14.58	11.13	11.70	12.19	12.76	14.18
	4H	12.24	12.75	13.30	13.81	15.26	11.83	12.35	12.90	13.41	14.85
	6H	12.75	13.19	13.82	14.28	15.71	12.34	12.78	13.41	13.87	15.30
	8H	12.90	13.31	13.97	14.39	15.84	12.49	12.90	13.56	13.98	15.43
	12H	12.97	13.34	14.06	14.43	15.89	12.55	12.92	13.64	14.01	15.47
8H	4H	12.43	12.84	13.50	13.92	15.37	12.07	12.48	13.14	13.56	15.01
	6H	13.06	13.40	14.16	14.52	15.97	12.70	13.04	13.79	14.16	15.61
	8H	13.28	13.58	14.38	14.68	16.15	12.91	13.21	14.02	14.31	15.78
	12H	13.41	13.67	14.52	14.77	16.28	13.02	13.29	14.13	14.39	15.89
12H	4H	12.41	12.79	13.50	13.88	15.33	12.06	12.43	13.15	13.52	14.98
	6H	13.09	13.39	14.19	14.49	15.96	12.74	13.04	13.84	14.14	15.61
	8H	13.33	13.59	14.44	14.69	16.20	12.97	13.24	14.08	14.33	15.84

END OF REPORT