

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927062

Luminaire Tested: DFN2DIP-HX4F0-090D060US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927062
REPORT IS A COMBINATION OF REPORTS P900866 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D060US830-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12808.6 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 132.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927062
CATALOG NUMBER: DFN2DIP-HX4F0-090D060US830-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P927062
 CATALOG NUMBER: DFN2DIP-HX4F0-090D060US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53	49	49	49	49
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46	42	42	42	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31	27	27	27	27
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	24	24	24	24
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2607	2607	2607
5°	2611	2566	2582
10°	2586	2516	2498
15°	2550	2433	2368
20°	2503	2318	2209
25°	2455	2190	2055
30°	2391	2059	1860
35°	2328	1917	1689
40°	2263	1771	1492
45°	2188	1608	1314
50°	2111	1444	1140
55°	2031	1269	973
60°	1937	1086	801
65°	1830	899	721
70°	1700	726	653
75°	1537	640	594
80°	1300	538	516
85°	909	360	388

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2188 cd/sqm



TEST NUMBER: P927062

CATALOG NUMBER: DFN2DIP-HX4F0-090D060US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.6	2.6
10°-20°	902.0	7.0
20°-30°	1266.4	9.9
30°-40°	1380.4	10.8
40°-50°	1268.7	9.9
50°-60°	996.4	7.8
60°-70°	648.6	5.1
70°-80°	333.9	2.6
80°-90°	88.6	0.7
90°-100°	62.9	0.5
100°-110°	234.6	1.8
110°-120°	622.2	4.9
120°-130°	1031.9	8.1
130°-140°	1096.2	8.6
140°-150°	1018.8	8.0
150°-160°	819.1	6.4
160°-170°	527.8	4.1
170°-180°	181.7	1.4
0°-30°	2496.9	19.5
0°-40°	3877.3	30.3
0°-60°	6142.5	48.0
0°-90°	7213.5	56.3
90°-120°	919.7	7.2
90°-150°	4066.6	31.7
90°-180°	5595.0	43.7
0°-180°	12808.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3506	3506	3506	3506	3506	
5°	3506	3490	3449	3477	3468	332
15°	3334	3300	3192	3132	3100	940
25°	3027	2925	2716	2586	2538	1392
35°	2608	2446	2167	1967	1897	1632
45°	2132	1919	1586	1361	1285	1647
55°	1621	1374	1031	841	781	1449
65°	1095	838	552	444	435	1085
75°	584	362	254	232	229	617
85°	136	70	60	60	60	156
90°	1	17	28	35	37	12
95°	90	44	54	61	59	106
105°	420	461	84	99	105	449
115°	794	818	852	213	113	782
125°	1123	1141	1167	1177	1181	1001
135°	1389	1412	1424	1438	1435	1073
145°	1612	1610	1634	1643	1636	1008
155°	1774	1762	1779	1787	1776	818
165°	1870	1862	1866	1875	1866	528
175°	1913	1903	1906	1915	1902	182
180°	1908	1908	1908	1908	1908	



TEST NUMBER: P927062

CATALOG NUMBER: DFN2DIP-HX4F0-090D060US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3505.8	3505.8	3505.8	3505.8	3505.8
2.5°	3521.7	3505.8	3470.8	3502.8	3496.4
5°	3505.8	3490.0	3448.6	3477.2	3467.7
7.5°	3477.2	3458.3	3413.9	3426.4	3410.5
10°	3439.2	3416.9	3353.7	3343.9	3325.0
12.5°	3391.7	3363.1	3277.3	3258.4	3223.4
15°	3334.5	3299.5	3191.8	3131.5	3099.9
17.5°	3267.8	3217.0	3083.7	3014.0	2963.2
20°	3191.8	3128.2	2969.5	2890.5	2820.4
22.5°	3109.3	3036.3	2852.1	2744.4	2697.0
25°	3026.8	2925.1	2715.8	2585.8	2538.1
27.5°	2928.5	2820.4	2588.9	2439.8	2366.7
30°	2823.8	2703.0	2449.2	2287.6	2201.8
32.5°	2722.1	2576.0	2316.2	2125.7	2046.3
35°	2608.1	2446.2	2167.1	1967.2	1897.2
37.5°	2497.0	2322.3	2027.4	1808.3	1729.2
40°	2379.5	2189.3	1881.3	1656.2	1573.7
42.5°	2259.0	2056.1	1735.5	1500.6	1421.5
45°	2132.1	1919.4	1586.4	1360.9	1284.8
47.5°	2011.6	1786.4	1443.7	1218.2	1148.5
50°	1878.3	1653.1	1304.0	1084.9	1018.6
52.5°	1748.1	1510.1	1170.8	961.4	901.1
55°	1621.1	1373.7	1031.0	840.9	780.6
57.5°	1491.2	1237.4	907.5	729.8	679.0
60°	1357.9	1104.0	777.3	615.6	564.8
62.5°	1228.0	974.2	666.2	514.0	488.8
65°	1094.6	837.5	552.0	444.3	434.6
67.5°	967.8	710.6	444.3	390.1	380.7
70°	834.5	587.1	368.0	336.3	323.5
72.5°	707.5	472.6	307.6	282.4	276.1
75°	583.7	361.5	253.8	231.6	228.6
77.5°	460.1	256.8	199.9	187.2	180.8
80°	345.7	184.2	152.1	139.7	139.7
82.5°	241.0	123.8	104.7	98.3	98.3
85°	136.3	69.7	60.2	60.2	60.2
87.5°	50.8	25.3	25.3	22.2	22.2
90°	1.3	16.6	27.5	34.6	37.2
92.5°	34.6	29.0	33.1	35.9	37.2
95°	89.7	44.1	53.8	60.9	59.4
97.5°	161.5	48.4	70.3	74.6	76.0
100°	244.5	55.2	78.7	89.7	92.5
102.5°	335.5	332.9	81.5	96.6	100.8
105°	419.8	461.3	84.3	99.3	105.0
107.5°	517.9	552.3	87.1	102.2	107.7
110°	611.9	640.7	241.8	103.7	109.0



TEST NUMBER: P927062

CATALOG NUMBER: DFN2DIP-HX4F0-090D060US830-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	700.2	725.0	701.5	106.2	110.6
115°	794.1	817.5	852.1	212.7	113.3
117.5°	875.5	903.1	926.7	729.1	367.3
120°	966.7	987.4	1012.3	1028.8	842.4
122.5°	1043.9	1066.1	1093.8	1102.0	1103.5
125°	1122.7	1140.7	1166.9	1176.6	1180.7
127.5°	1194.5	1213.8	1234.7	1248.4	1249.8
130°	1262.2	1284.3	1299.4	1314.7	1313.4
132.5°	1331.3	1349.3	1364.4	1376.8	1375.5
135°	1389.3	1411.5	1423.7	1437.7	1434.9
137.5°	1449.9	1466.5	1480.5	1494.2	1490.2
140°	1509.3	1520.5	1535.6	1548.1	1541.2
142.5°	1559.2	1568.9	1586.8	1597.7	1590.8
145°	1611.7	1610.2	1633.6	1643.3	1636.5
147.5°	1657.1	1653.0	1676.4	1683.3	1677.9
150°	1701.4	1691.7	1713.8	1722.0	1715.2
152.5°	1738.6	1727.6	1748.2	1756.6	1746.9
155°	1774.5	1762.2	1778.8	1787.0	1776.0
157.5°	1803.6	1792.5	1805.0	1814.7	1803.6
160°	1828.4	1820.1	1828.4	1836.6	1827.0
162.5°	1850.4	1842.2	1849.1	1858.8	1846.4
165°	1869.8	1861.6	1865.7	1875.4	1865.7
167.5°	1885.0	1876.7	1880.9	1890.7	1878.1
170°	1897.5	1889.1	1892.0	1901.6	1889.1
172.5°	1905.7	1897.5	1900.3	1910.0	1897.5
175°	1912.6	1902.9	1905.7	1915.3	1901.6
177.5°	1915.3	1905.7	1907.1	1916.9	1904.4
180°	1908.5	1908.5	1908.5	1908.5	1908.5



TEST NUMBER: P927062
 CATALOG NUMBER: DFN2DIP-HX4F0-090D060US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.05	11.93	11.96	12.85	14.04	7.02	7.91	7.93	8.83	10.01
	3H	12.73	13.52	13.65	14.45	15.66	8.22	9.01	9.14	9.94	11.14
	4H	13.34	14.09	14.28	15.03	16.24	8.67	9.42	9.60	10.35	11.57
	6H	13.77	14.45	14.71	15.40	16.62	9.00	9.68	9.94	10.63	11.85
	8H	13.90	14.55	14.85	15.51	16.73	9.09	9.74	10.04	10.70	11.93
	12H	13.96	14.58	14.92	15.53	16.78	9.13	9.76	10.09	10.71	11.96
4H	2H	11.07	11.82	12.01	12.76	13.97	7.62	8.37	8.56	9.31	10.52
	3H	12.91	13.53	13.86	14.50	15.73	8.98	9.60	9.93	10.57	11.80
	4H	13.60	14.17	14.56	15.13	16.38	9.53	10.10	10.49	11.06	12.31
	6H	14.12	14.61	15.10	15.59	16.85	9.96	10.44	10.93	11.43	12.68
	8H	14.30	14.75	15.27	15.73	17.00	10.09	10.54	11.06	11.52	12.79
	12H	14.40	14.81	15.39	15.80	17.07	10.16	10.57	11.15	11.56	12.83
8H	4H	13.58	14.03	14.55	15.01	16.28	9.82	10.27	10.79	11.25	12.52
	6H	14.14	14.52	15.14	15.54	16.81	10.34	10.71	11.34	11.74	13.00
	8H	14.36	14.69	15.37	15.70	16.99	10.53	10.86	11.54	11.87	13.16
	12H	14.50	14.80	15.51	15.80	17.13	10.66	10.95	11.67	11.95	13.28
12H	4H	13.53	13.94	14.52	14.93	16.21	9.82	10.23	10.82	11.23	12.50
	6H	14.12	14.45	15.13	15.46	16.74	10.39	10.72	11.40	11.73	13.01
	8H	14.34	14.64	15.36	15.64	16.97	10.60	10.90	11.61	11.90	13.23