

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927077

Luminaire Tested: DFN2DIP-HX4F0-090D100US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927077
REPORT IS A COMBINATION OF REPORTS P899418 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D100US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15551.3 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927077

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927077

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	71	66	64	60	57	52	50	48	42	41	39
3	82	72	65	60	75	67	61	56	56	52	48	47	44	41	38	36	34
4	75	64	57	51	69	60	53	48	50	45	41	42	38	35	34	32	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2607	2607	2607
5°	2611	2566	2582
10°	2586	2516	2498
15°	2550	2433	2368
20°	2503	2318	2209
25°	2455	2190	2055
30°	2391	2059	1860
35°	2328	1917	1689
40°	2263	1771	1492
45°	2188	1608	1314
50°	2111	1444	1140
55°	2031	1269	973
60°	1937	1086	801
65°	1830	899	721
70°	1700	726	653
75°	1537	640	594
80°	1300	538	516
85°	909	360	388

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2248 cd/sqm

TEST NUMBER: P927077

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.6	2.1
10°-20°	902.0	5.8
20°-30°	1266.4	8.1
30°-40°	1380.4	8.9
40°-50°	1268.7	8.2
50°-60°	996.4	6.4
60°-70°	648.6	4.2
70°-80°	333.9	2.1
80°-90°	93.7	0.6
90°-100°	184.5	1.2
100°-110°	586.1	3.8
110°-120°	1002.9	6.4
120°-130°	1319.0	8.5
130°-140°	1480.5	9.5
140°-150°	1451.8	9.3
150°-160°	1217.9	7.8
160°-170°	807.7	5.2
170°-180°	282.3	1.8
0°-30°	2496.9	16.1
0°-40°	3877.3	24.9
0°-60°	6142.5	39.5
0°-90°	7218.6	46.4
90°-120°	1773.4	11.4
90°-150°	6024.8	38.7
90°-180°	8333.0	53.6
0°-180°	15551.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3506	3506	3506	3506	3506	
5°	3506	3490	3449	3477	3468	332
15°	3334	3300	3192	3132	3100	940
25°	3027	2925	2716	2586	2538	1392
35°	2608	2446	2167	1967	1897	1632
45°	2132	1919	1586	1361	1285	1647
55°	1621	1374	1031	841	781	1449
65°	1095	838	552	444	435	1085
75°	584	362	254	232	229	617
85°	136	70	60	60	60	156
90°	3	32	88	83	85	15
95°	131	156	161	161	156	146
105°	541	548	554	558	558	571
115°	1006	1021	1016	1014	1006	995
125°	1464	1486	1479	1471	1468	1308
135°	1893	1921	1927	1924	1917	1464
145°	2299	2317	2331	2334	2324	1436
155°	2628	2636	2644	2656	2648	1210
165°	2860	2857	2857	2875	2862	807
175°	2975	2968	2963	2981	2966	283
180°	2981	2981	2981	2981	2981	

TEST NUMBER: P927077

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3505.8	3505.8	3505.8	3505.8	3505.8
2.5°	3521.7	3505.8	3470.8	3502.8	3496.4
5°	3505.8	3490.0	3448.6	3477.2	3467.7
7.5°	3477.2	3458.3	3413.9	3426.4	3410.5
10°	3439.2	3416.9	3353.7	3343.9	3325.0
12.5°	3391.7	3363.1	3277.3	3258.4	3223.4
15°	3334.5	3299.5	3191.8	3131.5	3099.9
17.5°	3267.8	3217.0	3083.7	3014.0	2963.2
20°	3191.8	3128.2	2969.5	2890.5	2820.4
22.5°	3109.3	3036.3	2852.1	2744.4	2697.0
25°	3026.8	2925.1	2715.8	2585.8	2538.1
27.5°	2928.5	2820.4	2588.9	2439.8	2366.7
30°	2823.8	2703.0	2449.2	2287.6	2201.8
32.5°	2722.1	2576.0	2316.2	2125.7	2046.3
35°	2608.1	2446.2	2167.1	1967.2	1897.2
37.5°	2497.0	2322.3	2027.4	1808.3	1729.2
40°	2379.5	2189.3	1881.3	1656.2	1573.7
42.5°	2259.0	2056.1	1735.5	1500.6	1421.5
45°	2132.1	1919.4	1586.4	1360.9	1284.8
47.5°	2011.6	1786.4	1443.7	1218.2	1148.5
50°	1878.3	1653.1	1304.0	1084.9	1018.6
52.5°	1748.1	1510.1	1170.8	961.4	901.1
55°	1621.1	1373.7	1031.0	840.9	780.6
57.5°	1491.2	1237.4	907.5	729.8	679.0
60°	1357.9	1104.0	777.3	615.6	564.8
62.5°	1228.0	974.2	666.2	514.0	488.8
65°	1094.6	837.5	552.0	444.3	434.6
67.5°	967.8	710.6	444.3	390.1	380.7
70°	834.5	587.1	368.0	336.3	323.5
72.5°	707.5	472.6	307.6	282.4	276.1
75°	583.7	361.5	253.8	231.6	228.6
77.5°	460.1	256.8	199.9	187.2	180.8
80°	345.7	184.2	152.1	139.7	139.7
82.5°	241.0	123.8	104.7	98.3	98.3
85°	136.3	69.7	60.2	60.2	60.2
87.5°	50.8	25.3	25.3	22.2	22.2
90°	2.7	32.3	88.0	82.7	85.4
92.5°	55.7	75.5	78.2	80.9	80.9
95°	131.2	156.4	160.9	160.9	156.4
97.5°	218.4	241.8	251.6	251.6	251.6
100°	319.0	339.7	346.8	346.8	344.2
102.5°	425.1	440.3	450.2	452.9	450.2
105°	541.0	548.2	553.5	558.1	558.1
107.5°	656.0	666.8	666.8	668.6	656.0
110°	767.5	781.8	781.8	781.8	774.6

TEST NUMBER: P927077

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	887.8	903.1	900.5	893.2	887.8
115°	1006.5	1020.8	1016.4	1013.7	1006.5
117.5°	1124.2	1144.0	1131.4	1124.2	1117.0
120°	1242.8	1262.6	1242.8	1242.8	1234.8
122.5°	1350.6	1375.8	1363.2	1356.1	1350.6
125°	1463.9	1486.3	1479.2	1471.1	1468.4
127.5°	1574.4	1602.2	1592.4	1581.6	1574.4
130°	1677.7	1710.1	1705.6	1700.2	1690.4
132.5°	1793.7	1818.8	1820.6	1808.1	1800.8
135°	1893.4	1921.3	1926.7	1924.0	1916.8
137.5°	2004.9	2027.3	2031.8	2030.1	2019.2
140°	2102.8	2125.2	2137.9	2137.9	2128.0
142.5°	2203.5	2225.9	2233.1	2235.8	2225.9
145°	2298.7	2316.7	2331.1	2333.7	2323.8
147.5°	2384.1	2406.6	2417.3	2421.8	2412.0
150°	2472.2	2487.4	2497.3	2505.4	2497.3
152.5°	2550.3	2565.6	2578.2	2588.1	2578.2
155°	2628.5	2635.7	2643.8	2656.3	2648.2
157.5°	2695.9	2701.3	2705.8	2723.7	2711.2
160°	2756.2	2761.5	2764.2	2779.4	2768.7
162.5°	2811.9	2811.9	2814.5	2831.6	2819.0
165°	2859.5	2856.7	2856.7	2874.7	2862.2
167.5°	2902.6	2894.5	2894.5	2912.5	2899.9
170°	2934.9	2927.8	2925.0	2943.1	2927.8
172.5°	2957.4	2950.2	2947.5	2965.5	2950.2
175°	2975.4	2968.2	2962.8	2980.8	2965.5
177.5°	2985.3	2978.1	2972.6	2987.9	2972.6
180°	2980.8	2980.8	2980.8	2980.8	2980.8

TEST NUMBER: P927077

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.13	10.93	11.12	11.93	13.26	6.10	6.91	7.10	7.91	9.23
	3H	11.81	12.52	12.81	13.53	14.88	7.29	8.01	8.30	9.02	10.36
	4H	12.41	13.09	13.43	14.11	15.46	7.74	8.42	8.76	9.43	10.79
	6H	12.84	13.46	13.86	14.48	15.84	8.06	8.69	9.09	9.71	11.07
	8H	12.96	13.56	13.99	14.59	15.95	8.15	8.75	9.19	9.78	11.14
	12H	13.02	13.59	14.06	14.61	16.00	8.20	8.76	9.24	9.79	11.17
4H	2H	10.15	10.82	11.17	11.84	13.19	6.70	7.37	7.72	8.39	9.74
	3H	11.97	12.54	13.01	13.58	14.95	8.05	8.61	9.08	9.65	11.02
	4H	12.67	13.18	13.70	14.21	15.60	8.59	9.11	9.63	10.14	11.53
	6H	13.18	13.62	14.23	14.68	16.06	9.01	9.46	10.06	10.51	11.90
	8H	13.36	13.77	14.40	14.82	16.22	9.14	9.56	10.19	10.61	12.01
	12H	13.45	13.82	14.52	14.89	16.29	9.21	9.58	10.28	10.65	12.05
8H	4H	12.63	13.04	13.68	14.09	15.49	8.87	9.29	9.92	10.34	11.74
	6H	13.20	13.54	14.27	14.63	16.03	9.39	9.73	10.47	10.83	12.22
	8H	13.41	13.71	14.49	14.79	16.21	9.59	9.88	10.67	10.96	12.38
	12H	13.55	13.82	14.64	14.89	16.35	9.70	9.97	10.79	11.04	12.50
12H	4H	12.58	12.96	13.65	14.02	15.42	8.88	9.25	9.94	10.31	11.72
	6H	13.17	13.47	14.25	14.55	15.97	9.44	9.74	10.52	10.82	12.23
	8H	13.39	13.66	14.48	14.73	16.19	9.65	9.92	10.74	10.99	12.44