

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927138

Luminaire Tested: DFN2DIP-HX4F0-110D070US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927138
REPORT IS A COMBINATION OF REPORTS P900888 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D070US830-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15343.9 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927138

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927138

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		75	75	75		63	63	63
1	100	96	92	89		93	89	86	83		78	75	73		67	65	63		57	55	54
2	92	84	78	73		85	79	74	69		69	65	61		59	56	54		50	48	47
3	84	75	68	62		78	70	64	59		61	56	52		53	49	46		45	43	40
4	77	66	59	53		72	62	56	50		55	49	45		47	43	40		41	38	35
5	71	60	52	46		66	56	49	44		49	44	39		43	39	35		37	34	31
6	66	54	46	40		61	51	43	38		45	39	35		39	35	31		34	30	28
7	61	49	41	35		57	46	39	34		41	35	31		36	31	28		31	27	25
8	57	44	37	32		53	42	35	30		37	32	28		33	28	25		29	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	23		27	23	20
10	49	37	30	26		46	35	29	25		32	26	23		28	24	21		25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3186	3186	3186
5°	3191	3136	3156
10°	3160	3075	3053
15°	3117	2973	2895
20°	3060	2834	2700
25°	3001	2677	2512
30°	2922	2516	2273
35°	2845	2343	2064
40°	2766	2164	1824
45°	2675	1966	1606
50°	2580	1765	1393
55°	2482	1551	1189
60°	2368	1327	979
65°	2237	1099	881
70°	2078	887	798
75°	1878	782	726
80°	1589	657	630
85°	1111	440	475

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2675 cd/sqm

TEST NUMBER: P927138

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	401.6	2.6
10°-20°	1102.4	7.2
20°-30°	1547.8	10.1
30°-40°	1687.2	11.0
40°-50°	1550.7	10.1
50°-60°	1217.8	7.9
60°-70°	792.7	5.2
70°-80°	408.0	2.7
80°-90°	108.1	0.7
90°-100°	73.4	0.5
100°-110°	273.7	1.8
110°-120°	725.9	4.7
120°-130°	1203.9	7.8
130°-140°	1278.9	8.3
140°-150°	1188.6	7.7
150°-160°	955.6	6.2
160°-170°	615.7	4.0
170°-180°	211.9	1.4
0°-30°	3051.8	19.9
0°-40°	4738.9	30.9
0°-60°	7507.5	48.9
0°-90°	8816.3	57.5
90°-120°	1073.0	7.0
90°-150°	4744.3	30.9
90°-180°	6528.0	42.5
0°-180°	15343.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4285	4285	4285	4285	4285	
5°	4285	4266	4215	4250	4238	406
15°	4076	4033	3901	3827	3789	1148
25°	3699	3575	3319	3160	3102	1701
35°	3188	2990	2649	2404	2319	1995
45°	2606	2346	1939	1663	1570	2012
55°	1981	1679	1260	1028	954	1771
65°	1338	1024	675	543	531	1326
75°	713	442	310	283	279	755
85°	167	85	74	74	74	191
90°	2	19	32	40	43	14
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1361	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2181	2172	2177	2188	2177	616
175°	2231	2220	2223	2235	2219	212
180°	2227	2227	2227	2227	2227	

TEST NUMBER: P927138

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4284.9	4284.9	4284.9	4284.9	4284.9
2.5°	4304.2	4284.9	4242.1	4281.2	4273.4
5°	4284.9	4265.6	4215.0	4249.9	4238.4
7.5°	4249.9	4226.8	4172.5	4187.8	4168.4
10°	4203.5	4176.2	4098.9	4087.0	4064.0
12.5°	4145.4	4110.4	4005.5	3982.4	3939.6
15°	4075.5	4032.7	3901.0	3827.4	3788.7
17.5°	3994.0	3931.9	3769.0	3683.8	3621.7
20°	3901.0	3823.3	3629.5	3532.8	3447.2
22.5°	3800.3	3710.9	3485.9	3354.3	3296.2
25°	3699.4	3575.2	3319.3	3160.5	3102.1
27.5°	3579.3	3447.2	3164.2	2981.9	2892.6
30°	3451.3	3303.7	2993.5	2795.9	2691.0
32.5°	3327.1	3148.5	2830.9	2598.1	2501.0
35°	3187.6	2989.7	2648.7	2404.3	2318.7
37.5°	3051.9	2838.3	2477.9	2210.1	2113.5
40°	2908.3	2675.9	2299.4	2024.1	1923.4
42.5°	2761.0	2512.9	2121.3	1834.1	1737.4
45°	2605.9	2345.9	1939.0	1663.3	1570.4
47.5°	2458.6	2183.4	1764.5	1488.9	1403.8
50°	2295.6	2020.4	1593.9	1326.0	1244.9
52.5°	2136.5	1845.6	1430.9	1175.0	1101.3
55°	1981.3	1679.0	1260.1	1027.7	954.1
57.5°	1822.6	1512.3	1109.1	892.0	829.8
60°	1659.6	1349.5	949.9	752.5	690.4
62.5°	1500.8	1190.7	814.2	628.3	597.4
65°	1337.9	1023.6	674.7	543.1	531.1
67.5°	1182.8	868.5	543.1	476.8	465.3
70°	1019.9	717.5	449.7	411.0	395.4
72.5°	864.7	577.7	376.1	345.1	337.3
75°	713.4	441.8	310.2	283.0	279.4
77.5°	562.4	313.9	244.4	228.7	220.9
80°	422.5	225.1	186.0	170.8	170.8
82.5°	294.5	151.4	128.0	120.2	120.2
85°	166.6	85.2	73.6	73.6	73.6
87.5°	62.1	30.8	30.8	27.1	27.1
90°	1.5	19.3	32.1	40.3	43.4
92.5°	40.3	33.8	38.6	41.9	43.4
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.1	644.4	101.6	119.2	125.7
110°	713.8	747.5	282.0	120.9	127.2

TEST NUMBER: P927138

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.7	994.1	248.2	132.2
117.5°	1021.5	1053.6	1081.1	850.6	428.6
120°	1127.8	1151.9	1181.0	1200.4	982.8
122.5°	1217.9	1243.7	1276.1	1285.7	1287.4
125°	1309.8	1330.8	1361.4	1372.8	1377.5
127.5°	1393.6	1416.1	1440.4	1456.5	1458.0
130°	1472.6	1498.4	1516.0	1533.8	1532.3
132.5°	1553.1	1574.2	1591.8	1606.3	1604.8
135°	1620.8	1646.6	1661.1	1677.3	1674.1
137.5°	1691.6	1711.0	1727.2	1743.3	1738.5
140°	1760.9	1773.9	1791.5	1806.0	1798.0
142.5°	1819.0	1830.3	1851.2	1864.0	1856.0
145°	1880.3	1878.6	1905.9	1917.2	1909.2
147.5°	1933.3	1928.5	1955.9	1963.9	1957.6
150°	1984.9	1973.7	1999.5	2009.0	2001.0
152.5°	2028.4	2015.5	2039.7	2049.4	2038.2
155°	2070.3	2055.9	2075.2	2084.8	2072.0
157.5°	2104.1	2091.3	2105.8	2117.1	2104.1
160°	2133.3	2123.5	2133.3	2142.8	2131.5
162.5°	2158.9	2149.3	2157.3	2168.6	2154.1
165°	2181.4	2171.9	2176.6	2187.9	2176.6
167.5°	2199.2	2189.4	2194.4	2205.7	2191.2
170°	2213.7	2204.0	2207.2	2218.6	2204.0
172.5°	2223.4	2213.7	2217.0	2228.3	2213.7
175°	2231.4	2220.1	2223.4	2234.6	2218.6
177.5°	2234.6	2223.4	2225.1	2236.4	2221.8
180°	2226.6	2226.6	2226.6	2226.6	2226.6

TEST NUMBER: P927138

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.84	12.74	12.74	13.65	14.81	7.82	8.71	8.71	9.62	10.79
	3H	13.53	14.33	14.44	15.25	16.44	9.01	9.81	9.92	10.73	11.92
	4H	14.14	14.89	15.06	15.82	17.02	9.47	10.22	10.39	11.15	12.35
	6H	14.56	15.26	15.50	16.19	17.40	9.79	10.49	10.73	11.42	12.63
	8H	14.69	15.35	15.64	16.31	17.51	9.89	10.55	10.83	11.50	12.71
	12H	14.76	15.39	15.71	16.33	17.56	9.93	10.56	10.88	11.51	12.74
4H	2H	11.87	12.63	12.80	13.55	14.75	8.42	9.18	9.35	10.10	11.30
	3H	13.71	14.33	14.65	15.29	16.50	9.78	10.41	10.72	11.36	12.58
	4H	14.40	14.97	15.35	15.93	17.16	10.33	10.90	11.28	11.86	13.09
	6H	14.92	15.41	15.88	16.39	17.63	10.76	11.25	11.72	12.22	13.46
	8H	15.10	15.56	16.06	16.53	17.78	10.89	11.35	11.85	12.32	13.57
	12H	15.20	15.61	16.18	16.60	17.85	10.96	11.37	11.94	12.36	13.61
8H	4H	14.37	14.83	15.34	15.80	17.06	10.62	11.08	11.58	12.05	13.30
	6H	14.94	15.32	15.93	16.34	17.59	11.14	11.52	12.13	12.53	13.78
	8H	15.16	15.50	16.16	16.50	17.77	11.33	11.67	12.33	12.67	13.94
	12H	15.30	15.60	16.31	16.59	17.91	11.46	11.75	12.46	12.74	14.06
12H	4H	14.33	14.74	15.31	15.73	16.99	10.62	11.04	11.61	12.03	13.28
	6H	14.92	15.26	15.92	16.26	17.52	11.19	11.52	12.19	12.52	13.79
	8H	15.14	15.44	16.15	16.43	17.75	11.40	11.70	12.41	12.69	14.01