

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927141

Luminaire Tested: DFN2DIP-HX4F0-110D080US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927141
REPORT IS A COMBINATION OF REPORTS P899386 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D080US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15485.3 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 170.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927141
CATALOG NUMBER: DFN2DIP-HX4F0-110D080US830-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P927141

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57	57	57	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49	49	49	49
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42	42	42	42
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	32	32	32	32
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	33	31	28	28	28	28
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25	25	25	25
7	61	49	41	35	57	46	39	34	40	35	31	35	31	28	31	27	25	22	22	22	22
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20	18	18	18	18
10	49	37	30	26	46	35	29	24	32	26	22	28	24	20	24	21	18	17	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3186	3186	3186
5°	3191	3136	3156
10°	3160	3075	3053
15°	3117	2973	2895
20°	3060	2834	2700
25°	3001	2677	2512
30°	2922	2516	2273
35°	2845	2343	2064
40°	2766	2164	1824
45°	2675	1966	1606
50°	2580	1765	1393
55°	2482	1551	1189
60°	2368	1327	979
65°	2237	1099	881
70°	2078	887	798
75°	1878	782	726
80°	1589	657	630
85°	1111	440	475

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2675 cd/sqm



TEST NUMBER: P927141

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	401.6	2.6
10°-20°	1102.4	7.1
20°-30°	1547.8	10.0
30°-40°	1687.2	10.9
40°-50°	1550.7	10.0
50°-60°	1217.8	7.9
60°-70°	792.7	5.1
70°-80°	408.0	2.6
80°-90°	110.9	0.7
90°-100°	147.6	1.0
100°-110°	468.9	3.0
110°-120°	802.3	5.2
120°-130°	1055.2	6.8
130°-140°	1184.4	7.6
140°-150°	1161.5	7.5
150°-160°	974.3	6.3
160°-170°	646.1	4.2
170°-180°	225.8	1.5
0°-30°	3051.8	19.7
0°-40°	4738.9	30.6
0°-60°	7507.5	48.5
0°-90°	8819.2	57.0
90°-120°	1418.8	9.2
90°-150°	4819.9	31.1
90°-180°	6666.0	43.0
0°-180°	15485.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4285	4285	4285	4285	4285	
5°	4285	4266	4215	4250	4238	406
15°	4076	4033	3901	3827	3789	1148
25°	3699	3575	3319	3160	3102	1701
35°	3188	2990	2649	2404	2319	1995
45°	2606	2346	1939	1663	1570	2012
55°	1981	1679	1260	1028	954	1771
65°	1338	1024	675	543	531	1326
75°	713	442	310	283	279	755
85°	167	85	74	74	74	191
90°	2	26	70	66	68	15
95°	105	125	129	129	125	117
105°	433	438	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1533	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2285	2285	2300	2290	645
175°	2380	2374	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	



TEST NUMBER: P927141

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4284.9	4284.9	4284.9	4284.9	4284.9
2.5°	4304.2	4284.9	4242.1	4281.2	4273.4
5°	4284.9	4265.6	4215.0	4249.9	4238.4
7.5°	4249.9	4226.8	4172.5	4187.8	4168.4
10°	4203.5	4176.2	4098.9	4087.0	4064.0
12.5°	4145.4	4110.4	4005.5	3982.4	3939.6
15°	4075.5	4032.7	3901.0	3827.4	3788.7
17.5°	3994.0	3931.9	3769.0	3683.8	3621.7
20°	3901.0	3823.3	3629.5	3532.8	3447.2
22.5°	3800.3	3710.9	3485.9	3354.3	3296.2
25°	3699.4	3575.2	3319.3	3160.5	3102.1
27.5°	3579.3	3447.2	3164.2	2981.9	2892.6
30°	3451.3	3303.7	2993.5	2795.9	2691.0
32.5°	3327.1	3148.5	2830.9	2598.1	2501.0
35°	3187.6	2989.7	2648.7	2404.3	2318.7
37.5°	3051.9	2838.3	2477.9	2210.1	2113.5
40°	2908.3	2675.9	2299.4	2024.1	1923.4
42.5°	2761.0	2512.9	2121.3	1834.1	1737.4
45°	2605.9	2345.9	1939.0	1663.3	1570.4
47.5°	2458.6	2183.4	1764.5	1488.9	1403.8
50°	2295.6	2020.4	1593.9	1326.0	1244.9
52.5°	2136.5	1845.6	1430.9	1175.0	1101.3
55°	1981.3	1679.0	1260.1	1027.7	954.1
57.5°	1822.6	1512.3	1109.1	892.0	829.8
60°	1659.6	1349.5	949.9	752.5	690.4
62.5°	1500.8	1190.7	814.2	628.3	597.4
65°	1337.9	1023.6	674.7	543.1	531.1
67.5°	1182.8	868.5	543.1	476.8	465.3
70°	1019.9	717.5	449.7	411.0	395.4
72.5°	864.7	577.7	376.1	345.1	337.3
75°	713.4	441.8	310.2	283.0	279.4
77.5°	562.4	313.9	244.4	228.7	220.9
80°	422.5	225.1	186.0	170.8	170.8
82.5°	294.5	151.4	128.0	120.2	120.2
85°	166.6	85.2	73.6	73.6	73.6
87.5°	62.1	30.8	30.8	27.1	27.1
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.5	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	613.9	625.4	625.4	625.4	619.7



TEST NUMBER: P927141

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.5	720.4	714.6	710.3
115°	805.2	816.7	813.1	810.9	805.2
117.5°	899.3	915.2	905.1	899.3	893.6
120°	994.2	1010.1	994.2	994.2	987.7
122.5°	1080.5	1100.7	1090.6	1084.8	1080.5
125°	1171.1	1189.1	1183.3	1176.8	1174.7
127.5°	1259.6	1281.8	1273.9	1265.3	1259.6
130°	1342.2	1368.0	1364.5	1360.2	1352.3
132.5°	1435.0	1455.0	1456.5	1446.5	1440.7
135°	1514.7	1537.0	1541.4	1539.2	1533.4
137.5°	1603.9	1621.9	1625.4	1624.0	1615.4
140°	1682.3	1700.2	1710.3	1710.3	1702.3
142.5°	1762.8	1780.8	1786.5	1788.7	1780.8
145°	1839.0	1853.3	1864.8	1867.0	1859.1
147.5°	1907.2	1925.2	1933.8	1937.5	1929.6
150°	1977.7	1989.9	1997.8	2004.3	1997.8
152.5°	2040.2	2052.5	2062.6	2070.5	2062.6
155°	2102.8	2108.6	2115.1	2125.1	2118.6
157.5°	2156.7	2161.1	2164.6	2179.0	2169.0
160°	2204.9	2209.2	2211.4	2223.5	2215.0
162.5°	2249.5	2249.5	2251.6	2265.3	2255.2
165°	2287.5	2285.4	2285.4	2299.8	2289.7
167.5°	2322.0	2315.6	2315.6	2330.0	2319.9
170°	2348.0	2342.2	2340.0	2354.5	2342.2
172.5°	2366.0	2360.2	2358.0	2372.4	2360.2
175°	2380.3	2374.5	2370.2	2384.6	2372.4
177.5°	2388.2	2382.5	2378.1	2390.4	2378.1
180°	2384.6	2384.6	2384.6	2384.6	2384.6



TEST NUMBER: P927141
 CATALOG NUMBER: DFN2DIP-HX4F0-110D080US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.80	12.69	12.70	13.61	14.78	7.77	8.66	8.67	9.58	10.75
	3H	13.48	14.28	14.40	15.20	16.40	8.97	9.76	9.88	10.69	11.89
	4H	14.09	14.85	15.02	15.78	16.98	9.42	10.17	10.35	11.10	12.31
	6H	14.52	15.21	15.46	16.15	17.37	9.75	10.44	10.69	11.38	12.59
	8H	14.65	15.31	15.60	16.26	17.48	9.84	10.50	10.79	11.45	12.67
	12H	14.71	15.34	15.66	16.29	17.53	9.89	10.51	10.84	11.46	12.70
4H	2H	11.82	12.58	12.76	13.51	14.71	8.38	9.13	9.31	10.06	11.26
	3H	13.66	14.29	14.61	15.25	16.47	9.73	10.36	10.68	11.32	12.54
	4H	14.36	14.93	15.31	15.88	17.13	10.28	10.85	11.24	11.81	13.06
	6H	14.87	15.36	15.84	16.35	17.59	10.71	11.20	11.68	12.18	13.42
	8H	15.05	15.51	16.02	16.48	17.74	10.84	11.30	11.81	12.27	13.53
	12H	15.15	15.56	16.14	16.55	17.82	10.91	11.32	11.90	12.31	13.58
8H	4H	14.33	14.79	15.30	15.76	17.02	10.57	11.03	11.54	12.00	13.26
	6H	14.90	15.28	15.89	16.29	17.55	11.09	11.47	12.09	12.49	13.74
	8H	15.12	15.45	16.12	16.45	17.73	11.29	11.62	12.29	12.62	13.90
	12H	15.26	15.55	16.26	16.55	17.87	11.41	11.70	12.41	12.70	14.02
12H	4H	14.28	14.70	15.27	15.69	16.95	10.58	10.99	11.56	11.98	13.24
	6H	14.87	15.21	15.88	16.21	17.49	11.14	11.48	12.15	12.48	13.75
	8H	15.10	15.39	16.10	16.39	17.71	11.36	11.65	12.36	12.65	13.97