

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905406

Luminaire Tested: DFN2DIP-HX3F0-090D070US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905406
REPORT IS A COMBINATION OF REPORTS P899269 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-090D070US835-FLLFL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15105.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 146.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905406

CATALOG NUMBER: DFN2DIP-HX3F0-090D070US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905406

CATALOG NUMBER: DFN2DIP-HX3F0-090D070US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		102	102	102	102		88	88	88		76	76	76		64	64	64
1	100	95	91	88		93	89	86	83		78	75	73		67	65	63		57	56	54
2	91	83	77	72		85	78	73	68		68	64	60		59	56	53		50	48	46
3	83	73	66	60		77	69	62	57		60	55	51		52	48	45		44	42	39
4	76	65	57	51		71	61	54	48		53	48	43		46	42	38		40	36	34
5	70	58	50	44		65	54	47	41		48	42	37		42	37	33		36	32	29
6	64	52	44	38		60	49	41	36		43	37	33		38	33	29		33	29	26
7	59	47	39	33		55	44	37	32		39	33	29		34	29	26		30	26	23
8	55	43	35	29		51	40	33	28		36	30	26		31	27	23		27	23	21
9	51	39	31	26		48	37	30	25		33	27	23		29	24	21		25	21	19
10	48	36	29	24		45	34	27	23		30	25	21		27	22	19		23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4056	4056	4056
5°	4061	3997	4025
10°	4026	3940	3968
15°	3965	3873	3881
20°	3883	3780	3791
25°	3802	3669	3688
30°	3700	3566	3558
35°	3604	3445	3420
40°	3485	3322	3289
45°	3367	3199	3155
50°	3238	3070	2999
55°	3102	2921	2856
60°	2949	2744	2691
65°	2781	2560	2497
70°	2568	2336	2288
75°	2272	2067	2091
80°	1916	1723	1722
85°	1359	1141	1117

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3367 cd/sqm

TEST NUMBER: P905406

CATALOG NUMBER: DFN2DIP-HX3F0-090D070US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	2.2
10°-20°	927.4	6.1
20°-30°	1362.9	9.0
30°-40°	1582.9	10.5
40°-50°	1580.9	10.5
50°-60°	1378.5	9.1
60°-70°	1019.0	6.7
70°-80°	576.6	3.8
80°-90°	158.5	1.0
90°-100°	137.0	0.9
100°-110°	435.3	2.9
110°-120°	744.9	4.9
120°-130°	979.6	6.5
130°-140°	1099.6	7.3
140°-150°	1078.3	7.1
150°-160°	904.5	6.0
160°-170°	599.9	4.0
170°-180°	209.7	1.4
0°-30°	2619.9	17.3
0°-40°	4202.8	27.8
0°-60°	7162.3	47.4
0°-90°	8916.3	59.0
90°-120°	1317.2	8.7
90°-150°	4474.7	29.6
90°-180°	6189.0	41.0
0°-180°	15105.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	154
90°	2	24	65	61	63	15
95°	97	116	120	120	116	108
105°	402	407	411	414	414	424
115°	748	758	755	753	748	739
125°	1087	1104	1099	1093	1091	972
135°	1406	1427	1431	1429	1424	1087
145°	1707	1721	1731	1733	1726	1067
155°	1952	1958	1964	1973	1967	899
165°	2124	2122	2122	2135	2126	599
175°	2210	2204	2200	2214	2202	210
180°	2214	2214	2214	2214	2214	

TEST NUMBER: P905406

CATALOG NUMBER: DFN2DIP-HX3F0-090D070US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	2.0	24.0	65.4	61.4	63.4
92.5°	41.4	56.1	58.1	60.1	60.1
95°	97.4	116.1	119.5	119.5	116.1
97.5°	162.2	179.5	186.9	186.9	186.9
100°	236.9	252.3	257.6	257.6	255.6
102.5°	315.7	327.0	334.4	336.4	334.4
105°	401.8	407.1	411.1	414.5	414.5
107.5°	487.2	495.2	495.2	496.6	487.2
110°	570.0	580.7	580.7	580.7	575.3

TEST NUMBER: P905406

CATALOG NUMBER: DFN2DIP-HX3F0-090D070US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.4	670.8	668.8	663.4	659.4
115°	747.5	758.2	754.9	752.9	747.5
117.5°	834.9	849.6	840.3	834.9	829.6
120°	923.0	937.7	923.0	923.0	917.0
122.5°	1003.1	1021.8	1012.5	1007.1	1003.1
125°	1087.2	1103.9	1098.6	1092.6	1090.6
127.5°	1169.3	1190.0	1182.7	1174.7	1169.3
130°	1246.1	1270.1	1266.8	1262.8	1255.4
132.5°	1332.2	1350.9	1352.2	1342.9	1337.5
135°	1406.3	1426.9	1431.0	1428.9	1423.6
137.5°	1489.0	1505.7	1509.0	1507.7	1499.7
140°	1561.8	1578.5	1587.8	1587.8	1580.5
142.5°	1636.5	1653.2	1658.5	1660.5	1653.2
145°	1707.3	1720.6	1731.3	1733.3	1726.0
147.5°	1770.7	1787.4	1795.4	1798.7	1791.4
150°	1836.1	1847.4	1854.8	1860.8	1854.8
152.5°	1894.1	1905.5	1914.8	1922.2	1914.8
155°	1952.2	1957.5	1963.6	1972.9	1966.9
157.5°	2002.3	2006.3	2009.6	2023.0	2013.6
160°	2047.0	2051.0	2053.0	2064.3	2056.3
162.5°	2088.4	2088.4	2090.4	2103.0	2093.7
165°	2123.7	2121.7	2121.7	2135.1	2125.7
167.5°	2155.8	2149.8	2149.8	2163.1	2153.8
170°	2179.8	2174.5	2172.5	2185.8	2174.5
172.5°	2196.5	2191.1	2189.1	2202.5	2191.1
175°	2209.8	2204.5	2200.5	2213.8	2202.5
177.5°	2217.2	2211.8	2207.8	2219.2	2207.8
180°	2213.8	2213.8	2213.8	2213.8	2213.8

TEST NUMBER: P905406

CATALOG NUMBER: DFN2DIP-HX3F0-090D070US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.89	13.84	13.76	14.73	15.87	12.46	13.41	13.33	14.30	15.44
	3H	14.55	15.40	15.43	16.30	17.46	14.08	14.93	14.96	15.83	17.00
	4H	15.13	15.94	16.04	16.85	18.02	14.66	15.47	15.57	16.38	17.55
	6H	15.53	16.27	16.45	17.19	18.38	15.06	15.80	15.98	16.72	17.91
	8H	15.63	16.34	16.56	17.28	18.46	15.17	15.87	16.09	16.81	17.99
	12H	15.68	16.36	16.61	17.29	18.49	15.21	15.88	16.14	16.81	18.02
4H	2H	13.36	14.16	14.26	15.07	16.24	13.01	13.82	13.92	14.73	15.90
	3H	15.22	15.89	16.14	16.84	18.02	14.83	15.50	15.75	16.45	17.63
	4H	15.93	16.55	16.86	17.48	18.70	15.53	16.14	16.46	17.08	18.29
	6H	16.45	16.97	17.39	17.94	19.15	16.04	16.57	16.98	17.53	18.74
	8H	16.59	17.09	17.54	18.04	19.27	16.19	16.68	17.13	17.64	18.86
	12H	16.67	17.11	17.63	18.09	19.32	16.25	16.70	17.22	17.67	18.90
8H	4H	16.13	16.63	17.08	17.58	18.81	15.78	16.27	16.72	17.23	18.45
	6H	16.76	17.17	17.73	18.17	19.39	16.40	16.81	17.37	17.81	19.03
	8H	16.97	17.34	17.96	18.32	19.57	16.61	16.97	17.59	17.96	19.20
	12H	17.11	17.42	18.09	18.40	19.69	16.73	17.04	17.71	18.02	19.32
12H	4H	16.12	16.57	17.09	17.54	18.77	15.77	16.22	16.74	17.19	18.42
	6H	16.79	17.15	17.77	18.14	19.38	16.44	16.80	17.42	17.79	19.03
	8H	17.03	17.35	18.01	18.33	19.62	16.67	16.99	17.66	17.97	19.26