

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927158

Luminaire Tested: DFN2DIP-HX4F0-110D120US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927158
REPORT IS A COMBINATION OF REPORTS P900978 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D120US830-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20009.3 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 208.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927158

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927158

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44
2	89	81	76	71	81	75	70	66	62	59	56	51	49	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28
5	68	57	49	44	62	53	46	41	45	39	35	37	33	30	30	27	25
6	63	51	44	38	58	48	41	36	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3186	3186	3186
5°	3191	3136	3156
10°	3160	3075	3053
15°	3117	2973	2895
20°	3060	2834	2700
25°	3001	2677	2512
30°	2922	2516	2273
35°	2845	2343	2064
40°	2766	2164	1824
45°	2675	1966	1606
50°	2580	1765	1393
55°	2482	1551	1189
60°	2368	1327	979
65°	2237	1099	881
70°	2078	887	798
75°	1878	782	726
80°	1589	657	630
85°	1111	440	475

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2675 cd/sqm

TEST NUMBER: P927158

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	401.6	2.0
10°-20°	1102.4	5.5
20°-30°	1547.8	7.7
30°-40°	1687.2	8.4
40°-50°	1550.7	7.7
50°-60°	1217.8	6.1
60°-70°	792.7	4.0
70°-80°	408.0	2.0
80°-90°	110.9	0.6
90°-100°	125.9	0.6
100°-110°	469.2	2.3
110°-120°	1244.4	6.2
120°-130°	2063.9	10.3
130°-140°	2192.3	11.0
140°-150°	2037.5	10.2
150°-160°	1638.1	8.2
160°-170°	1055.6	5.3
170°-180°	363.3	1.8
0°-30°	3051.8	15.3
0°-40°	4738.9	23.7
0°-60°	7507.5	37.5
0°-90°	8819.1	44.1
90°-120°	1839.4	9.2
90°-150°	8133.2	40.6
90°-180°	11190.0	55.9
0°-180°	20009.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4285	4285	4285	4285	4285	
5°	4285	4266	4215	4250	4238	406
15°	4076	4033	3901	3827	3789	1148
25°	3699	3575	3319	3160	3102	1701
35°	3188	2990	2649	2404	2319	1995
45°	2606	2346	1939	1663	1570	2012
55°	1981	1679	1260	1028	954	1771
65°	1338	1024	675	543	531	1326
75°	713	442	310	283	279	755
85°	167	85	74	74	74	191
90°	3	33	55	69	74	19
95°	179	88	108	122	119	212
105°	840	923	169	199	210	897
115°	1588	1635	1704	425	227	1563
125°	2245	2281	2334	2353	2361	2003
135°	2779	2823	2848	2875	2870	2146
145°	3223	3220	3267	3287	3273	2016
155°	3549	3524	3558	3574	3552	1635
165°	3740	3723	3731	3751	3731	1057
175°	3825	3806	3811	3831	3803	364
180°	3817	3817	3817	3817	3817	

TEST NUMBER: P927158

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4284.9	4284.9	4284.9	4284.9	4284.9
2.5°	4304.2	4284.9	4242.1	4281.2	4273.4
5°	4284.9	4265.6	4215.0	4249.9	4238.4
7.5°	4249.9	4226.8	4172.5	4187.8	4168.4
10°	4203.5	4176.2	4098.9	4087.0	4064.0
12.5°	4145.4	4110.4	4005.5	3982.4	3939.6
15°	4075.5	4032.7	3901.0	3827.4	3788.7
17.5°	3994.0	3931.9	3769.0	3683.8	3621.7
20°	3901.0	3823.3	3629.5	3532.8	3447.2
22.5°	3800.3	3710.9	3485.9	3354.3	3296.2
25°	3699.4	3575.2	3319.3	3160.5	3102.1
27.5°	3579.3	3447.2	3164.2	2981.9	2892.6
30°	3451.3	3303.7	2993.5	2795.9	2691.0
32.5°	3327.1	3148.5	2830.9	2598.1	2501.0
35°	3187.6	2989.7	2648.7	2404.3	2318.7
37.5°	3051.9	2838.3	2477.9	2210.1	2113.5
40°	2908.3	2675.9	2299.4	2024.1	1923.4
42.5°	2761.0	2512.9	2121.3	1834.1	1737.4
45°	2605.9	2345.9	1939.0	1663.3	1570.4
47.5°	2458.6	2183.4	1764.5	1488.9	1403.8
50°	2295.6	2020.4	1593.9	1326.0	1244.9
52.5°	2136.5	1845.6	1430.9	1175.0	1101.3
55°	1981.3	1679.0	1260.1	1027.7	954.1
57.5°	1822.6	1512.3	1109.1	892.0	829.8
60°	1659.6	1349.5	949.9	752.5	690.4
62.5°	1500.8	1190.7	814.2	628.3	597.4
65°	1337.9	1023.6	674.7	543.1	531.1
67.5°	1182.8	868.5	543.1	476.8	465.3
70°	1019.9	717.5	449.7	411.0	395.4
72.5°	864.7	577.7	376.1	345.1	337.3
75°	713.4	441.8	310.2	283.0	279.4
77.5°	562.4	313.9	244.4	228.7	220.9
80°	422.5	225.1	186.0	170.8	170.8
82.5°	294.5	151.4	128.0	120.2	120.2
85°	166.6	85.2	73.6	73.6	73.6
87.5°	62.1	30.8	30.8	27.1	27.1
90°	2.6	33.1	55.1	69.2	74.5
92.5°	69.2	58.1	66.3	71.8	74.5
95°	179.4	88.2	107.5	121.7	118.8
97.5°	323.1	96.8	140.7	149.2	151.8
100°	489.0	110.6	157.4	179.4	185.0
102.5°	671.1	665.8	163.0	193.2	201.7
105°	839.6	922.6	168.6	198.8	209.9
107.5°	1035.7	1104.6	174.2	204.3	215.5
110°	1223.6	1281.4	483.4	207.3	218.1

TEST NUMBER: P927158

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1400.5	1449.9	1403.1	212.5	221.0
115°	1588.0	1635.0	1704.1	425.4	226.7
117.5°	1751.1	1806.2	1853.4	1458.1	734.7
120°	1933.4	1974.7	2024.6	2057.8	1684.8
122.5°	2087.9	2132.2	2187.6	2204.0	2207.0
125°	2245.3	2281.4	2333.9	2353.2	2361.4
127.5°	2389.0	2427.7	2469.4	2496.9	2499.5
130°	2524.4	2568.7	2598.8	2629.4	2626.7
132.5°	2662.5	2698.6	2728.7	2753.7	2751.1
135°	2778.6	2822.9	2847.5	2875.4	2869.8
137.5°	2900.0	2933.1	2961.0	2988.5	2980.3
140°	3018.7	3041.0	3071.1	3096.1	3082.4
142.5°	3118.4	3137.8	3173.5	3195.5	3181.7
145°	3223.4	3220.4	3267.3	3286.7	3272.8
147.5°	3314.2	3306.0	3352.9	3366.7	3355.9
150°	3402.7	3383.4	3427.7	3444.1	3430.3
152.5°	3477.2	3455.2	3496.6	3513.3	3493.9
155°	3549.0	3524.4	3557.6	3574.0	3552.0
157.5°	3607.0	3585.1	3610.1	3629.4	3607.0
160°	3656.9	3640.2	3656.9	3673.3	3654.0
162.5°	3700.9	3684.5	3698.3	3717.6	3692.7
165°	3739.6	3723.2	3731.4	3750.8	3731.4
167.5°	3770.1	3753.3	3761.9	3781.2	3756.3
170°	3795.0	3778.3	3783.9	3803.2	3778.3
172.5°	3811.4	3795.0	3800.6	3820.0	3795.0
175°	3825.1	3805.8	3811.4	3830.8	3803.2
177.5°	3830.8	3811.4	3814.4	3833.7	3808.8
180°	3817.0	3817.0	3817.0	3817.0	3817.0

TEST NUMBER: P927158

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.59	11.38	11.61	12.40	13.75	6.57	7.35	7.58	8.37	9.73
	3H	12.27	12.97	13.29	14.00	15.37	7.75	8.46	8.78	9.48	10.86
	4H	12.88	13.54	13.91	14.57	15.95	8.20	8.87	9.24	9.90	11.28
	6H	13.30	13.91	14.34	14.94	16.34	8.52	9.13	9.57	10.17	11.56
	8H	13.42	14.00	14.47	15.05	16.44	8.61	9.20	9.67	10.24	11.64
	12H	13.48	14.03	14.54	15.08	16.49	8.66	9.21	9.71	10.25	11.67
4H	2H	10.61	11.27	11.65	12.30	13.68	7.16	7.82	8.20	8.85	10.23
	3H	12.43	12.99	13.48	14.04	15.44	8.51	9.06	9.56	10.12	11.51
	4H	13.12	13.63	14.18	14.68	16.10	9.05	9.56	10.11	10.61	12.03
	6H	13.64	14.07	14.70	15.14	16.56	9.47	9.91	10.54	10.98	12.39
	8H	13.81	14.22	14.88	15.28	16.71	9.60	10.01	10.67	11.07	12.50
	12H	13.91	14.27	14.99	15.35	16.78	9.67	10.03	10.75	11.11	12.54
8H	4H	13.09	13.49	14.16	14.56	15.99	9.33	9.74	10.40	10.80	12.23
	6H	13.66	13.99	14.74	15.10	16.52	9.85	10.18	10.94	11.29	12.72
	8H	13.87	14.16	14.97	15.26	16.70	10.04	10.34	11.14	11.43	12.87
	12H	14.01	14.27	15.11	15.35	16.84	10.16	10.42	11.26	11.50	12.99
12H	4H	13.04	13.40	14.12	14.48	15.92	9.33	9.70	10.42	10.78	12.21
	6H	13.63	13.92	14.73	15.01	16.46	9.90	10.19	11.00	11.28	12.73
	8H	13.85	14.11	14.95	15.19	16.68	10.11	10.37	11.21	11.45	12.94