

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927168

Luminaire Tested: DFN2DIP-HX4F0-120D060US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927168
REPORT IS A COMBINATION OF REPORTS P900871 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D060US830-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16795.3 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 170.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927168

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927168

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3272	3272	3272
5°	3278	3227	3249
10°	3251	3184	3205
15°	3204	3132	3136
20°	3140	3059	3066
25°	3076	2972	2985
30°	2995	2892	2882
35°	2919	2796	2772
40°	2826	2700	2668
45°	2732	2604	2562
50°	2630	2503	2439
55°	2523	2386	2326
60°	2403	2247	2196
65°	2271	2103	2043
70°	2104	1928	1879
75°	1871	1718	1727
80°	1592	1451	1437
85°	1155	988	956

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2732 cd/sqm

TEST NUMBER: P927168

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.2	2.5
10°-20°	1165.4	6.9
20°-30°	1712.7	10.2
30°-40°	1989.2	11.8
40°-50°	1986.7	11.8
50°-60°	1732.3	10.3
60°-70°	1280.6	7.6
70°-80°	724.5	4.3
80°-90°	194.6	1.2
90°-100°	62.9	0.4
100°-110°	234.6	1.4
110°-120°	622.2	3.7
120°-130°	1031.9	6.1
130°-140°	1096.2	6.5
140°-150°	1018.8	6.1
150°-160°	819.1	4.9
160°-170°	527.8	3.1
170°-180°	181.7	1.1
0°-30°	3292.3	19.6
0°-40°	5281.5	31.4
0°-60°	9000.5	53.6
0°-90°	11200.2	66.7
90°-120°	919.7	5.5
90°-150°	4066.6	24.2
90°-180°	5595.0	33.3
0°-180°	16795.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4401	4401	4401	4401	4401	
5°	4401	4384	4338	4371	4363	418
15°	4189	4164	4109	4126	4105	1180
25°	3792	3758	3686	3694	3686	1745
35°	3271	3229	3161	3136	3114	2043
45°	2662	2632	2568	2522	2505	2054
55°	2014	1989	1938	1888	1866	1801
65°	1359	1333	1291	1253	1232	1343
75°	711	703	681	656	664	759
85°	173	169	165	152	148	193
90°	1	17	28	35	37	16
95°	90	44	54	61	59	106
105°	420	461	84	99	105	449
115°	794	818	852	213	113	782
125°	1123	1141	1167	1177	1181	1001
135°	1389	1412	1424	1438	1435	1073
145°	1612	1610	1634	1643	1636	1008
155°	1774	1762	1779	1787	1776	818
165°	1870	1862	1866	1875	1866	528
175°	1913	1903	1906	1915	1902	182
180°	1908	1908	1908	1908	1908	

TEST NUMBER: P927168

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4400.8	4400.8	4400.8	4400.8	4400.8
2.5°	4426.4	4405.2	4358.6	4400.8	4392.7
5°	4400.8	4384.1	4337.5	4371.1	4363.0
7.5°	4371.1	4346.0	4299.3	4333.4	4324.9
10°	4324.9	4295.3	4244.5	4278.2	4265.7
12.5°	4261.1	4236.0	4185.3	4206.4	4197.8
15°	4189.3	4164.2	4108.9	4126.0	4104.9
17.5°	4100.4	4075.3	4020.0	4041.2	4020.0
20°	4003.0	3977.8	3918.6	3931.2	3914.6
22.5°	3906.0	3867.8	3812.6	3812.6	3804.1
25°	3791.5	3757.8	3686.0	3694.1	3686.0
27.5°	3664.4	3634.8	3580.1	3567.5	3546.4
30°	3537.9	3503.7	3440.4	3427.9	3410.8
32.5°	3402.2	3377.2	3309.3	3283.8	3266.7
35°	3271.1	3229.0	3161.1	3135.6	3114.5
37.5°	3123.0	3084.9	3017.0	2987.4	2966.3
40°	2970.9	2936.7	2868.9	2831.2	2814.1
42.5°	2822.7	2788.6	2721.2	2678.6	2653.4
45°	2661.9	2632.3	2568.5	2522.3	2505.3
47.5°	2505.3	2475.6	2407.8	2361.2	2336.0
50°	2340.0	2318.9	2259.6	2200.4	2179.2
52.5°	2179.2	2149.7	2094.9	2048.1	2018.6
55°	2014.5	1989.0	1938.2	1887.5	1866.3
57.5°	1849.3	1828.2	1772.9	1722.2	1705.2
60°	1684.1	1667.5	1608.2	1561.5	1548.9
62.5°	1523.4	1493.7	1451.5	1409.3	1392.3
65°	1358.6	1333.0	1290.8	1252.6	1231.6
67.5°	1189.3	1167.8	1130.1	1100.5	1083.4
70°	1032.6	1015.5	977.4	947.8	931.2
72.5°	871.9	854.8	833.7	804.1	791.5
75°	710.7	702.6	681.1	656.0	664.5
77.5°	567.0	549.9	541.5	528.8	516.3
80°	423.4	418.8	410.4	397.8	389.3
82.5°	287.7	287.7	283.8	266.7	266.7
85°	173.3	169.3	165.2	152.2	148.2
87.5°	76.3	67.8	59.3	46.7	42.2
90°	1.3	16.6	27.5	34.6	37.2
92.5°	34.6	29.0	33.1	35.9	37.2
95°	89.7	44.1	53.8	60.9	59.4
97.5°	161.5	48.4	70.3	74.6	76.0
100°	244.5	55.2	78.7	89.7	92.5
102.5°	335.5	332.9	81.5	96.6	100.8
105°	419.8	461.3	84.3	99.3	105.0
107.5°	517.9	552.3	87.1	102.2	107.7
110°	611.9	640.7	241.8	103.7	109.0

TEST NUMBER: P927168

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	700.2	725.0	701.5	106.2	110.6
115°	794.1	817.5	852.1	212.7	113.3
117.5°	875.5	903.1	926.7	729.1	367.3
120°	966.7	987.4	1012.3	1028.8	842.4
122.5°	1043.9	1066.1	1093.8	1102.0	1103.5
125°	1122.7	1140.7	1166.9	1176.6	1180.7
127.5°	1194.5	1213.8	1234.7	1248.4	1249.8
130°	1262.2	1284.3	1299.4	1314.7	1313.4
132.5°	1331.3	1349.3	1364.4	1376.8	1375.5
135°	1389.3	1411.5	1423.7	1437.7	1434.9
137.5°	1449.9	1466.5	1480.5	1494.2	1490.2
140°	1509.3	1520.5	1535.6	1548.1	1541.2
142.5°	1559.2	1568.9	1586.8	1597.7	1590.8
145°	1611.7	1610.2	1633.6	1643.3	1636.5
147.5°	1657.1	1653.0	1676.4	1683.3	1677.9
150°	1701.4	1691.7	1713.8	1722.0	1715.2
152.5°	1738.6	1727.6	1748.2	1756.6	1746.9
155°	1774.5	1762.2	1778.8	1787.0	1776.0
157.5°	1803.6	1792.5	1805.0	1814.7	1803.6
160°	1828.4	1820.1	1828.4	1836.6	1827.0
162.5°	1850.4	1842.2	1849.1	1858.8	1846.4
165°	1869.8	1861.6	1865.7	1875.4	1865.7
167.5°	1885.0	1876.7	1880.9	1890.7	1878.1
170°	1897.5	1889.1	1892.0	1901.6	1889.1
172.5°	1905.7	1897.5	1900.3	1910.0	1897.5
175°	1912.6	1902.9	1905.7	1915.3	1901.6
177.5°	1915.3	1905.7	1907.1	1916.9	1904.4
180°	1908.5	1908.5	1908.5	1908.5	1908.5

TEST NUMBER: P927168

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.80	13.84	13.60	14.66	15.67	12.37	13.41	13.17	14.23	15.24
	3H	14.48	15.41	15.29	16.24	17.28	14.01	14.93	14.82	15.77	16.81
	4H	15.07	15.95	15.90	16.79	17.84	14.60	15.48	15.43	16.32	17.37
	6H	15.48	16.29	16.33	17.14	18.20	15.01	15.82	15.85	16.66	17.73
	8H	15.59	16.37	16.44	17.23	18.30	15.12	15.89	15.97	16.76	17.82
	12H	15.65	16.38	16.51	17.24	18.33	15.17	15.90	16.02	16.76	17.85
4H	2H	13.29	14.16	14.12	15.00	16.05	12.94	13.82	13.78	14.66	15.71
	3H	15.17	15.90	16.02	16.77	17.84	14.78	15.51	15.62	16.38	17.45
	4H	15.89	16.56	16.75	17.43	18.52	15.49	16.15	16.34	17.02	18.12
	6H	16.42	17.00	17.29	17.89	18.99	16.01	16.59	16.88	17.48	18.58
	8H	16.57	17.11	17.45	18.00	19.11	16.16	16.70	17.04	17.59	18.70
	12H	16.65	17.14	17.55	18.05	19.16	16.23	16.72	17.13	17.63	18.74
8H	4H	16.10	16.64	16.98	17.53	18.64	15.74	16.28	16.62	17.17	18.28
	6H	16.74	17.19	17.65	18.12	19.23	16.38	16.83	17.29	17.76	18.87
	8H	16.97	17.36	17.88	18.29	19.41	16.60	16.99	17.51	17.92	19.04
	12H	17.11	17.46	18.02	18.37	19.55	16.72	17.07	17.64	17.99	19.17
12H	4H	16.10	16.58	16.99	17.49	18.61	15.75	16.23	16.64	17.14	18.26
	6H	16.77	17.17	17.69	18.10	19.22	16.42	16.82	17.34	17.74	18.87
	8H	17.03	17.37	17.94	18.29	19.47	16.67	17.02	17.59	17.93	19.11