

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927169

Luminaire Tested: DFN2DIP-HX4F0-120D060US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927169
REPORT IS A COMBINATION OF REPORTS P899352 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D060US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14618.2 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 170.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927169

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927169

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3476	3476	3476
5°	3482	3421	3443
10°	3447	3354	3331
15°	3400	3244	3158
20°	3338	3091	2945
25°	3274	2920	2740
30°	3188	2745	2480
35°	3103	2556	2252
40°	3018	2361	1989
45°	2918	2144	1752
50°	2815	1926	1520
55°	2708	1692	1297
60°	2583	1448	1068
65°	2440	1199	961
70°	2267	968	870
75°	2049	854	792
80°	1734	717	687
85°	1212	480	518

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2918 cd/sqm

TEST NUMBER: P927169

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	3.0
10°-20°	1202.7	8.2
20°-30°	1688.5	11.6
30°-40°	1840.5	12.6
40°-50°	1691.7	11.6
50°-60°	1328.5	9.1
60°-70°	864.8	5.9
70°-80°	445.1	3.0
80°-90°	118.7	0.8
90°-100°	110.7	0.8
100°-110°	351.6	2.4
110°-120°	601.7	4.1
120°-130°	791.4	5.4
130°-140°	888.3	6.1
140°-150°	871.1	6.0
150°-160°	730.7	5.0
160°-170°	484.6	3.3
170°-180°	169.4	1.2
0°-30°	3329.2	22.8
0°-40°	5169.8	35.4
0°-60°	8190.0	56.0
0°-90°	9618.6	65.8
90°-120°	1064.0	7.3
90°-150°	3614.9	24.7
90°-180°	5000.0	34.2
0°-180°	14618.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4674	4674	4674	4674	4674	
5°	4674	4653	4598	4636	4624	443
15°	4446	4399	4256	4175	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3477	3262	2889	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1931
65°	1460	1117	736	592	579	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	2	19	53	50	51	14
95°	79	94	96	96	94	88
105°	325	329	332	335	335	343
115°	604	612	610	608	604	597
125°	878	892	888	883	881	785
135°	1136	1153	1156	1154	1150	878
145°	1379	1390	1399	1400	1394	862
155°	1577	1581	1586	1594	1589	726
165°	1716	1714	1714	1725	1717	484
175°	1785	1781	1778	1788	1779	170
180°	1788	1788	1788	1788	1788	

TEST NUMBER: P927169

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4674.4	4674.4	4674.4	4674.4	4674.4
2.5°	4695.5	4674.4	4627.8	4670.4	4661.8
5°	4674.4	4653.3	4598.1	4636.3	4623.7
7.5°	4636.3	4611.1	4551.9	4568.5	4547.4
10°	4585.5	4556.0	4471.5	4458.5	4433.4
12.5°	4522.2	4484.1	4369.6	4344.5	4297.9
15°	4446.0	4399.3	4255.7	4175.3	4133.1
17.5°	4357.1	4289.3	4111.6	4018.7	3951.0
20°	4255.7	4170.8	3959.4	3854.0	3760.6
22.5°	4145.7	4048.3	3802.8	3659.2	3595.9
25°	4035.8	3900.2	3621.0	3447.8	3384.0
27.5°	3904.7	3760.6	3451.8	3253.0	3155.6
30°	3765.1	3604.0	3265.6	3050.1	2935.7
32.5°	3629.6	3434.8	3088.3	2834.3	2728.3
35°	3477.4	3261.5	2889.4	2622.9	2529.5
37.5°	3329.3	3096.4	2703.2	2411.0	2305.5
40°	3172.6	2919.1	2508.5	2208.2	2098.2
42.5°	3011.9	2741.4	2314.1	2000.8	1895.4
45°	2842.8	2559.2	2115.3	1814.6	1713.1
47.5°	2682.1	2381.9	1925.0	1624.3	1531.4
50°	2504.4	2204.1	1738.7	1446.5	1358.1
52.5°	2330.7	2013.4	1561.0	1281.8	1201.5
55°	2161.5	1831.7	1374.7	1121.1	1040.8
57.5°	1988.2	1649.8	1210.0	973.0	905.3
60°	1810.5	1472.1	1036.3	820.9	753.2
62.5°	1637.3	1298.9	888.2	685.4	651.6
65°	1459.6	1116.7	736.1	592.5	579.4
67.5°	1290.4	947.4	592.5	520.2	507.6
70°	1112.6	782.7	490.6	448.3	431.3
72.5°	943.4	630.2	410.2	376.5	368.0
75°	778.2	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	1.6	19.4	52.9	49.6	51.2
92.5°	33.5	45.3	46.9	48.5	48.5
95°	78.7	93.8	96.5	96.5	93.8
97.5°	131.0	145.1	151.0	151.0	151.0
100°	191.4	203.8	208.1	208.1	206.5
102.5°	255.0	264.2	270.1	271.7	270.1
105°	324.6	328.9	332.1	334.9	334.9
107.5°	393.6	400.1	400.1	401.1	393.6
110°	460.5	469.1	469.1	469.1	464.7

TEST NUMBER: P927169

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	532.7	541.8	540.2	535.9	532.7
115°	603.9	612.5	609.8	608.2	603.9
117.5°	674.5	686.4	678.8	674.5	670.2
120°	745.7	757.6	745.7	745.7	740.8
122.5°	810.4	825.4	817.9	813.7	810.4
125°	878.3	891.8	887.5	882.7	881.0
127.5°	944.7	961.4	955.4	949.0	944.7
130°	1006.7	1026.1	1023.4	1020.2	1014.2
132.5°	1076.2	1091.3	1092.4	1084.8	1080.5
135°	1136.1	1152.8	1156.0	1154.4	1150.0
137.5°	1202.9	1216.4	1219.1	1218.0	1211.6
140°	1261.7	1275.2	1282.7	1282.7	1276.8
142.5°	1322.0	1335.5	1339.9	1341.5	1335.5
145°	1379.3	1390.0	1398.7	1400.3	1394.3
147.5°	1430.4	1443.9	1450.4	1453.1	1447.1
150°	1483.3	1492.4	1498.4	1503.2	1498.4
152.5°	1530.1	1539.4	1546.9	1552.9	1546.9
155°	1577.1	1581.4	1586.2	1593.9	1589.0
157.5°	1617.5	1620.8	1623.5	1634.3	1626.8
160°	1653.7	1656.9	1658.5	1667.7	1661.3
162.5°	1687.1	1687.1	1688.7	1699.0	1691.4
165°	1715.6	1714.0	1714.0	1724.9	1717.3
167.5°	1741.6	1736.7	1736.7	1747.5	1739.9
170°	1761.0	1756.6	1755.0	1765.8	1756.6
172.5°	1774.4	1770.1	1768.5	1779.3	1770.1
175°	1785.2	1780.9	1777.6	1788.5	1779.3
177.5°	1791.1	1786.9	1783.6	1792.7	1783.6
180°	1788.5	1788.5	1788.5	1788.5	1788.5

TEST NUMBER: P927169

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.84	13.81	13.65	14.65	15.68	8.81	9.79	9.63	10.62	11.65
	3H	14.53	15.40	15.36	16.24	17.30	10.01	10.89	10.84	11.73	12.79
	4H	15.14	15.97	15.99	16.82	17.89	10.47	11.29	11.32	12.14	13.21
	6H	15.57	16.33	16.43	17.19	18.27	10.80	11.56	11.66	12.42	13.50
	8H	15.70	16.43	16.57	17.30	18.38	10.90	11.62	11.76	12.49	13.58
	12H	15.77	16.46	16.64	17.33	18.43	10.94	11.63	11.82	12.50	13.61
4H	2H	12.87	13.70	13.72	14.55	15.62	9.42	10.25	10.27	11.10	12.17
	3H	14.72	15.40	15.58	16.29	17.37	10.79	11.47	11.65	12.36	13.44
	4H	15.42	16.04	16.29	16.92	18.03	11.34	11.97	12.22	12.85	13.96
	6H	15.94	16.48	16.83	17.38	18.50	11.77	12.31	12.66	13.21	14.33
	8H	16.12	16.62	17.01	17.52	18.65	11.91	12.41	12.80	13.31	14.43
	12H	16.22	16.67	17.13	17.59	18.72	11.98	12.43	12.89	13.35	14.48
8H	4H	15.39	15.90	16.29	16.79	17.92	11.64	12.14	12.53	13.04	14.16
	6H	15.97	16.38	16.89	17.32	18.45	12.16	12.58	13.08	13.52	14.64
	8H	16.19	16.55	17.11	17.49	18.63	12.35	12.72	13.28	13.66	14.80
	12H	16.33	16.65	17.26	17.58	18.77	12.48	12.80	13.41	13.73	14.93
12H	4H	15.35	15.80	16.26	16.72	17.85	11.65	12.10	12.56	13.02	14.15
	6H	15.94	16.31	16.87	17.24	18.39	12.21	12.58	13.14	13.51	14.66
	8H	16.17	16.49	17.10	17.42	18.62	12.43	12.75	13.36	13.68	14.87