

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927170

Luminaire Tested: DFN2DIP-HX4F0-120D060US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927170
REPORT IS A COMBINATION OF REPORTS P900872 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D060US830-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15211.9 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 170.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927170

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927170

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3476	3476	3476
5°	3482	3421	3443
10°	3447	3354	3331
15°	3400	3244	3158
20°	3338	3091	2945
25°	3274	2920	2740
30°	3188	2745	2480
35°	3103	2556	2252
40°	3018	2361	1989
45°	2918	2144	1752
50°	2815	1926	1520
55°	2708	1692	1297
60°	2583	1448	1068
65°	2440	1199	961
70°	2267	968	870
75°	2049	854	792
80°	1734	717	687
85°	1212	480	518

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2918 cd/sqm

TEST NUMBER: P927170

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	2.9
10°-20°	1202.7	7.9
20°-30°	1688.5	11.1
30°-40°	1840.5	12.1
40°-50°	1691.7	11.1
50°-60°	1328.5	8.7
60°-70°	864.8	5.7
70°-80°	445.1	2.9
80°-90°	117.0	0.8
90°-100°	62.9	0.4
100°-110°	234.6	1.5
110°-120°	622.2	4.1
120°-130°	1031.9	6.8
130°-140°	1096.2	7.2
140°-150°	1018.8	6.7
150°-160°	819.1	5.4
160°-170°	527.8	3.5
170°-180°	181.7	1.2
0°-30°	3329.2	21.9
0°-40°	5169.8	34.0
0°-60°	8190.0	53.8
0°-90°	9616.9	63.2
90°-120°	919.7	6.0
90°-150°	4066.6	26.7
90°-180°	5595.0	36.8
0°-180°	15211.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4674	4674	4674	4674	4674	
5°	4674	4653	4598	4636	4624	443
15°	4446	4399	4256	4175	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3477	3262	2889	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1931
65°	1460	1117	736	592	579	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	1	17	28	35	37	14
95°	90	44	54	61	59	106
105°	420	461	84	99	105	449
115°	794	818	852	213	113	782
125°	1123	1141	1167	1177	1181	1001
135°	1389	1412	1424	1438	1435	1073
145°	1612	1610	1634	1643	1636	1008
155°	1774	1762	1779	1787	1776	818
165°	1870	1862	1866	1875	1866	528
175°	1913	1903	1906	1915	1902	182
180°	1908	1908	1908	1908	1908	

TEST NUMBER: P927170

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4674.4	4674.4	4674.4	4674.4	4674.4
2.5°	4695.5	4674.4	4627.8	4670.4	4661.8
5°	4674.4	4653.3	4598.1	4636.3	4623.7
7.5°	4636.3	4611.1	4551.9	4568.5	4547.4
10°	4585.5	4556.0	4471.5	4458.5	4433.4
12.5°	4522.2	4484.1	4369.6	4344.5	4297.9
15°	4446.0	4399.3	4255.7	4175.3	4133.1
17.5°	4357.1	4289.3	4111.6	4018.7	3951.0
20°	4255.7	4170.8	3959.4	3854.0	3760.6
22.5°	4145.7	4048.3	3802.8	3659.2	3595.9
25°	4035.8	3900.2	3621.0	3447.8	3384.0
27.5°	3904.7	3760.6	3451.8	3253.0	3155.6
30°	3765.1	3604.0	3265.6	3050.1	2935.7
32.5°	3629.6	3434.8	3088.3	2834.3	2728.3
35°	3477.4	3261.5	2889.4	2622.9	2529.5
37.5°	3329.3	3096.4	2703.2	2411.0	2305.5
40°	3172.6	2919.1	2508.5	2208.2	2098.2
42.5°	3011.9	2741.4	2314.1	2000.8	1895.4
45°	2842.8	2559.2	2115.3	1814.6	1713.1
47.5°	2682.1	2381.9	1925.0	1624.3	1531.4
50°	2504.4	2204.1	1738.7	1446.5	1358.1
52.5°	2330.7	2013.4	1561.0	1281.8	1201.5
55°	2161.5	1831.7	1374.7	1121.1	1040.8
57.5°	1988.2	1649.8	1210.0	973.0	905.3
60°	1810.5	1472.1	1036.3	820.9	753.2
62.5°	1637.3	1298.9	888.2	685.4	651.6
65°	1459.6	1116.7	736.1	592.5	579.4
67.5°	1290.4	947.4	592.5	520.2	507.6
70°	1112.6	782.7	490.6	448.3	431.3
72.5°	943.4	630.2	410.2	376.5	368.0
75°	778.2	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	1.3	16.6	27.5	34.6	37.2
92.5°	34.6	29.0	33.1	35.9	37.2
95°	89.7	44.1	53.8	60.9	59.4
97.5°	161.5	48.4	70.3	74.6	76.0
100°	244.5	55.2	78.7	89.7	92.5
102.5°	335.5	332.9	81.5	96.6	100.8
105°	419.8	461.3	84.3	99.3	105.0
107.5°	517.9	552.3	87.1	102.2	107.7
110°	611.9	640.7	241.8	103.7	109.0



TEST NUMBER: P927170

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	700.2	725.0	701.5	106.2	110.6
115°	794.1	817.5	852.1	212.7	113.3
117.5°	875.5	903.1	926.7	729.1	367.3
120°	966.7	987.4	1012.3	1028.8	842.4
122.5°	1043.9	1066.1	1093.8	1102.0	1103.5
125°	1122.7	1140.7	1166.9	1176.6	1180.7
127.5°	1194.5	1213.8	1234.7	1248.4	1249.8
130°	1262.2	1284.3	1299.4	1314.7	1313.4
132.5°	1331.3	1349.3	1364.4	1376.8	1375.5
135°	1389.3	1411.5	1423.7	1437.7	1434.9
137.5°	1449.9	1466.5	1480.5	1494.2	1490.2
140°	1509.3	1520.5	1535.6	1548.1	1541.2
142.5°	1559.2	1568.9	1586.8	1597.7	1590.8
145°	1611.7	1610.2	1633.6	1643.3	1636.5
147.5°	1657.1	1653.0	1676.4	1683.3	1677.9
150°	1701.4	1691.7	1713.8	1722.0	1715.2
152.5°	1738.6	1727.6	1748.2	1756.6	1746.9
155°	1774.5	1762.2	1778.8	1787.0	1776.0
157.5°	1803.6	1792.5	1805.0	1814.7	1803.6
160°	1828.4	1820.1	1828.4	1836.6	1827.0
162.5°	1850.4	1842.2	1849.1	1858.8	1846.4
165°	1869.8	1861.6	1865.7	1875.4	1865.7
167.5°	1885.0	1876.7	1880.9	1890.7	1878.1
170°	1897.5	1889.1	1892.0	1901.6	1889.1
172.5°	1905.7	1897.5	1900.3	1910.0	1897.5
175°	1912.6	1902.9	1905.7	1915.3	1901.6
177.5°	1915.3	1905.7	1907.1	1916.9	1904.4
180°	1908.5	1908.5	1908.5	1908.5	1908.5

TEST NUMBER: P927170

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.63	13.58	13.47	14.44	15.51	8.60	9.55	9.44	10.41	11.48
	3H	14.32	15.17	15.17	16.04	17.14	9.80	10.65	10.66	11.52	12.62
	4H	14.93	15.73	15.80	16.61	17.72	10.26	11.06	11.13	11.94	13.05
	6H	15.36	16.10	16.24	16.98	18.10	10.59	11.33	11.47	12.21	13.33
	8H	15.49	16.19	16.38	17.09	18.22	10.68	11.38	11.57	12.28	13.41
	12H	15.56	16.23	16.45	17.12	18.27	10.73	11.40	11.63	12.29	13.44
4H	2H	12.66	13.46	13.54	14.34	15.45	9.21	10.02	10.09	10.89	12.00
	3H	14.50	15.17	15.39	16.08	17.20	10.58	11.24	11.46	12.15	13.27
	4H	15.20	15.81	16.10	16.71	17.86	11.13	11.74	12.03	12.64	13.79
	6H	15.72	16.25	16.64	17.17	18.33	11.56	12.08	12.47	13.01	14.16
	8H	15.90	16.39	16.82	17.31	18.48	11.69	12.18	12.61	13.10	14.27
	12H	16.00	16.44	16.94	17.38	18.55	11.76	12.20	12.70	13.14	14.31
8H	4H	15.18	15.67	16.09	16.59	17.75	11.42	11.91	12.33	12.83	14.00
	6H	15.75	16.15	16.69	17.12	18.28	11.94	12.35	12.89	13.31	14.48
	8H	15.97	16.32	16.92	17.28	18.46	12.14	12.49	13.09	13.45	14.63
	12H	16.11	16.43	17.07	17.37	18.61	12.26	12.58	13.22	13.52	14.76
12H	4H	15.14	15.57	16.07	16.51	17.69	11.43	11.87	12.36	12.81	13.98
	6H	15.73	16.08	16.68	17.04	18.22	11.99	12.35	12.95	13.31	14.49
	8H	15.95	16.27	16.91	17.21	18.45	12.21	12.53	13.17	13.47	14.71

END OF REPORT