

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927178

Luminaire Tested: DFN2DIP-HX4F0-120D080US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927178
REPORT IS A COMBINATION OF REPORTS P900908 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D080US830-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17078.1 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 184.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927178

CATALOG NUMBER: DFN2DIP-HX4F0-120D080US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927178

CATALOG NUMBER: DFN2DIP-HX4F0-120D080US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3476	3476	3476
5°	3482	3421	3443
10°	3447	3354	3331
15°	3400	3244	3158
20°	3338	3091	2945
25°	3274	2920	2740
30°	3188	2745	2480
35°	3103	2556	2252
40°	3018	2361	1989
45°	2918	2144	1752
50°	2815	1926	1520
55°	2708	1692	1297
60°	2583	1448	1068
65°	2440	1199	961
70°	2267	968	870
75°	2049	854	792
80°	1734	717	687
85°	1212	480	518

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2918 cd/sqm

TEST NUMBER: P927178

CATALOG NUMBER: DFN2DIP-HX4F0-120D080US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	2.6
10°-20°	1202.7	7.0
20°-30°	1688.5	9.9
30°-40°	1840.5	10.8
40°-50°	1691.7	9.9
50°-60°	1328.5	7.8
60°-70°	864.8	5.1
70°-80°	445.1	2.6
80°-90°	118.1	0.7
90°-100°	83.9	0.5
100°-110°	312.8	1.8
110°-120°	829.6	4.9
120°-130°	1375.9	8.1
130°-140°	1461.6	8.6
140°-150°	1358.3	8.0
150°-160°	1092.1	6.4
160°-170°	703.7	4.1
170°-180°	242.2	1.4
0°-30°	3329.2	19.5
0°-40°	5169.8	30.3
0°-60°	8190.0	48.0
0°-90°	9618.0	56.3
90°-120°	1226.3	7.2
90°-150°	5422.1	31.7
90°-180°	7460.0	43.7
0°-180°	17078.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4674	4674	4674	4674	4674	
5°	4674	4653	4598	4636	4624	443
15°	4446	4399	4256	4175	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3477	3262	2889	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1931
65°	1460	1117	736	592	579	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	2	22	37	46	50	16
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2500	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	

TEST NUMBER: P927178

CATALOG NUMBER: DFN2DIP-HX4F0-120D080US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4674.4	4674.4	4674.4	4674.4	4674.4
2.5°	4695.5	4674.4	4627.8	4670.4	4661.8
5°	4674.4	4653.3	4598.1	4636.3	4623.7
7.5°	4636.3	4611.1	4551.9	4568.5	4547.4
10°	4585.5	4556.0	4471.5	4458.5	4433.4
12.5°	4522.2	4484.1	4369.6	4344.5	4297.9
15°	4446.0	4399.3	4255.7	4175.3	4133.1
17.5°	4357.1	4289.3	4111.6	4018.7	3951.0
20°	4255.7	4170.8	3959.4	3854.0	3760.6
22.5°	4145.7	4048.3	3802.8	3659.2	3595.9
25°	4035.8	3900.2	3621.0	3447.8	3384.0
27.5°	3904.7	3760.6	3451.8	3253.0	3155.6
30°	3765.1	3604.0	3265.6	3050.1	2935.7
32.5°	3629.6	3434.8	3088.3	2834.3	2728.3
35°	3477.4	3261.5	2889.4	2622.9	2529.5
37.5°	3329.3	3096.4	2703.2	2411.0	2305.5
40°	3172.6	2919.1	2508.5	2208.2	2098.2
42.5°	3011.9	2741.4	2314.1	2000.8	1895.4
45°	2842.8	2559.2	2115.3	1814.6	1713.1
47.5°	2682.1	2381.9	1925.0	1624.3	1531.4
50°	2504.4	2204.1	1738.7	1446.5	1358.1
52.5°	2330.7	2013.4	1561.0	1281.8	1201.5
55°	2161.5	1831.7	1374.7	1121.1	1040.8
57.5°	1988.2	1649.8	1210.0	973.0	905.3
60°	1810.5	1472.1	1036.3	820.9	753.2
62.5°	1637.3	1298.9	888.2	685.4	651.6
65°	1459.6	1116.7	736.1	592.5	579.4
67.5°	1290.4	947.4	592.5	520.2	507.6
70°	1112.6	782.7	490.6	448.3	431.3
72.5°	943.4	630.2	410.2	376.5	368.0
75°	778.2	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.1	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.7	134.5
105°	559.8	615.1	112.3	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.8	854.3	322.3	138.2	145.4

TEST NUMBER: P927178

CATALOG NUMBER: DFN2DIP-HX4F0-120D080US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	933.6	966.6	935.4	141.7	147.4
115°	1058.7	1090.0	1136.1	283.6	151.1
117.5°	1167.4	1204.1	1235.6	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.8	1123.2
122.5°	1391.9	1421.5	1458.4	1469.4	1471.3
125°	1496.9	1520.9	1555.9	1568.8	1574.3
127.5°	1592.6	1618.5	1646.3	1664.5	1666.3
130°	1682.9	1712.4	1732.6	1753.0	1751.2
132.5°	1775.0	1799.0	1819.2	1835.8	1834.0
135°	1852.4	1881.9	1898.3	1917.0	1913.2
137.5°	1933.4	1955.4	1974.0	1992.4	1986.9
140°	2012.4	2027.3	2047.5	2064.1	2054.8
142.5°	2079.0	2091.8	2115.6	2130.3	2121.1
145°	2148.9	2146.9	2178.2	2191.1	2181.9
147.5°	2209.5	2204.0	2235.2	2244.5	2237.2
150°	2268.5	2255.6	2285.1	2296.0	2286.9
152.5°	2318.2	2303.5	2331.0	2342.2	2329.3
155°	2366.1	2349.7	2371.7	2382.6	2368.0
157.5°	2404.7	2390.1	2406.7	2419.6	2404.7
160°	2438.0	2426.8	2438.0	2448.9	2436.0
162.5°	2467.3	2456.3	2465.5	2478.4	2461.8
165°	2493.1	2482.2	2487.6	2500.5	2487.6
167.5°	2513.4	2502.2	2507.9	2520.8	2504.2
170°	2530.0	2518.8	2522.6	2535.5	2518.8
172.5°	2541.0	2530.0	2533.7	2546.6	2530.0
175°	2550.1	2537.2	2541.0	2553.8	2535.5
177.5°	2553.8	2541.0	2542.9	2555.8	2539.2
180°	2544.7	2544.7	2544.7	2544.7	2544.7

TEST NUMBER: P927178

CATALOG NUMBER: DFN2DIP-HX4F0-120D080US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.05	12.93	12.95	13.85	15.03	8.02	8.90	8.93	9.83	11.01
	3H	13.73	14.52	14.65	15.45	16.66	9.21	10.01	10.13	10.94	12.14
	4H	14.34	15.09	15.28	16.02	17.24	9.67	10.42	10.60	11.35	12.57
	6H	14.77	15.45	15.71	16.40	17.62	9.99	10.68	10.94	11.62	12.85
	8H	14.89	15.55	15.85	16.51	17.73	10.09	10.74	11.04	11.70	12.93
	12H	14.96	15.58	15.92	16.53	17.78	10.13	10.76	11.09	11.71	12.96
4H	2H	12.07	12.82	13.01	13.76	14.97	8.62	9.37	9.56	10.31	11.52
	3H	13.91	14.53	14.86	15.50	16.72	9.98	10.60	10.93	11.57	12.80
	4H	14.60	15.17	15.56	16.13	17.38	10.53	11.10	11.49	12.06	13.31
	6H	15.12	15.61	16.09	16.59	17.85	10.96	11.44	11.93	12.43	13.68
	8H	15.30	15.75	16.27	16.73	18.00	11.09	11.54	12.06	12.52	13.79
	12H	15.40	15.81	16.39	16.80	18.07	11.15	11.56	12.15	12.56	13.83
8H	4H	14.57	15.03	15.55	16.01	17.28	10.82	11.27	11.79	12.25	13.52
	6H	15.14	15.52	16.14	16.54	17.81	11.34	11.71	12.34	12.73	14.00
	8H	15.36	15.69	16.37	16.70	17.99	11.53	11.86	12.54	12.87	14.15
	12H	15.50	15.79	16.51	16.80	18.13	11.65	11.95	12.66	12.95	14.28
12H	4H	14.53	14.94	15.52	15.93	17.21	10.82	11.23	11.82	12.23	13.50
	6H	15.12	15.45	16.13	16.46	17.74	11.39	11.72	12.40	12.73	14.01
	8H	15.34	15.64	16.35	16.64	17.97	11.60	11.89	12.61	12.90	14.23

END OF REPORT