

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908013

Luminaire Tested: DFN2DIP-HX3F0-040D060US840-RLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P908013  
REPORT IS A COMBINATION OF REPORTS P900766 AND P897645  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-040D060US840-RLONL  
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9432.1 lumens  
Efficiency: N/A  
Efficacy: 118.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 79.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P908013  
CATALOG NUMBER: DFN2DIP-HX3F0-040D060US840-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P908013  
 CATALOG NUMBER: DFN2DIP-HX3F0-040D060US840-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36			36
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31			31
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32	27			27
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28	23			23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20			20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18			18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16			16
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14			14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13			13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12			12
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13	11			11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1934	1934	1934
5°	1936	1902	1914
10°	1916	1863	1851
15°	1889	1800	1754
20°	1853	1714	1635
25°	1816	1618	1520
30°	1767	1519	1374
35°	1720	1413	1247
40°	1671	1304	1101
45°	1614	1183	968
50°	1555	1060	839
55°	1494	930	715
60°	1423	793	587
65°	1341	655	527
70°	1242	526	476
75°	1117	461	431
80°	936	382	370
85°	639	249	272

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1614 cd/sqm



TEST NUMBER: P908013

CATALOG NUMBER: DFN2DIP-HX3F0-040D060US840-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.5	1.7
10°-20°	429.5	4.6
20°-30°	603.0	6.4
30°-40°	657.4	7.0
40°-50°	604.2	6.4
50°-60°	474.5	5.0
60°-70°	308.9	3.3
70°-80°	159.0	1.7
80°-90°	44.2	0.5
90°-100°	67.4	0.7
100°-110°	251.4	2.7
110°-120°	666.7	7.1
120°-130°	1105.7	11.7
130°-140°	1174.5	12.5
140°-150°	1091.6	11.6
150°-160°	877.6	9.3
160°-170°	565.5	6.0
170°-180°	194.6	2.1
0°-30°	1189.0	12.6
0°-40°	1846.4	19.6
0°-60°	2925.1	31.0
0°-90°	3437.1	36.4
90°-120°	985.5	10.4
90°-150°	4357.2	46.2
90°-180°	5995.0	63.6
0°-180°	9432.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1670	1670	1670	1670	1670	
5°	1670	1662	1642	1656	1651	158
15°	1588	1571	1520	1491	1476	447
25°	1441	1393	1293	1231	1209	663
35°	1242	1165	1032	937	903	777
45°	1015	914	756	648	612	784
55°	772	654	491	400	372	690
65°	521	399	263	212	207	517
75°	278	172	121	110	109	294
85°	65	33	29	29	29	75
90°	1	18	30	37	40	9
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1489	1512	1526	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2004	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2038	195
180°	2045	2045	2045	2045	2045	



TEST NUMBER: P908013

CATALOG NUMBER: DFN2DIP-HX3F0-040D060US840-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1669.5	1669.5	1669.5	1669.5	1669.5
2.5°	1677.1	1669.5	1652.8	1668.1	1665.0
5°	1669.5	1661.9	1642.2	1655.9	1651.4
7.5°	1655.9	1646.9	1625.8	1631.6	1624.2
10°	1637.8	1627.2	1597.0	1592.4	1583.5
12.5°	1615.2	1601.5	1560.6	1551.7	1535.0
15°	1587.9	1571.2	1519.9	1491.3	1476.2
17.5°	1556.2	1532.0	1468.4	1435.3	1411.1
20°	1519.9	1489.7	1414.1	1376.4	1343.1
22.5°	1480.7	1445.9	1358.2	1306.9	1284.3
25°	1441.4	1393.0	1293.2	1231.4	1208.6
27.5°	1394.6	1343.1	1232.8	1161.9	1127.0
30°	1344.7	1287.2	1166.3	1089.3	1048.5
32.5°	1296.4	1226.8	1103.0	1012.3	974.4
35°	1242.0	1164.9	1032.0	936.8	903.4
37.5°	1189.1	1105.9	965.4	861.1	823.4
40°	1133.2	1042.6	896.0	788.7	749.4
42.5°	1075.7	979.1	826.5	714.6	676.9
45°	1015.3	914.0	755.5	648.1	611.9
47.5°	958.0	850.7	687.5	580.2	546.9
50°	894.4	787.2	621.0	516.6	485.0
52.5°	832.4	719.1	557.5	457.8	429.1
55°	772.0	654.2	491.0	400.4	371.7
57.5°	710.1	589.3	432.1	347.5	323.4
60°	646.6	525.7	370.1	293.2	269.0
62.5°	584.8	463.9	317.2	244.8	232.8
65°	521.3	398.8	262.9	211.6	206.9
67.5°	460.9	338.4	211.6	185.8	181.3
70°	397.4	279.5	175.2	160.2	154.0
72.5°	337.0	225.1	146.5	134.5	131.5
75°	277.9	172.2	120.9	110.3	108.9
77.5°	219.1	122.3	95.2	89.2	86.0
80°	164.6	87.7	72.4	66.6	66.6
82.5°	114.8	59.0	49.9	46.8	46.8
85°	64.9	33.2	28.7	28.7	28.7
87.5°	24.2	12.0	12.0	10.6	10.6
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	262.0	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.4	103.5	108.1
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.8	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8



TEST NUMBER: P908013

CATALOG NUMBER: DFN2DIP-HX3F0-040D060US840-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.8	751.6	113.8	118.5
115°	850.8	876.0	913.0	227.9	121.4
117.5°	938.1	967.7	992.9	781.2	393.5
120°	1035.8	1057.9	1084.7	1102.4	902.6
122.5°	1118.5	1142.3	1171.9	1180.7	1182.4
125°	1203.0	1222.2	1250.3	1260.7	1265.1
127.5°	1279.9	1300.6	1322.9	1337.7	1339.1
130°	1352.4	1376.1	1392.3	1408.7	1407.2
132.5°	1426.4	1445.7	1461.9	1475.2	1473.8
135°	1488.6	1512.4	1525.5	1540.4	1537.4
137.5°	1553.6	1571.4	1586.3	1601.0	1596.7
140°	1617.2	1629.2	1645.4	1658.7	1651.3
142.5°	1670.6	1681.0	1700.2	1711.9	1704.6
145°	1726.9	1725.3	1750.4	1760.8	1753.4
147.5°	1775.5	1771.1	1796.2	1803.6	1797.9
150°	1823.0	1812.6	1836.3	1845.1	1837.8
152.5°	1862.9	1851.1	1873.2	1882.2	1871.8
155°	1901.4	1888.1	1905.9	1914.7	1902.9
157.5°	1932.5	1920.7	1934.0	1944.4	1932.5
160°	1959.1	1950.2	1959.1	1967.9	1957.6
162.5°	1982.7	1973.9	1981.3	1991.7	1978.3
165°	2003.5	1994.7	1999.0	2009.4	1999.0
167.5°	2019.7	2010.8	2015.4	2025.8	2012.4
170°	2033.2	2024.2	2027.2	2037.5	2024.2
172.5°	2041.9	2033.2	2036.1	2046.5	2033.2
175°	2049.3	2038.9	2041.9	2052.2	2037.5
177.5°	2052.2	2041.9	2043.5	2053.9	2040.5
180°	2044.9	2044.9	2044.9	2044.9	2044.9



TEST NUMBER: P908013  
 CATALOG NUMBER: DFN2DIP-HX3F0-040D060US840-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.98	8.71	9.05	9.78	11.23	3.96	4.69	5.03	5.76	7.21
	3H	9.64	10.30	10.72	11.37	12.85	5.13	5.79	6.21	6.86	8.34
	4H	10.24	10.86	11.33	11.94	13.42	5.58	6.19	6.67	7.27	8.75
	6H	10.65	11.22	11.75	12.30	13.79	5.89	6.46	6.99	7.54	9.03
	8H	10.77	11.31	11.88	12.41	13.90	5.97	6.52	7.08	7.61	9.10
	12H	10.83	11.34	11.93	12.43	13.94	6.01	6.53	7.12	7.62	9.13
4H	2H	7.98	8.60	9.08	9.68	11.16	4.53	5.15	5.63	6.23	7.71
	3H	9.80	10.31	10.90	11.42	12.91	5.87	6.39	6.98	7.49	8.98
	4H	10.48	10.95	11.59	12.05	13.56	6.41	6.88	7.52	7.98	9.49
	6H	10.98	11.39	12.10	12.50	14.01	6.82	7.23	7.94	8.34	9.85
	8H	11.15	11.53	12.27	12.64	14.16	6.95	7.32	8.06	8.43	9.95
	12H	11.24	11.58	12.37	12.70	14.23	7.00	7.34	8.14	8.47	9.99
8H	4H	10.44	10.82	11.55	11.93	13.45	6.68	7.06	7.80	8.17	9.69
	6H	10.99	11.30	12.13	12.46	13.97	7.19	7.50	8.33	8.65	10.17
	8H	11.20	11.48	12.35	12.61	14.15	7.38	7.65	8.52	8.78	10.32
	12H	11.33	11.57	12.48	12.70	14.28	7.49	7.73	8.63	8.86	10.43
12H	4H	10.39	10.73	11.52	11.85	13.38	6.68	7.02	7.81	8.14	9.67
	6H	10.97	11.24	12.11	12.37	13.91	7.24	7.51	8.38	8.64	10.18
	8H	11.18	11.42	12.32	12.55	14.12	7.44	7.68	8.58	8.81	10.38