

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927192

Luminaire Tested: DFN2DIP-HX4F0-120D120US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927192
REPORT IS A COMBINATION OF REPORTS P900979 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D120US830-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22393.8 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 222.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927192

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927192

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3272	3272	3272
5°	3278	3227	3249
10°	3251	3184	3205
15°	3204	3132	3136
20°	3140	3059	3066
25°	3076	2972	2985
30°	2995	2892	2882
35°	2919	2796	2772
40°	2826	2700	2668
45°	2732	2604	2562
50°	2630	2503	2439
55°	2523	2386	2326
60°	2403	2247	2196
65°	2271	2103	2043
70°	2104	1928	1879
75°	1871	1718	1727
80°	1592	1451	1437
85°	1155	988	956

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2732 cd/sqm

TEST NUMBER: P927192

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.2	1.8
10°-20°	1165.4	5.2
20°-30°	1712.7	7.6
30°-40°	1989.2	8.9
40°-50°	1986.7	8.9
50°-60°	1732.3	7.7
60°-70°	1280.6	5.7
70°-80°	724.5	3.2
80°-90°	197.9	0.9
90°-100°	125.9	0.6
100°-110°	469.2	2.1
110°-120°	1244.4	5.6
120°-130°	2063.9	9.2
130°-140°	2192.3	9.8
140°-150°	2037.5	9.1
150°-160°	1638.1	7.3
160°-170°	1055.6	4.7
170°-180°	363.3	1.6
0°-30°	3292.3	14.7
0°-40°	5281.5	23.6
0°-60°	9000.5	40.2
0°-90°	11203.6	50.0
90°-120°	1839.4	8.2
90°-150°	8133.2	36.3
90°-180°	11190.0	50.0
0°-180°	22393.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4401	4401	4401	4401	4401	
5°	4401	4384	4338	4371	4363	418
15°	4189	4164	4109	4126	4105	1180
25°	3792	3758	3686	3694	3686	1745
35°	3271	3229	3161	3136	3114	2043
45°	2662	2632	2568	2522	2505	2054
55°	2014	1989	1938	1888	1866	1801
65°	1359	1333	1291	1253	1232	1343
75°	711	703	681	656	664	759
85°	173	169	165	152	148	193
90°	3	33	55	69	74	21
95°	179	88	108	122	119	212
105°	840	923	169	199	210	897
115°	1588	1635	1704	425	227	1563
125°	2245	2281	2334	2353	2361	2003
135°	2779	2823	2848	2875	2870	2146
145°	3223	3220	3267	3287	3273	2016
155°	3549	3524	3558	3574	3552	1635
165°	3740	3723	3731	3751	3731	1057
175°	3825	3806	3811	3831	3803	364
180°	3817	3817	3817	3817	3817	

TEST NUMBER: P927192

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4400.8	4400.8	4400.8	4400.8	4400.8
2.5°	4426.4	4405.2	4358.6	4400.8	4392.7
5°	4400.8	4384.1	4337.5	4371.1	4363.0
7.5°	4371.1	4346.0	4299.3	4333.4	4324.9
10°	4324.9	4295.3	4244.5	4278.2	4265.7
12.5°	4261.1	4236.0	4185.3	4206.4	4197.8
15°	4189.3	4164.2	4108.9	4126.0	4104.9
17.5°	4100.4	4075.3	4020.0	4041.2	4020.0
20°	4003.0	3977.8	3918.6	3931.2	3914.6
22.5°	3906.0	3867.8	3812.6	3812.6	3804.1
25°	3791.5	3757.8	3686.0	3694.1	3686.0
27.5°	3664.4	3634.8	3580.1	3567.5	3546.4
30°	3537.9	3503.7	3440.4	3427.9	3410.8
32.5°	3402.2	3377.2	3309.3	3283.8	3266.7
35°	3271.1	3229.0	3161.1	3135.6	3114.5
37.5°	3123.0	3084.9	3017.0	2987.4	2966.3
40°	2970.9	2936.7	2868.9	2831.2	2814.1
42.5°	2822.7	2788.6	2721.2	2678.6	2653.4
45°	2661.9	2632.3	2568.5	2522.3	2505.3
47.5°	2505.3	2475.6	2407.8	2361.2	2336.0
50°	2340.0	2318.9	2259.6	2200.4	2179.2
52.5°	2179.2	2149.7	2094.9	2048.1	2018.6
55°	2014.5	1989.0	1938.2	1887.5	1866.3
57.5°	1849.3	1828.2	1772.9	1722.2	1705.2
60°	1684.1	1667.5	1608.2	1561.5	1548.9
62.5°	1523.4	1493.7	1451.5	1409.3	1392.3
65°	1358.6	1333.0	1290.8	1252.6	1231.6
67.5°	1189.3	1167.8	1130.1	1100.5	1083.4
70°	1032.6	1015.5	977.4	947.8	931.2
72.5°	871.9	854.8	833.7	804.1	791.5
75°	710.7	702.6	681.1	656.0	664.5
77.5°	567.0	549.9	541.5	528.8	516.3
80°	423.4	418.8	410.4	397.8	389.3
82.5°	287.7	287.7	283.8	266.7	266.7
85°	173.3	169.3	165.2	152.2	148.2
87.5°	76.3	67.8	59.3	46.7	42.2
90°	2.6	33.1	55.1	69.2	74.5
92.5°	69.2	58.1	66.3	71.8	74.5
95°	179.4	88.2	107.5	121.7	118.8
97.5°	323.1	96.8	140.7	149.2	151.8
100°	489.0	110.6	157.4	179.4	185.0
102.5°	671.1	665.8	163.0	193.2	201.7
105°	839.6	922.6	168.6	198.8	209.9
107.5°	1035.7	1104.6	174.2	204.3	215.5
110°	1223.6	1281.4	483.4	207.3	218.1

TEST NUMBER: P927192

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1400.5	1449.9	1403.1	212.5	221.0
115°	1588.0	1635.0	1704.1	425.4	226.7
117.5°	1751.1	1806.2	1853.4	1458.1	734.7
120°	1933.4	1974.7	2024.6	2057.8	1684.8
122.5°	2087.9	2132.2	2187.6	2204.0	2207.0
125°	2245.3	2281.4	2333.9	2353.2	2361.4
127.5°	2389.0	2427.7	2469.4	2496.9	2499.5
130°	2524.4	2568.7	2598.8	2629.4	2626.7
132.5°	2662.5	2698.6	2728.7	2753.7	2751.1
135°	2778.6	2822.9	2847.5	2875.4	2869.8
137.5°	2900.0	2933.1	2961.0	2988.5	2980.3
140°	3018.7	3041.0	3071.1	3096.1	3082.4
142.5°	3118.4	3137.8	3173.5	3195.5	3181.7
145°	3223.4	3220.4	3267.3	3286.7	3272.8
147.5°	3314.2	3306.0	3352.9	3366.7	3355.9
150°	3402.7	3383.4	3427.7	3444.1	3430.3
152.5°	3477.2	3455.2	3496.6	3513.3	3493.9
155°	3549.0	3524.4	3557.6	3574.0	3552.0
157.5°	3607.0	3585.1	3610.1	3629.4	3607.0
160°	3656.9	3640.2	3656.9	3673.3	3654.0
162.5°	3700.9	3684.5	3698.3	3717.6	3692.7
165°	3739.6	3723.2	3731.4	3750.8	3731.4
167.5°	3770.1	3753.3	3761.9	3781.2	3756.3
170°	3795.0	3778.3	3783.9	3803.2	3778.3
172.5°	3811.4	3795.0	3800.6	3820.0	3795.0
175°	3825.1	3805.8	3811.4	3830.8	3803.2
177.5°	3830.8	3811.4	3814.4	3833.7	3808.8
180°	3817.0	3817.0	3817.0	3817.0	3817.0

TEST NUMBER: P927192

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.39	12.26	12.35	13.23	14.50	10.96	11.82	11.92	12.80	14.07
	3H	13.06	13.83	14.02	14.81	16.10	12.58	13.36	13.55	14.34	15.63
	4H	13.64	14.38	14.63	15.36	16.66	13.17	13.90	14.15	14.89	16.19
	6H	14.04	14.72	15.04	15.71	17.02	13.57	14.24	14.56	15.23	16.55
	8H	14.15	14.79	15.15	15.80	17.11	13.67	14.32	14.67	15.32	16.63
	12H	14.20	14.81	15.20	15.81	17.15	13.72	14.33	14.72	15.33	16.66
4H	2H	11.86	12.59	12.84	13.57	14.88	11.51	12.24	12.50	13.23	14.53
	3H	13.72	14.33	14.72	15.35	16.66	13.33	13.94	14.33	14.96	16.27
	4H	14.44	15.00	15.44	16.00	17.34	14.03	14.59	15.04	15.60	16.94
	6H	14.96	15.44	15.97	16.47	17.80	14.55	15.03	15.56	16.06	17.39
	8H	15.11	15.55	16.12	16.58	17.93	14.69	15.14	15.71	16.17	17.52
	12H	15.18	15.58	16.22	16.62	17.98	14.76	15.16	15.79	16.20	17.56
8H	4H	14.64	15.09	15.65	16.11	17.46	14.28	14.73	15.29	15.75	17.10
	6H	15.27	15.64	16.31	16.71	18.05	14.91	15.28	15.95	16.34	17.69
	8H	15.49	15.82	16.54	16.87	18.24	15.12	15.45	16.17	16.50	17.87
	12H	15.62	15.91	16.68	16.96	18.37	15.24	15.53	16.29	16.57	17.98
12H	4H	14.62	15.03	15.66	16.07	17.42	14.27	14.68	15.31	15.72	17.07
	6H	15.30	15.63	16.35	16.68	18.05	14.95	15.27	16.00	16.33	17.69
	8H	15.54	15.83	16.60	16.88	18.29	15.18	15.47	16.24	16.52	17.93

END OF REPORT