

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908048

Luminaire Tested: DFN2DIP-HX3F0-060D030US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908048
REPORT IS A COMBINATION OF REPORTS P899208 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-060D030US840-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7831.5 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 79.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908048
CATALOG NUMBER: DFN2DIP-HX3F0-060D030US840-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P908048

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US840-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66				66
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	57				57
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52	49				49
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45	42				42
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40	36				36
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32				32
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31	29				29
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28	26				26
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25	23				23
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23	21				21
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19				19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2901	2901	2901
5°	2904	2853	2871
10°	2874	2795	2776
15°	2833	2700	2630
20°	2780	2571	2452
25°	2725	2427	2280
30°	2651	2279	2062
35°	2579	2120	1870
40°	2506	1956	1651
45°	2421	1774	1452
50°	2333	1590	1258
55°	2241	1395	1072
60°	2134	1190	881
65°	2011	983	791
70°	1862	789	714
75°	1675	691	646
80°	1404	574	555
85°	960	373	407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2421 cd/sqm



TEST NUMBER: P908048

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	3.0
10°-20°	644.3	8.2
20°-30°	904.6	11.6
30°-40°	986.1	12.6
40°-50°	906.3	11.6
50°-60°	711.7	9.1
60°-70°	463.3	5.9
70°-80°	238.5	3.0
80°-90°	63.6	0.8
90°-100°	59.3	0.8
100°-110°	188.4	2.4
110°-120°	322.4	4.1
120°-130°	424.0	5.4
130°-140°	475.9	6.1
140°-150°	466.7	6.0
150°-160°	391.5	5.0
160°-170°	259.6	3.3
170°-180°	90.7	1.2
0°-30°	1783.6	22.8
0°-40°	2769.6	35.4
0°-60°	4387.7	56.0
0°-90°	5153.0	65.8
90°-120°	570.1	7.3
90°-150°	1936.6	24.7
90°-180°	2678.0	34.2
0°-180°	7831.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2504	2504	2504	2504	2504	
5°	2504	2493	2463	2484	2477	237
15°	2382	2357	2280	2237	2214	671
25°	2162	2090	1940	1847	1813	994
35°	1863	1747	1548	1405	1355	1166
45°	1523	1371	1133	972	918	1176
55°	1158	981	736	601	558	1035
65°	782	598	394	317	310	775
75°	417	258	181	165	163	441
85°	97	50	43	43	43	112
90°	1	10	28	27	28	8
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	



TEST NUMBER: P908048

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2504.3	2504.3	2504.3	2504.3	2504.3
2.5°	2515.6	2504.3	2479.2	2502.0	2497.5
5°	2504.3	2493.0	2463.4	2483.9	2477.1
7.5°	2483.9	2470.3	2438.6	2447.5	2436.2
10°	2456.6	2440.7	2395.6	2388.6	2375.1
12.5°	2422.8	2402.3	2341.0	2327.5	2302.5
15°	2381.9	2356.8	2279.9	2236.9	2214.2
17.5°	2334.3	2297.9	2202.7	2152.9	2116.7
20°	2279.9	2234.4	2121.2	2064.7	2014.7
22.5°	2221.0	2168.8	2037.3	1960.4	1926.4
25°	2162.1	2089.5	1940.0	1847.1	1813.0
27.5°	2091.9	2014.7	1849.3	1742.7	1690.6
30°	2017.1	1930.8	1749.5	1634.1	1572.8
32.5°	1944.5	1840.2	1654.6	1518.4	1461.7
35°	1863.0	1747.4	1548.0	1405.1	1355.1
37.5°	1783.6	1658.8	1448.2	1291.7	1235.2
40°	1699.7	1563.9	1343.8	1183.0	1124.1
42.5°	1613.7	1468.6	1239.7	1071.9	1015.4
45°	1523.0	1371.0	1133.3	972.1	917.8
47.5°	1436.9	1276.1	1031.3	870.2	820.4
50°	1341.7	1180.8	931.5	775.0	727.6
52.5°	1248.6	1078.6	836.3	686.7	643.7
55°	1158.0	981.3	736.5	600.7	557.5
57.5°	1065.2	883.8	648.2	521.3	484.9
60°	970.0	788.7	555.2	439.8	403.4
62.5°	877.2	695.9	475.8	367.2	349.1
65°	781.9	598.2	394.4	317.4	310.4
67.5°	691.3	507.6	317.4	278.7	272.0
70°	596.0	419.3	262.8	240.2	231.1
72.5°	505.4	337.6	219.7	201.8	197.1
75°	417.0	258.2	181.3	165.4	163.3
77.5°	328.7	183.5	142.8	133.7	129.2
80°	246.9	131.5	108.7	99.8	99.8
82.5°	172.2	88.5	74.7	70.2	70.2
85°	97.4	49.8	43.0	43.0	43.0
87.5°	36.4	18.1	18.1	15.9	15.9
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0



TEST NUMBER: P908048

CATALOG NUMBER: DFN2DIP-HX3F0-060D030US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2



TEST NUMBER: P908048
 CATALOG NUMBER: DFN2DIP-HX3F0-060D030US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.16	13.14	12.98	13.97	15.00	8.14	9.12	8.96	9.95	10.98
	3H	13.84	14.72	14.67	15.56	16.62	9.34	10.21	10.16	11.05	12.11
	4H	14.45	15.28	15.30	16.13	17.20	9.79	10.62	10.64	11.47	12.53
	6H	14.88	15.64	15.74	16.50	17.58	10.11	10.87	10.97	11.73	12.81
	8H	15.00	15.73	15.87	16.60	17.68	10.21	10.93	11.07	11.81	12.89
	12H	15.07	15.76	15.94	16.63	17.73	10.25	10.94	11.13	11.81	12.92
4H	2H	12.20	13.02	13.05	13.87	14.94	8.75	9.57	9.60	10.42	11.49
	3H	14.03	14.72	14.89	15.60	16.68	10.11	10.79	10.97	11.68	12.76
	4H	14.72	15.35	15.60	16.23	17.34	10.66	11.28	11.53	12.16	13.27
	6H	15.24	15.78	16.13	16.68	17.80	11.08	11.62	11.97	12.52	13.64
	8H	15.41	15.92	16.31	16.81	17.94	11.21	11.71	12.10	12.61	13.74
	12H	15.51	15.96	16.42	16.88	18.01	11.28	11.73	12.19	12.65	13.78
8H	4H	14.70	15.20	15.59	16.10	17.23	10.94	11.45	11.84	12.34	13.47
	6H	15.27	15.68	16.18	16.62	17.75	11.46	11.88	12.38	12.82	13.94
	8H	15.48	15.84	16.41	16.78	17.92	11.65	12.02	12.58	12.95	14.09
	12H	15.62	15.94	16.55	16.86	18.06	11.77	12.09	12.70	13.02	14.21
12H	4H	14.66	15.11	15.57	16.03	17.16	10.95	11.41	11.87	12.32	13.45
	6H	15.24	15.61	16.17	16.54	17.68	11.51	11.88	12.44	12.81	13.95
	8H	15.46	15.79	16.39	16.71	17.91	11.72	12.04	12.65	12.97	14.17