

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908095

Luminaire Tested: DFN2DIP-HX3F0-080D030US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908095
REPORT IS A COMBINATION OF REPORTS P900731 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-080D030US840-FLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10997.5 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 102.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908095
CATALOG NUMBER: DFN2DIP-HX3F0-080D030US840-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P908095

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	65	65	65	61
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	55	55	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	47	47	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	40	40	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	35	35	35	32
6	67	54	45	39	63	52	44	38	47	41	36	43	37	33	39	35	31	31	31	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	28	28	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	25	25	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	22	22	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	20	20	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3641	3641	3641
5°	3645	3588	3613
10°	3614	3537	3562
15°	3560	3476	3483
20°	3486	3393	3403
25°	3413	3294	3311
30°	3322	3201	3194
35°	3235	3092	3070
40°	3129	2982	2952
45°	3023	2872	2832
50°	2906	2756	2692
55°	2785	2622	2563
60°	2647	2463	2416
65°	2497	2298	2242
70°	2305	2097	2054
75°	2040	1856	1877
80°	1720	1548	1545
85°	1220	1025	1002

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3023 cd/sqm



TEST NUMBER: P908095

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.9	2.7
10°-20°	832.5	7.6
20°-30°	1223.4	11.1
30°-40°	1420.9	12.9
40°-50°	1419.1	12.9
50°-60°	1237.5	11.3
60°-70°	914.7	8.3
70°-80°	517.6	4.7
80°-90°	138.4	1.3
90°-100°	33.7	0.3
100°-110°	125.7	1.1
110°-120°	333.3	3.0
120°-130°	552.9	5.0
130°-140°	587.3	5.3
140°-150°	545.8	5.0
150°-160°	438.8	4.0
160°-170°	282.8	2.6
170°-180°	97.3	0.9
0°-30°	2351.8	21.4
0°-40°	3772.7	34.3
0°-60°	6429.3	58.5
0°-90°	8000.0	72.7
90°-120°	492.7	4.5
90°-150°	2178.7	19.8
90°-180°	2998.0	27.3
0°-180°	10997.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3144	3144	3144	3144	3144	
5°	3144	3132	3098	3122	3117	298
15°	2992	2975	2935	2947	2932	843
25°	2708	2684	2633	2639	2633	1246
35°	2337	2306	2258	2240	2225	1459
45°	1902	1880	1835	1802	1790	1467
55°	1439	1421	1384	1348	1333	1287
65°	970	952	922	895	880	959
75°	508	502	487	469	475	542
85°	124	121	118	109	106	138
90°	1	9	15	19	20	10
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P908095

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3143.5	3143.5	3143.5	3143.5	3143.5
2.5°	3161.8	3146.7	3113.4	3143.5	3137.8
5°	3143.5	3131.7	3098.4	3122.4	3116.6
7.5°	3122.4	3104.4	3071.1	3095.4	3089.4
10°	3089.4	3068.2	3031.9	3056.0	3047.1
12.5°	3043.8	3025.9	2989.6	3004.7	2998.6
15°	2992.5	2974.6	2935.1	2947.3	2932.2
17.5°	2929.0	2911.0	2871.6	2886.7	2871.6
20°	2859.4	2841.5	2799.1	2808.1	2796.2
22.5°	2790.2	2762.9	2723.4	2723.4	2717.3
25°	2708.4	2684.3	2633.0	2638.8	2633.0
27.5°	2617.6	2596.5	2557.3	2548.3	2533.2
30°	2527.2	2502.7	2457.6	2448.6	2436.4
32.5°	2430.3	2412.4	2363.9	2345.6	2333.5
35°	2336.6	2306.5	2258.1	2239.8	2224.7
37.5°	2230.8	2203.5	2155.2	2133.9	2118.9
40°	2122.1	2097.7	2049.3	2022.4	2010.1
42.5°	2016.3	1991.9	1943.8	1913.3	1895.4
45°	1901.5	1880.3	1834.7	1801.7	1789.6
47.5°	1789.6	1768.4	1719.9	1686.6	1668.6
50°	1671.5	1656.5	1614.1	1571.8	1556.7
52.5°	1556.7	1535.5	1496.4	1463.1	1441.9
55°	1439.0	1420.7	1384.5	1348.3	1333.1
57.5°	1321.0	1306.0	1266.5	1230.2	1218.0
60°	1203.0	1191.1	1148.7	1115.4	1106.4
62.5°	1088.1	1067.0	1036.8	1006.7	994.5
65°	970.5	952.2	922.0	894.7	879.7
67.5°	849.5	834.1	807.2	786.1	773.9
70°	737.6	725.4	698.2	677.0	665.1
72.5°	622.8	610.7	595.5	574.4	565.4
75°	507.7	501.9	486.6	468.6	474.6
77.5°	405.1	392.8	386.8	377.8	368.8
80°	302.5	299.2	293.2	284.2	278.0
82.5°	205.6	205.6	202.7	190.5	190.5
85°	123.8	120.9	118.1	108.8	105.8
87.5°	54.5	48.5	42.3	33.3	30.2
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P908095

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P908095
 CATALOG NUMBER: DFN2DIP-HX3F0-080D030US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.60	14.71	14.33	15.46	16.37	13.17	14.28	13.90	15.03	15.94
	3H	15.27	16.27	16.01	17.03	17.97	14.80	15.80	15.55	16.56	17.50
	4H	15.86	16.80	16.63	17.58	18.52	15.39	16.33	16.16	17.11	18.06
	6H	16.27	17.14	17.05	17.92	18.88	15.80	16.67	16.57	17.45	18.41
	8H	16.38	17.20	17.16	18.01	18.97	15.91	16.74	16.69	17.54	18.50
	12H	16.43	17.22	17.22	18.02	19.01	15.95	16.75	16.75	17.54	18.53
4H	2H	14.08	15.03	14.85	15.80	16.75	13.74	14.68	14.51	15.46	16.41
	3H	15.96	16.75	16.74	17.56	18.52	15.57	16.36	16.35	17.17	18.13
	4H	16.68	17.40	17.48	18.21	19.20	16.28	17.00	17.08	17.80	18.80
	6H	17.20	17.82	18.02	18.66	19.66	16.80	17.42	17.61	18.25	19.25
	8H	17.36	17.94	18.17	18.76	19.78	16.95	17.53	17.77	18.36	19.37
	12H	17.44	17.96	18.27	18.81	19.83	17.02	17.54	17.86	18.39	19.41
8H	4H	16.89	17.47	17.71	18.30	19.32	16.54	17.12	17.35	17.95	18.96
	6H	17.53	18.01	18.37	18.88	19.89	17.17	17.65	18.01	18.52	19.53
	8H	17.75	18.17	18.60	19.04	20.07	17.38	17.81	18.24	18.68	19.70
	12H	17.88	18.26	18.74	19.12	20.20	17.50	17.88	18.36	18.74	19.82
12H	4H	16.89	17.41	17.73	18.26	19.28	16.54	17.06	17.38	17.91	18.93
	6H	17.56	17.99	18.42	18.85	19.88	17.21	17.64	18.07	18.50	19.53
	8H	17.81	18.18	18.67	19.04	20.13	17.45	17.83	18.31	18.69	19.77