

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908120

Luminaire Tested: DFN2DIP-HX3F0-090D030US840-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P908120  
REPORT IS A COMBINATION OF REPORTS P899214 AND P896089  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-090D030US840-RLLFLL  
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10406.7 lumens  
Efficiency: N/A  
Efficacy: 90.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 115.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P908120  
CATALOG NUMBER: DFN2DIP-HX3F0-090D030US840-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P908120  
 CATALOG NUMBER: DFN2DIP-HX3F0-090D030US840-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	78	78	78	74
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68	68	68	68	64
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58	58	58	58	55
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50	50	50	50	47
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	44	44	44	41
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39	39	39	39	36
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35	35	35	35	32
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31	31	31	31	29
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28	28	28	28	26
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26	26	26	26	24
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23	23	23	23	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4351	4351	4351
5°	4356	4279	4307
10°	4311	4192	4165
15°	4250	4051	3946
20°	4169	3857	3678
25°	4087	3640	3420
30°	3977	3418	3092
35°	3869	3180	2805
40°	3759	2934	2476
45°	3632	2661	2178
50°	3500	2386	1887
55°	3361	2092	1608
60°	3201	1786	1321
65°	3017	1474	1186
70°	2794	1184	1070
75°	2513	1037	969
80°	2106	860	832
85°	1439	560	611

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3632 cd/sqm



TEST NUMBER: P908120

CATALOG NUMBER: DFN2DIP-HX3F0-090D030US840-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	352.1	3.4
10°-20°	966.5	9.3
20°-30°	1356.9	13.0
30°-40°	1479.1	14.2
40°-50°	1359.4	13.1
50°-60°	1067.6	10.3
60°-70°	694.9	6.7
70°-80°	357.7	3.4
80°-90°	94.0	0.9
90°-100°	59.3	0.6
100°-110°	188.4	1.8
110°-120°	322.4	3.1
120°-130°	424.0	4.1
130°-140°	475.9	4.6
140°-150°	466.7	4.5
150°-160°	391.5	3.8
160°-170°	259.6	2.5
170°-180°	90.7	0.9
0°-30°	2675.4	25.7
0°-40°	4154.5	39.9
0°-60°	6581.5	63.2
0°-90°	7728.2	74.3
90°-120°	570.1	5.5
90°-150°	1936.6	18.6
90°-180°	2678.0	25.7
0°-180°	10406.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3756	3756	3756	3756	3756	
5°	3756	3739	3695	3726	3716	356
15°	3573	3535	3420	3355	3321	1007
25°	3243	3134	2910	2771	2720	1492
35°	2794	2621	2322	2108	2033	1749
45°	2284	2057	1700	1458	1377	1764
55°	1737	1472	1105	901	836	1552
65°	1173	897	592	476	466	1163
75°	625	387	272	248	245	661
85°	146	75	64	64	64	168
90°	1	10	28	27	28	10
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	



TEST NUMBER: P908120

CATALOG NUMBER: DFN2DIP-HX3F0-090D030US840-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3756.4	3756.4	3756.4	3756.4	3756.4
2.5°	3773.4	3756.4	3718.8	3753.2	3746.3
5°	3756.4	3739.4	3695.1	3725.7	3715.6
7.5°	3725.7	3705.5	3657.9	3671.3	3654.3
10°	3685.0	3661.2	3593.4	3582.9	3562.7
12.5°	3634.1	3603.5	3511.5	3491.3	3453.7
15°	3572.8	3535.3	3419.9	3355.3	3321.4
17.5°	3501.4	3447.0	3304.1	3229.4	3175.0
20°	3419.9	3351.7	3181.8	3097.1	3022.0
22.5°	3331.5	3253.3	3056.0	2940.5	2889.7
25°	3243.2	3134.2	2909.9	2770.7	2719.5
27.5°	3137.9	3022.0	2773.9	2614.1	2535.9
30°	3025.7	2896.2	2624.2	2451.1	2359.1
32.5°	2916.7	2760.2	2481.7	2277.7	2192.5
35°	2794.5	2621.0	2322.0	2107.8	2032.8
37.5°	2675.4	2488.3	2172.3	1937.5	1852.8
40°	2549.6	2345.8	2015.8	1774.5	1686.2
42.5°	2420.4	2203.0	1859.6	1607.9	1523.1
45°	2284.5	2056.6	1699.8	1458.1	1376.6
47.5°	2155.4	1914.1	1546.9	1305.3	1230.6
50°	2012.6	1771.2	1397.2	1162.5	1091.4
52.5°	1873.0	1618.0	1254.5	1030.1	965.5
55°	1737.0	1471.9	1104.7	901.0	836.4
57.5°	1597.8	1325.9	972.4	781.9	727.5
60°	1454.9	1183.0	832.8	659.6	605.2
62.5°	1315.8	1043.8	713.8	550.8	523.7
65°	1172.9	897.4	591.5	476.1	465.6
67.5°	1036.9	761.3	476.1	418.0	407.9
70°	894.1	629.0	394.3	360.3	346.6
72.5°	758.1	506.3	329.6	302.6	295.8
75°	625.4	387.4	272.0	248.1	244.9
77.5°	493.0	275.2	214.2	200.6	193.7
80°	370.4	197.3	163.0	149.7	149.7
82.5°	258.2	132.7	112.2	105.3	105.3
85°	146.0	74.6	64.5	64.5	64.5
87.5°	54.4	27.1	27.1	23.8	23.8
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0



TEST NUMBER: P908120

CATALOG NUMBER: DFN2DIP-HX3F0-090D030US840-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2



TEST NUMBER: P908120  
 CATALOG NUMBER: DFN2DIP-HX3F0-090D030US840-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.23	15.31	14.96	16.05	16.93	10.21	11.29	10.93	12.02	12.90
	3H	15.92	16.88	16.66	17.63	18.55	11.41	12.38	12.15	13.12	14.04
	4H	16.54	17.44	17.29	18.20	19.13	11.87	12.78	12.63	13.54	14.46
	6H	16.96	17.80	17.73	18.57	19.50	12.20	13.04	12.97	13.80	14.74
	8H	17.09	17.89	17.87	18.68	19.61	12.29	13.09	13.07	13.88	14.82
	12H	17.16	17.92	17.94	18.70	19.66	12.34	13.10	13.13	13.88	14.85
4H	2H	14.28	15.19	15.04	15.95	16.87	10.83	11.74	11.59	12.50	13.42
	3H	16.12	16.88	16.89	17.67	18.61	12.20	12.95	12.97	13.74	14.68
	4H	16.82	17.50	17.60	18.30	19.27	12.75	13.43	13.54	14.23	15.20
	6H	17.34	17.93	18.14	18.75	19.72	13.18	13.77	13.98	14.59	15.56
	8H	17.51	18.07	18.32	18.88	19.87	13.31	13.86	14.12	14.67	15.66
	12H	17.62	18.11	18.44	18.95	19.94	13.38	13.88	14.21	14.71	15.71
8H	4H	16.80	17.35	17.61	18.17	19.16	13.04	13.59	13.85	14.41	15.40
	6H	17.37	17.82	18.20	18.68	19.67	13.56	14.02	14.40	14.88	15.87
	8H	17.58	17.99	18.43	18.84	19.85	13.75	14.16	14.60	15.01	16.02
	12H	17.72	18.08	18.57	18.93	19.99	13.88	14.24	14.73	15.08	16.14
12H	4H	16.76	17.26	17.59	18.10	19.09	13.06	13.55	13.89	14.39	15.38
	6H	17.34	17.75	18.19	18.60	19.61	13.61	14.02	14.46	14.87	15.88
	8H	17.57	17.93	18.42	18.77	19.83	13.83	14.19	14.68	15.03	16.09