

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927308

Luminaire Tested: DFN2DIP-HX4F0-070D050US835-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927308
REPORT IS A COMBINATION OF REPORTS P900843 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D050US835-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11880.1 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927308
CATALOG NUMBER: DFN2DIP-HX4F0-070D050US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P927308
 CATALOG NUMBER: DFN2DIP-HX4F0-070D050US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	64	64	64	58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	54	54	54	49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	47	45	45	45	45	41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39	39	39	39	35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	33	33	33	30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29	29	29	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	26	26	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	23	23	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	20	20	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	18	18	18	16
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	19	17	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2025	2025	2025
5°	2029	1997	2011
10°	2012	1971	1983
15°	1983	1938	1941
20°	1943	1893	1898
25°	1904	1840	1847
30°	1854	1790	1783
35°	1807	1731	1716
40°	1749	1671	1651
45°	1691	1612	1586
50°	1628	1549	1509
55°	1562	1477	1439
60°	1487	1391	1359
65°	1406	1302	1264
70°	1302	1193	1163
75°	1158	1063	1069
80°	985	898	889
85°	715	612	591

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1691 cd/sqm



TEST NUMBER: P927308

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	2.2
10°-20°	721.3	6.1
20°-30°	1060.0	8.9
30°-40°	1231.1	10.4
40°-50°	1229.6	10.4
50°-60°	1072.2	9.0
60°-70°	792.6	6.7
70°-80°	448.4	3.8
80°-90°	121.3	1.0
90°-100°	55.7	0.5
100°-110°	207.4	1.7
110°-120°	550.1	4.6
120°-130°	912.4	7.7
130°-140°	969.2	8.2
140°-150°	900.8	7.6
150°-160°	724.2	6.1
160°-170°	466.6	3.9
170°-180°	160.6	1.4
0°-30°	2037.7	17.2
0°-40°	3268.8	27.5
0°-60°	5570.6	46.9
0°-90°	6933.0	58.4
90°-120°	813.2	6.8
90°-150°	3595.6	30.3
90°-180°	4947.0	41.6
0°-180°	11880.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	120
90°	1	15	24	31	33	11
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	



TEST NUMBER: P927308

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P927308

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4



TEST NUMBER: P927308
 CATALOG NUMBER: DFN2DIP-HX4F0-070D050US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.46	11.40	11.34	12.31	13.45	10.03	10.97	10.91	11.87	13.02
	3H	12.13	12.97	13.02	13.89	15.06	11.66	12.50	12.55	13.41	14.59
	4H	12.72	13.52	13.63	14.44	15.62	12.25	13.05	13.16	13.96	15.15
	6H	13.13	13.86	14.05	14.79	15.98	12.65	13.39	13.57	14.31	15.51
	8H	13.23	13.94	14.16	14.88	16.07	12.76	13.46	13.69	14.40	15.60
	12H	13.29	13.95	14.22	14.89	16.11	12.80	13.47	13.74	14.41	15.63
4H	2H	10.93	11.73	11.85	12.65	13.83	10.59	11.39	11.50	12.31	13.49
	3H	12.81	13.48	13.73	14.42	15.62	12.42	13.08	13.34	14.03	15.23
	4H	13.53	14.14	14.46	15.08	16.30	13.12	13.73	14.06	14.67	15.90
	6H	14.05	14.57	15.00	15.54	16.76	13.64	14.16	14.59	15.13	16.35
	8H	14.20	14.69	15.15	15.65	16.89	13.79	14.28	14.74	15.24	16.48
	12H	14.28	14.72	15.25	15.70	16.94	13.86	14.30	14.83	15.28	16.52
8H	4H	13.73	14.22	14.68	15.18	16.42	13.37	13.86	14.32	14.82	16.06
	6H	14.37	14.77	15.34	15.78	17.01	14.00	14.41	14.98	15.41	16.65
	8H	14.59	14.95	15.58	15.94	17.19	14.22	14.58	15.21	15.57	16.82
	12H	14.73	15.04	15.72	16.03	17.33	14.34	14.66	15.33	15.64	16.94
12H	4H	13.72	14.16	14.69	15.14	16.38	13.37	13.81	14.34	14.79	16.03
	6H	14.40	14.76	15.38	15.75	17.00	14.05	14.41	15.03	15.40	16.65
	8H	14.64	14.96	15.63	15.95	17.25	14.29	14.60	15.28	15.59	16.89