

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905485

Luminaire Tested: DFN2DIP-HX4F0-070D120US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905485
REPORT IS A COMBINATION OF REPORTS P899450 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D120US835-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16570.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 139.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905485

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905485

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	91	87	84	86	82	79	77	67	64	63	52	51	49	39	38	37
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	34	33	32
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	21	19
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	19	17
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	15	14
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2151	2151	2151
5°	2155	2117	2131
10°	2134	2076	2061
15°	2104	2008	1954
20°	2066	1913	1823
25°	2026	1807	1696
30°	1973	1699	1535
35°	1921	1582	1394
40°	1868	1461	1231
45°	1806	1327	1084
50°	1742	1192	941
55°	1676	1047	803
60°	1599	896	661
65°	1510	742	595
70°	1403	599	538
75°	1268	528	490
80°	1073	444	426
85°	750	297	321

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2862 cd/sqm

TEST NUMBER: P905485

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	1.6
10°-20°	744.3	4.5
20°-30°	1045.0	6.3
30°-40°	1139.2	6.9
40°-50°	1047.0	6.3
50°-60°	822.3	5.0
60°-70°	535.2	3.2
70°-80°	275.5	1.7
80°-90°	81.1	0.5
90°-100°	234.8	1.4
100°-110°	746.2	4.5
110°-120°	1276.9	7.7
120°-130°	1679.4	10.1
130°-140°	1885.0	11.4
140°-150°	1848.5	11.2
150°-160°	1550.6	9.4
160°-170°	1028.3	6.2
170°-180°	359.4	2.2
0°-30°	2060.5	12.4
0°-40°	3199.7	19.3
0°-60°	5068.9	30.6
0°-90°	5960.7	36.0
90°-120°	2257.9	13.6
90°-150°	7670.8	46.3
90°-180°	10609.0	64.0
0°-180°	16570.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	129
90°	3	41	112	105	109	16
95°	167	199	205	205	199	186
105°	689	698	705	710	710	727
115°	1281	1300	1294	1291	1281	1267
125°	1864	1892	1883	1873	1870	1666
135°	2411	2446	2453	2450	2440	1863
145°	2927	2950	2968	2971	2959	1829
155°	3347	3356	3366	3382	3372	1540
165°	3641	3637	3637	3660	3644	1027
175°	3788	3779	3772	3795	3776	360
180°	3795	3795	3795	3795	3795	

TEST NUMBER: P905485

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	3.4	41.2	112.1	105.3	108.7
92.5°	70.9	96.1	99.5	103.0	103.0
95°	167.0	199.1	204.8	204.8	199.1
97.5°	278.0	307.8	320.4	320.4	320.4
100°	406.2	432.5	441.6	441.6	438.2
102.5°	541.2	560.6	573.2	576.7	573.2
105°	688.8	697.9	704.8	710.5	710.5
107.5°	835.2	849.0	849.0	851.2	835.2
110°	977.1	995.4	995.4	995.4	986.3

TEST NUMBER: P905485

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1130.4	1149.9	1146.4	1137.3	1130.4
115°	1281.4	1299.8	1294.0	1290.6	1281.4
117.5°	1431.3	1456.5	1440.5	1431.3	1422.2
120°	1582.4	1607.5	1582.4	1582.4	1572.1
122.5°	1719.7	1751.7	1735.7	1726.5	1719.7
125°	1863.8	1892.4	1883.3	1873.0	1869.5
127.5°	2004.6	2040.0	2027.4	2013.7	2004.6
130°	2136.1	2177.3	2171.6	2164.7	2152.1
132.5°	2283.7	2315.8	2318.0	2302.0	2292.9
135°	2410.7	2446.2	2453.1	2449.6	2440.5
137.5°	2552.6	2581.2	2586.9	2584.6	2570.9
140°	2677.3	2705.9	2721.9	2721.9	2709.3
142.5°	2805.5	2834.1	2843.2	2846.6	2834.1
145°	2926.7	2949.6	2967.9	2971.4	2958.8
147.5°	3035.4	3064.0	3077.8	3083.5	3070.9
150°	3147.6	3167.0	3179.6	3189.9	3179.6
152.5°	3247.1	3266.5	3282.6	3295.2	3282.6
155°	3346.6	3355.8	3366.1	3382.1	3371.8
157.5°	3432.5	3439.3	3445.0	3467.9	3451.9
160°	3509.1	3516.0	3519.4	3538.9	3525.1
162.5°	3580.0	3580.0	3583.5	3605.2	3589.2
165°	3640.7	3637.3	3637.3	3660.1	3644.1
167.5°	3695.6	3685.3	3685.3	3708.2	3692.2
170°	3736.8	3727.6	3724.2	3747.1	3727.6
172.5°	3765.4	3756.2	3752.8	3775.7	3756.2
175°	3788.3	3779.1	3772.3	3795.1	3775.7
177.5°	3800.9	3791.7	3784.8	3804.3	3784.8
180°	3795.1	3795.1	3795.1	3795.1	3795.1

TEST NUMBER: P905485

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.34	9.06	9.41	10.14	11.60	4.31	5.04	5.38	6.11	7.57
	3H	10.01	10.66	11.09	11.74	13.22	5.49	6.14	6.58	7.22	8.70
	4H	10.61	11.23	11.71	12.31	13.79	5.94	6.56	7.03	7.64	9.12
	6H	11.03	11.60	12.13	12.68	14.18	6.26	6.82	7.36	7.91	9.40
	8H	11.15	11.69	12.26	12.79	14.28	6.34	6.88	7.45	7.98	9.48
	12H	11.21	11.72	12.32	12.82	14.33	6.39	6.90	7.50	7.99	9.51
4H	2H	8.34	8.96	9.44	10.04	11.53	4.89	5.51	5.99	6.59	8.08
	3H	10.16	10.68	11.27	11.78	13.28	6.24	6.75	7.34	7.86	9.35
	4H	10.85	11.32	11.96	12.42	13.94	6.78	7.25	7.89	8.35	9.87
	6H	11.36	11.77	12.48	12.89	14.40	7.20	7.60	8.32	8.72	10.23
	8H	11.54	11.91	12.66	13.03	14.55	7.32	7.70	8.44	8.81	10.34
	12H	11.63	11.97	12.76	13.09	14.63	7.39	7.73	8.52	8.85	10.38
8H	4H	10.81	11.19	11.93	12.30	13.83	7.05	7.43	8.17	8.54	10.07
	6H	11.38	11.69	12.52	12.84	14.37	7.57	7.88	8.71	9.04	10.56
	8H	11.59	11.86	12.74	13.00	14.54	7.76	8.03	8.91	9.17	10.71
	12H	11.73	11.97	12.88	13.10	14.68	7.88	8.12	9.03	9.25	10.83
12H	4H	10.76	11.10	11.90	12.23	13.76	7.05	7.39	8.19	8.52	10.05
	6H	11.35	11.62	12.50	12.76	14.30	7.62	7.89	8.77	9.03	10.57
	8H	11.57	11.81	12.72	12.94	14.52	7.83	8.07	8.98	9.20	10.78

END OF REPORT