

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910731

Luminaire Tested: DFN2DIP-HX3F0-040D040US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910731
REPORT IS A COMBINATION OF REPORTS P900737 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-040D040US850-FLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8783.3 lumens
Efficiency: N/A
Efficacy: 136.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910731
CATALOG NUMBER: DFN2DIP-HX3F0-040D040US850-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P910731

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1999	1999	1999
5°	2002	1970	1984
10°	1985	1942	1956
15°	1954	1909	1913
20°	1914	1863	1869
25°	1874	1809	1818
30°	1824	1758	1754
35°	1776	1698	1686
40°	1718	1638	1621
45°	1660	1577	1555
50°	1596	1513	1478
55°	1529	1440	1408
60°	1453	1352	1326
65°	1371	1262	1231
70°	1266	1151	1128
75°	1120	1019	1031
80°	944	849	849
85°	670	562	550

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1660 cd/sqm



TEST NUMBER: P910731

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	1.8
10°-20°	457.1	5.2
20°-30°	671.7	7.6
30°-40°	780.2	8.9
40°-50°	779.2	8.9
50°-60°	679.5	7.7
60°-70°	502.3	5.7
70°-80°	284.2	3.2
80°-90°	77.6	0.9
90°-100°	49.4	0.6
100°-110°	184.0	2.1
110°-120°	488.1	5.6
120°-130°	809.5	9.2
130°-140°	859.9	9.8
140°-150°	799.2	9.1
150°-160°	642.5	7.3
160°-170°	414.0	4.7
170°-180°	142.5	1.6
0°-30°	1291.3	14.7
0°-40°	2071.5	23.6
0°-60°	3530.2	40.2
0°-90°	4394.3	50.0
90°-120°	721.5	8.2
90°-150°	3190.0	36.3
90°-180°	4389.0	50.0
0°-180°	8783.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	76
90°	1	13	22	27	29	8
95°	70	35	42	48	47	83
105°	329	362	66	78	82	352
115°	623	641	668	167	89	613
125°	881	895	915	923	926	785
135°	1090	1107	1117	1128	1126	842
145°	1264	1263	1281	1289	1284	791
155°	1392	1382	1395	1402	1393	641
165°	1467	1460	1464	1471	1464	414
175°	1500	1493	1495	1502	1492	143
180°	1497	1497	1497	1497	1497	



TEST NUMBER: P910731

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	1.0	13.0	21.6	27.2	29.2
92.5°	27.2	22.7	26.0	28.2	29.2
95°	70.3	34.6	42.1	47.7	46.6
97.5°	126.8	37.9	55.2	58.6	59.6
100°	191.7	43.4	61.8	70.3	72.5
102.5°	263.2	261.2	63.9	75.7	79.1
105°	329.3	361.9	66.1	78.0	82.3
107.5°	406.2	433.3	68.3	80.2	84.5
110°	480.0	502.6	189.6	81.3	85.5



TEST NUMBER: P910731

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	549.3	568.7	550.3	83.4	86.7
115°	622.8	641.2	668.4	166.8	88.9
117.5°	686.8	708.4	726.9	571.9	288.1
120°	758.3	774.5	794.0	807.1	660.9
122.5°	818.9	836.3	858.0	864.5	865.6
125°	880.7	894.9	915.4	923.0	926.2
127.5°	937.0	952.2	968.5	979.4	980.4
130°	990.1	1007.5	1019.3	1031.3	1030.3
132.5°	1044.2	1058.4	1070.3	1080.1	1079.1
135°	1089.8	1107.2	1116.9	1127.7	1125.6
137.5°	1137.4	1150.4	1161.3	1172.1	1168.9
140°	1184.0	1192.7	1204.6	1214.4	1208.9
142.5°	1223.1	1230.7	1244.7	1253.3	1248.0
145°	1264.3	1263.2	1281.4	1289.1	1283.7
147.5°	1299.9	1296.6	1315.1	1320.5	1316.3
150°	1334.6	1327.0	1344.4	1350.9	1345.4
152.5°	1363.8	1355.2	1371.4	1377.9	1370.4
155°	1392.0	1382.4	1395.3	1401.8	1393.1
157.5°	1414.8	1406.1	1416.0	1423.5	1414.8
160°	1434.3	1427.7	1434.3	1440.7	1433.2
162.5°	1451.6	1445.1	1450.6	1458.1	1448.4
165°	1466.8	1460.3	1463.5	1471.1	1463.5
167.5°	1478.7	1472.1	1475.5	1483.1	1473.3
170°	1488.5	1482.0	1484.1	1491.7	1482.0
172.5°	1494.9	1488.5	1490.7	1498.3	1488.5
175°	1500.3	1492.7	1494.9	1502.5	1491.7
177.5°	1502.5	1494.9	1496.0	1503.7	1493.9
180°	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P910731
 CATALOG NUMBER: DFN2DIP-HX3F0-040D040US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.64	10.50	10.60	11.47	12.74	9.21	10.07	10.17	11.04	12.31
	3H	11.29	12.06	12.26	13.05	14.34	10.82	11.60	11.79	12.58	13.87
	4H	11.87	12.61	12.86	13.59	14.89	11.40	12.14	12.39	13.12	14.42
	6H	12.27	12.94	13.26	13.93	15.25	11.80	12.47	12.79	13.46	14.78
	8H	12.37	13.01	13.37	14.02	15.33	11.90	12.54	12.90	13.55	14.86
	12H	12.41	13.03	13.42	14.03	15.36	11.94	12.55	12.94	13.55	14.89
4H	2H	10.10	10.83	11.09	11.81	13.12	9.75	10.49	10.74	11.47	12.77
	3H	11.95	12.57	12.95	13.58	14.90	11.56	12.18	12.56	13.19	14.51
	4H	12.66	13.22	13.67	14.23	15.57	12.26	12.82	13.27	13.83	15.17
	6H	13.17	13.65	14.19	14.68	16.02	12.77	13.25	13.78	14.28	15.61
	8H	13.32	13.77	14.33	14.79	16.14	12.91	13.36	13.93	14.38	15.73
	12H	13.39	13.79	14.42	14.83	16.19	12.97	13.38	14.01	14.41	15.77
8H	4H	12.86	13.31	13.87	14.33	15.68	12.50	12.95	13.52	13.97	15.32
	6H	13.48	13.85	14.52	14.92	16.26	13.12	13.49	14.16	14.56	15.90
	8H	13.69	14.02	14.74	15.07	16.44	13.33	13.66	14.38	14.71	16.07
	12H	13.82	14.11	14.87	15.15	16.56	13.44	13.73	14.49	14.77	16.18
12H	4H	12.84	13.25	13.88	14.29	15.64	12.49	12.90	13.53	13.94	15.29
	6H	13.51	13.83	14.56	14.89	16.25	13.16	13.49	14.21	14.54	15.90
	8H	13.74	14.03	14.80	15.08	16.49	13.39	13.68	14.44	14.72	16.13