

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910821

Luminaire Tested: DFN2DIP-HX3F0-070D090US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910821
REPORT IS A COMBINATION OF REPORTS P899294 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D090US850-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15431.7 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 140.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910821

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910821

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	36
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	52	46	41	44	39	35	36	32	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3716	3716	3716
5°	3721	3655	3679
10°	3682	3581	3557
15°	3630	3460	3370
20°	3561	3294	3142
25°	3491	3109	2921
30°	3397	2920	2642
35°	3305	2716	2396
40°	3211	2506	2115
45°	3102	2273	1861
50°	2989	2038	1612
55°	2871	1787	1374
60°	2734	1525	1129
65°	2577	1259	1013
70°	2386	1011	914
75°	2146	886	827
80°	1799	735	711
85°	1230	478	522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3102 cd/sqm

TEST NUMBER: P910821

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	1.9
10°-20°	825.5	5.3
20°-30°	1158.9	7.5
30°-40°	1263.3	8.2
40°-50°	1161.1	7.5
50°-60°	911.9	5.9
60°-70°	593.5	3.8
70°-80°	305.5	2.0
80°-90°	87.0	0.6
90°-100°	195.3	1.3
100°-110°	620.6	4.0
110°-120°	1062.1	6.9
120°-130°	1396.8	9.1
130°-140°	1567.9	10.2
140°-150°	1537.5	10.0
150°-160°	1289.7	8.4
160°-170°	855.3	5.5
170°-180°	299.0	1.9
0°-30°	2285.1	14.8
0°-40°	3548.4	23.0
0°-60°	5621.4	36.4
0°-90°	6607.5	42.8
90°-120°	1878.1	12.2
90°-150°	6380.2	41.3
90°-180°	8824.0	57.2
0°-180°	15431.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3208	3208	3208	3208	3208	
5°	3208	3194	3156	3182	3174	304
15°	3052	3020	2921	2866	2837	860
25°	2770	2677	2485	2366	2323	1274
35°	2387	2239	1983	1800	1736	1494
45°	1951	1756	1452	1246	1176	1507
55°	1484	1257	944	770	714	1326
65°	1002	766	505	407	398	993
75°	534	331	232	212	209	565
85°	125	64	55	55	55	143
90°	3	34	93	88	90	15
95°	139	166	170	170	166	155
105°	573	580	586	591	591	605
115°	1066	1081	1076	1074	1066	1054
125°	1550	1574	1566	1558	1555	1385
135°	2005	2035	2040	2038	2030	1550
145°	2434	2453	2468	2471	2461	1521
155°	2784	2791	2800	2813	2805	1281
165°	3028	3025	3025	3044	3031	854
175°	3151	3143	3138	3157	3140	299
180°	3157	3157	3157	3157	3157	

TEST NUMBER: P910821

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3208.4	3208.4	3208.4	3208.4	3208.4
2.5°	3222.9	3208.4	3176.4	3205.7	3199.8
5°	3208.4	3193.9	3156.1	3182.3	3173.6
7.5°	3182.3	3165.0	3124.4	3135.7	3121.3
10°	3147.5	3127.2	3069.2	3060.3	3043.0
12.5°	3104.0	3077.8	2999.3	2982.0	2949.9
15°	3051.6	3019.6	2921.0	2865.9	2836.9
17.5°	2990.6	2944.2	2822.2	2758.3	2711.8
20°	2921.0	2862.8	2717.7	2645.3	2581.2
22.5°	2845.6	2778.7	2610.1	2511.6	2468.2
25°	2770.1	2677.0	2485.4	2366.5	2322.8
27.5°	2680.1	2581.2	2369.3	2232.9	2166.0
30°	2584.3	2473.7	2241.4	2093.6	2015.1
32.5°	2491.3	2357.6	2119.7	1945.4	1872.7
35°	2386.8	2238.6	1983.3	1800.4	1736.3
37.5°	2285.2	2125.3	1855.5	1654.8	1582.5
40°	2177.6	2003.6	1721.7	1515.7	1440.1
42.5°	2067.4	1881.6	1588.3	1373.3	1301.0
45°	1951.3	1756.5	1451.9	1245.5	1175.9
47.5°	1840.9	1634.9	1321.3	1114.9	1051.1
50°	1719.0	1512.9	1193.4	992.9	932.2
52.5°	1599.7	1381.9	1071.4	879.8	824.7
55°	1483.6	1257.2	943.5	769.5	714.4
57.5°	1364.7	1132.4	830.5	667.8	621.4
60°	1242.7	1010.4	711.3	563.5	516.9
62.5°	1123.7	891.5	609.6	470.4	447.3
65°	1001.8	766.4	505.3	406.7	397.7
67.5°	885.6	650.3	406.7	357.0	348.4
70°	763.7	537.2	336.7	307.7	296.0
72.5°	647.5	432.5	281.6	258.5	252.6
75°	534.2	330.8	232.2	211.9	209.2
77.5°	421.1	235.0	183.0	171.2	165.5
80°	316.4	168.5	139.3	127.9	127.9
82.5°	220.6	113.3	95.8	89.9	89.9
85°	124.8	63.8	55.1	55.1	55.1
87.5°	46.5	23.1	23.1	20.3	20.3
90°	2.9	34.3	93.3	87.5	90.4
92.5°	59.0	80.0	82.8	85.6	85.6
95°	139.0	165.6	170.3	170.3	165.6
97.5°	231.2	256.0	266.5	266.5	266.5
100°	337.8	359.8	367.3	367.3	364.5
102.5°	450.1	466.3	476.8	479.6	476.8
105°	572.9	580.5	586.2	591.0	591.0
107.5°	694.7	706.1	706.1	708.0	694.7
110°	812.7	828.0	828.0	828.0	820.3

TEST NUMBER: P910821

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	940.2	956.4	953.5	946.0	940.2
115°	1065.9	1081.1	1076.3	1073.5	1065.9
117.5°	1190.5	1211.5	1198.2	1190.5	1182.9
120°	1316.2	1337.0	1316.2	1316.2	1307.5
122.5°	1430.3	1457.0	1443.7	1436.0	1430.3
125°	1550.3	1574.0	1566.5	1557.8	1555.0
127.5°	1667.3	1696.8	1686.3	1674.9	1667.3
130°	1776.7	1811.0	1806.2	1800.5	1790.0
132.5°	1899.5	1926.1	1928.0	1914.7	1907.1
135°	2005.1	2034.6	2040.3	2037.5	2029.9
137.5°	2123.1	2146.9	2151.7	2149.8	2138.4
140°	2226.9	2250.6	2263.9	2263.9	2253.5
142.5°	2333.4	2357.2	2364.8	2367.7	2357.2
145°	2434.4	2453.3	2468.5	2471.4	2461.0
147.5°	2524.7	2548.5	2559.9	2564.7	2554.2
150°	2618.0	2634.2	2644.6	2653.2	2644.6
152.5°	2700.7	2716.9	2730.2	2740.8	2730.2
155°	2783.6	2791.1	2799.8	2813.1	2804.6
157.5°	2854.9	2860.7	2865.4	2884.4	2871.1
160°	2918.7	2924.4	2927.3	2943.4	2932.0
162.5°	2977.7	2977.7	2980.5	2998.6	2985.3
165°	3028.1	3025.2	3025.2	3044.3	3031.0
167.5°	3073.8	3065.3	3065.3	3084.2	3070.9
170°	3108.1	3100.4	3097.7	3116.6	3100.4
172.5°	3131.8	3124.3	3121.4	3140.5	3124.3
175°	3150.9	3143.2	3137.6	3156.7	3140.5
177.5°	3161.3	3153.8	3148.0	3164.2	3148.0
180°	3156.7	3156.7	3156.7	3156.7	3156.7

TEST NUMBER: P910821

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.95	11.73	11.98	12.75	14.13	6.93	7.70	7.95	8.73	10.10
	3H	12.62	13.31	13.65	14.35	15.74	8.11	8.80	9.14	9.84	11.23
	4H	13.22	13.87	14.26	14.91	16.31	8.55	9.21	9.60	10.25	11.65
	6H	13.63	14.23	14.69	15.28	16.69	8.87	9.47	9.92	10.51	11.93
	8H	13.75	14.33	14.81	15.38	16.79	8.96	9.53	10.01	10.59	11.99
	12H	13.81	14.35	14.87	15.41	16.84	8.99	9.54	10.06	10.59	12.02
4H	2H	10.96	11.62	12.01	12.66	14.06	7.51	8.17	8.56	9.21	10.61
	3H	12.78	13.32	13.84	14.39	15.80	8.85	9.40	9.91	10.46	11.88
	4H	13.46	13.96	14.53	15.02	16.45	9.39	9.89	10.46	10.95	12.39
	6H	13.97	14.40	15.04	15.48	16.91	9.81	10.23	10.88	11.32	12.75
	8H	14.14	14.54	15.21	15.61	17.05	9.93	10.33	11.01	11.40	12.85
	12H	14.23	14.59	15.32	15.67	17.12	9.99	10.35	11.08	11.44	12.89
8H	4H	13.43	13.82	14.50	14.90	16.34	9.67	10.07	10.74	11.14	12.58
	6H	13.98	14.31	15.08	15.43	16.87	10.18	10.51	11.27	11.62	13.06
	8H	14.19	14.48	15.30	15.58	17.04	10.36	10.65	11.47	11.75	13.21
	12H	14.32	14.58	15.43	15.67	17.17	10.48	10.73	11.58	11.82	13.32
12H	4H	13.37	13.74	14.47	14.82	16.27	9.67	10.03	10.76	11.12	12.57
	6H	13.96	14.25	15.06	15.34	16.80	10.22	10.51	11.33	11.61	13.07
	8H	14.17	14.42	15.28	15.52	17.02	10.43	10.68	11.53	11.77	13.28