

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905535

Luminaire Tested: DFN2DIP-HX4F0-100D100US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905535
REPORT IS A COMBINATION OF REPORTS P899420 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D100US835-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17350.0 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 157.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905535

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905535

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3073	3073	3073
5°	3078	3025	3044
10°	3048	2966	2945
15°	3006	2868	2792
20°	2951	2733	2604
25°	2895	2582	2423
30°	2818	2427	2193
35°	2744	2260	1991
40°	2668	2088	1759
45°	2580	1896	1549
50°	2489	1703	1344
55°	2394	1496	1147
60°	2284	1280	944
65°	2157	1060	850
70°	2004	855	769
75°	1811	755	700
80°	1532	634	608
85°	1071	425	458

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2580 cd/sqm

TEST NUMBER: P905535

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.3	2.2
10°-20°	1063.3	6.1
20°-30°	1492.9	8.6
30°-40°	1627.4	9.4
40°-50°	1495.7	8.6
50°-60°	1174.7	6.8
60°-70°	764.6	4.4
70°-80°	393.6	2.3
80°-90°	109.5	0.6
90°-100°	195.7	1.1
100°-110°	621.8	3.6
110°-120°	1064.1	6.1
120°-130°	1399.5	8.1
130°-140°	1570.9	9.1
140°-150°	1540.4	8.9
150°-160°	1292.2	7.4
160°-170°	856.9	4.9
170°-180°	299.5	1.7
0°-30°	2943.6	17.0
0°-40°	4571.0	26.3
0°-60°	7241.3	41.7
0°-90°	8509.0	49.0
90°-120°	1881.6	10.8
90°-150°	6392.4	36.8
90°-180°	8841.0	51.0
0°-180°	17350.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4133	4133	4133	4133	4133	
5°	4133	4114	4066	4099	4088	392
15°	3931	3890	3763	3692	3654	1108
25°	3568	3448	3202	3048	2992	1641
35°	3075	2884	2555	2319	2236	1924
45°	2514	2263	1870	1604	1515	1941
55°	1911	1620	1216	991	920	1708
65°	1290	987	651	524	512	1279
75°	688	426	299	273	269	728
85°	161	82	71	71	71	184
90°	3	34	93	88	91	17
95°	139	166	171	171	166	155
105°	574	582	587	592	592	606
115°	1068	1083	1078	1076	1068	1056
125°	1553	1577	1569	1561	1558	1388
135°	2009	2038	2044	2041	2034	1553
145°	2439	2458	2473	2476	2466	1524
155°	2789	2796	2805	2818	2810	1284
165°	3034	3031	3031	3050	3037	856
175°	3157	3149	3144	3163	3146	300
180°	3163	3163	3163	3163	3163	



TEST NUMBER: P905535

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4133.0	4133.0	4133.0	4133.0	4133.0
2.5°	4151.6	4133.0	4091.7	4129.4	4121.9
5°	4133.0	4114.3	4065.5	4099.3	4088.1
7.5°	4099.3	4077.0	4024.6	4039.3	4020.7
10°	4054.4	4028.2	3953.6	3942.1	3919.9
12.5°	3998.5	3964.7	3863.5	3841.3	3800.0
15°	3931.0	3889.7	3762.7	3691.7	3654.4
17.5°	3852.4	3792.5	3635.4	3553.2	3493.3
20°	3762.7	3687.7	3500.8	3407.6	3325.0
22.5°	3665.5	3579.4	3362.3	3235.4	3179.4
25°	3568.3	3448.5	3201.6	3048.4	2992.1
27.5°	3452.4	3325.0	3052.0	2876.2	2790.1
30°	3329.0	3186.5	2887.3	2696.9	2595.7
32.5°	3209.2	3036.9	2730.6	2506.0	2412.3
35°	3074.6	2883.8	2554.8	2319.1	2236.5
37.5°	2943.7	2737.7	2390.1	2131.8	2038.5
40°	2805.2	2581.0	2217.9	1952.4	1855.2
42.5°	2663.1	2423.8	2046.1	1769.1	1675.8
45°	2513.5	2262.7	1870.3	1604.4	1514.7
47.5°	2371.5	2106.0	1702.0	1436.1	1354.0
50°	2214.3	1948.8	1537.3	1279.0	1200.8
52.5°	2060.7	1780.2	1380.2	1133.3	1062.3
55°	1911.1	1619.5	1215.5	991.3	920.2
57.5°	1758.0	1458.7	1069.9	860.3	800.4
60°	1600.8	1301.6	916.3	725.8	665.9
62.5°	1447.6	1148.4	785.3	606.0	576.2
65°	1290.5	987.3	650.8	523.8	512.3
67.5°	1140.9	837.7	523.8	459.9	448.8
70°	983.7	692.1	433.7	396.4	381.4
72.5°	834.1	557.1	362.7	332.9	325.4
75°	688.1	426.2	299.2	273.0	269.4
77.5°	542.5	302.8	235.7	220.6	213.1
80°	407.5	217.1	179.4	164.7	164.7
82.5°	284.1	146.0	123.4	115.9	115.9
85°	160.7	82.1	71.0	71.0	71.0
87.5°	59.9	29.8	29.8	26.2	26.2
90°	2.9	34.3	93.4	87.7	90.6
92.5°	59.1	80.1	83.0	85.8	85.8
95°	139.2	165.9	170.7	170.7	165.9
97.5°	231.7	256.5	267.0	267.0	267.0
100°	338.5	360.4	368.0	368.0	365.2
102.5°	451.0	467.2	477.7	480.5	477.7
105°	574.0	581.6	587.3	592.1	592.1
107.5°	696.0	707.5	707.5	709.4	696.0
110°	814.3	829.5	829.5	829.5	821.9



TEST NUMBER: P905535

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	942.0	958.2	955.4	947.7	942.0
115°	1067.9	1083.1	1078.4	1075.5	1067.9
117.5°	1192.8	1213.8	1200.4	1192.8	1185.1
120°	1318.6	1339.6	1318.6	1318.6	1310.1
122.5°	1433.0	1459.7	1446.4	1438.8	1433.0
125°	1553.2	1577.0	1569.4	1560.8	1558.0
127.5°	1670.5	1700.0	1689.5	1678.1	1670.5
130°	1780.1	1814.4	1809.7	1803.9	1793.5
132.5°	1903.1	1929.8	1931.7	1918.4	1910.7
135°	2008.9	2038.5	2044.2	2041.4	2033.7
137.5°	2127.2	2151.0	2155.8	2153.9	2142.4
140°	2231.1	2254.9	2268.3	2268.3	2257.8
142.5°	2337.9	2361.7	2369.3	2372.2	2361.7
145°	2438.9	2458.0	2473.3	2476.1	2465.6
147.5°	2529.5	2553.4	2564.8	2569.6	2559.1
150°	2623.0	2639.2	2649.7	2658.2	2649.7
152.5°	2705.9	2722.1	2735.5	2746.0	2735.5
155°	2788.9	2796.5	2805.1	2818.4	2809.8
157.5°	2860.4	2866.1	2870.9	2889.9	2876.6
160°	2924.3	2930.0	2932.8	2949.0	2937.6
162.5°	2983.4	2983.4	2986.2	3004.3	2991.0
165°	3033.9	3031.0	3031.0	3050.1	3036.8
167.5°	3079.7	3071.1	3071.1	3090.2	3076.8
170°	3114.0	3106.4	3103.5	3122.6	3106.4
172.5°	3137.8	3130.2	3127.3	3146.4	3130.2
175°	3156.9	3149.3	3143.6	3162.6	3146.4
177.5°	3167.4	3159.8	3154.0	3170.2	3154.0
180°	3162.6	3162.6	3162.6	3162.6	3162.6

TEST NUMBER: P905535

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.96	11.78	11.93	12.76	14.05	6.93	7.75	7.90	8.73	10.02
	3H	12.63	13.37	13.62	14.36	15.67	8.12	8.85	9.10	9.85	11.15
	4H	13.24	13.94	14.24	14.93	16.25	8.57	9.27	9.57	10.26	11.58
	6H	13.67	14.31	14.67	15.30	16.63	8.89	9.53	9.90	10.53	11.86
	8H	13.79	14.40	14.80	15.42	16.74	8.98	9.59	10.00	10.61	11.93
	12H	13.85	14.43	14.87	15.44	16.79	9.03	9.61	10.05	10.62	11.97
4H	2H	10.97	11.67	11.98	12.66	13.98	7.52	8.22	8.53	9.21	10.53
	3H	12.80	13.38	13.82	14.41	15.74	8.88	9.45	9.89	10.48	11.81
	4H	13.50	14.02	14.52	15.04	16.40	9.43	9.95	10.44	10.97	12.32
	6H	14.01	14.47	15.04	15.51	16.86	9.85	10.30	10.88	11.34	12.69
	8H	14.19	14.61	15.22	15.64	17.01	9.98	10.40	11.01	11.43	12.80
	12H	14.28	14.67	15.33	15.71	17.08	10.04	10.42	11.09	11.47	12.84
8H	4H	13.46	13.89	14.49	14.92	16.29	9.71	10.13	10.74	11.16	12.53
	6H	14.03	14.38	15.09	15.45	16.82	10.23	10.58	11.28	11.65	13.01
	8H	14.25	14.56	15.31	15.61	17.00	10.42	10.73	11.48	11.78	13.17
	12H	14.39	14.66	15.45	15.71	17.14	10.54	10.81	11.60	11.86	13.29
12H	4H	13.42	13.80	14.46	14.85	16.22	9.71	10.09	10.76	11.14	12.51
	6H	14.01	14.31	15.07	15.37	16.76	10.28	10.58	11.34	11.64	13.02
	8H	14.23	14.50	15.29	15.55	16.98	10.49	10.76	11.55	11.81	13.24

END OF REPORT