

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905548

Luminaire Tested: DFN2DIP-HX4F0-110D080US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905548
REPORT IS A COMBINATION OF REPORTS P899385 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D080US835-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17970.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 157.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905548

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905548

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	88	94	90	86	83	78	76	73	68	66	64	58	57	56
2	91	84	77	72	85	78	73	68	69	64	61	60	56	54	51	49	47
3	83	74	66	60	78	69	62	57	61	55	51	53	49	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	29	26
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	30	27	24
8	55	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3183	3183	3183
5°	3188	3139	3160
10°	3162	3097	3117
15°	3116	3046	3050
20°	3054	2975	2982
25°	2991	2891	2903
30°	2913	2812	2803
35°	2839	2720	2696
40°	2748	2626	2595
45°	2657	2533	2492
50°	2558	2434	2372
55°	2454	2320	2262
60°	2337	2185	2136
65°	2209	2045	1987
70°	2046	1875	1827
75°	1820	1671	1680
80°	1549	1411	1397
85°	1124	961	929

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2657 cd/sqm

TEST NUMBER: P905548

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.8	2.2
10°-20°	1133.5	6.3
20°-30°	1665.7	9.3
30°-40°	1934.7	10.8
40°-50°	1932.3	10.8
50°-60°	1684.9	9.4
60°-70°	1245.5	6.9
70°-80°	704.7	3.9
80°-90°	193.2	1.1
90°-100°	156.6	0.9
100°-110°	497.5	2.8
110°-120°	851.3	4.7
120°-130°	1119.6	6.2
130°-140°	1256.7	7.0
140°-150°	1232.3	6.9
150°-160°	1033.7	5.8
160°-170°	685.6	3.8
170°-180°	239.6	1.3
0°-30°	3202.1	17.8
0°-40°	5136.7	28.6
0°-60°	8753.8	48.7
0°-90°	10897.2	60.6
90°-120°	1505.3	8.4
90°-150°	5113.9	28.5
90°-180°	7073.0	39.4
0°-180°	17970.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4280	4280	4280	4280	4280	
5°	4280	4264	4219	4251	4244	406
15°	4074	4050	3996	4013	3992	1148
25°	3688	3655	3585	3593	3585	1697
35°	3182	3140	3074	3050	3029	1987
45°	2589	2560	2498	2453	2437	1998
55°	1959	1934	1885	1836	1815	1752
65°	1321	1296	1255	1218	1198	1306
75°	691	683	662	638	646	738
85°	169	165	161	148	144	188
90°	2	28	75	70	72	17
95°	111	133	136	136	133	124
105°	459	465	470	474	474	485
115°	854	866	863	860	854	845
125°	1242	1262	1256	1249	1246	1110
135°	1607	1631	1635	1633	1627	1242
145°	1951	1966	1979	1981	1972	1219
155°	2231	2237	2244	2255	2248	1027
165°	2427	2425	2425	2440	2429	685
175°	2526	2519	2515	2530	2517	240
180°	2530	2530	2530	2530	2530	

TEST NUMBER: P905548

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4280.2	4280.2	4280.2	4280.2	4280.2
2.5°	4305.0	4284.5	4239.1	4280.2	4272.3
5°	4280.2	4264.0	4218.6	4251.3	4243.5
7.5°	4251.3	4226.9	4181.5	4214.7	4206.4
10°	4206.4	4177.5	4128.2	4160.9	4148.7
12.5°	4144.4	4119.9	4070.6	4091.1	4082.8
15°	4074.5	4050.0	3996.3	4012.9	3992.4
17.5°	3988.0	3963.6	3909.9	3930.4	3909.9
20°	3893.3	3868.8	3811.2	3823.4	3807.3
22.5°	3799.0	3761.8	3708.1	3708.1	3699.8
25°	3687.6	3654.9	3585.0	3592.9	3585.0
27.5°	3564.0	3535.2	3481.9	3469.7	3449.2
30°	3440.9	3407.7	3346.1	3333.9	3317.3
32.5°	3309.0	3284.6	3218.6	3193.7	3177.1
35°	3181.5	3140.5	3074.5	3049.6	3029.1
37.5°	3037.4	3000.3	2934.4	2905.5	2885.0
40°	2889.4	2856.2	2790.3	2753.6	2737.0
42.5°	2745.3	2712.1	2646.6	2605.1	2580.7
45°	2589.0	2560.1	2498.1	2453.2	2436.6
47.5°	2436.6	2407.8	2341.8	2296.4	2271.9
50°	2275.9	2255.4	2197.7	2140.1	2119.6
52.5°	2119.6	2090.7	2037.5	1992.0	1963.2
55°	1959.3	1934.4	1885.1	1835.7	1815.2
57.5°	1798.6	1778.1	1724.4	1675.0	1658.4
60°	1637.9	1621.8	1564.1	1518.7	1506.5
62.5°	1481.6	1452.8	1411.7	1370.7	1354.1
65°	1321.3	1296.4	1255.4	1218.3	1197.8
67.5°	1156.7	1135.8	1099.1	1070.3	1053.7
70°	1004.3	987.7	950.6	921.8	905.6
72.5°	848.0	831.4	810.9	782.1	769.8
75°	691.2	683.4	662.4	638.0	646.3
77.5°	551.5	534.9	526.6	514.4	502.2
80°	411.8	407.4	399.1	386.9	378.6
82.5°	279.9	279.9	276.0	259.4	259.4
85°	168.6	164.6	160.7	148.0	144.1
87.5°	74.2	65.9	57.6	45.4	41.0
90°	2.3	27.5	74.8	70.2	72.5
92.5°	47.3	64.1	66.4	68.6	68.6
95°	111.4	132.7	136.5	136.5	132.7
97.5°	185.4	205.2	213.6	213.6	213.6
100°	270.8	288.3	294.4	294.4	292.1
102.5°	360.8	373.8	382.1	384.4	382.1
105°	459.2	465.3	469.9	473.7	473.7
107.5°	556.8	566.0	566.0	567.5	556.8
110°	651.4	663.6	663.6	663.6	657.5

TEST NUMBER: P905548

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	753.6	766.6	764.3	758.2	753.6
115°	854.3	866.5	862.7	860.4	854.3
117.5°	954.2	971.0	960.3	954.2	948.1
120°	1054.9	1071.7	1054.9	1054.9	1048.0
122.5°	1146.4	1167.8	1157.1	1151.0	1146.4
125°	1242.5	1261.6	1255.5	1248.6	1246.4
127.5°	1336.4	1360.0	1351.6	1342.5	1336.4
130°	1424.1	1451.5	1447.7	1443.2	1434.8
132.5°	1522.5	1543.8	1545.4	1534.7	1528.6
135°	1607.1	1630.8	1635.4	1633.1	1627.0
137.5°	1701.7	1720.8	1724.6	1723.1	1713.9
140°	1784.9	1803.9	1814.6	1814.6	1806.2
142.5°	1870.3	1889.4	1895.5	1897.8	1889.4
145°	1951.2	1966.4	1978.6	1980.9	1972.5
147.5°	2023.6	2042.7	2051.8	2055.7	2047.3
150°	2098.4	2111.3	2119.7	2126.6	2119.7
152.5°	2164.7	2177.7	2188.4	2196.8	2188.4
155°	2231.1	2237.2	2244.1	2254.7	2247.9
157.5°	2288.3	2292.9	2296.7	2311.9	2301.3
160°	2339.4	2344.0	2346.3	2359.2	2350.1
162.5°	2386.7	2386.7	2389.0	2403.5	2392.8
165°	2427.1	2424.8	2424.8	2440.1	2429.4
167.5°	2463.7	2456.9	2456.9	2472.1	2461.4
170°	2491.2	2485.1	2482.8	2498.1	2485.1
172.5°	2510.3	2504.2	2501.9	2517.1	2504.2
175°	2525.5	2519.4	2514.8	2530.1	2517.1
177.5°	2533.9	2527.8	2523.2	2536.2	2523.2
180°	2530.1	2530.1	2530.1	2530.1	2530.1

TEST NUMBER: P905548

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.22	13.19	13.08	14.07	15.18	11.79	12.76	12.65	13.64	14.75
	3H	13.89	14.76	14.76	15.65	16.79	13.42	14.28	14.29	15.18	16.31
	4H	14.48	15.30	15.37	16.20	17.35	14.01	14.83	14.90	15.73	16.87
	6H	14.89	15.65	15.79	16.55	17.71	14.41	15.17	15.31	16.07	17.23
	8H	15.00	15.72	15.91	16.64	17.80	14.52	15.24	15.43	16.16	17.32
	12H	15.05	15.74	15.96	16.65	17.84	14.57	15.25	15.48	16.17	17.36
4H	2H	12.70	13.52	13.59	14.41	15.56	12.35	13.17	13.24	14.07	15.22
	3H	14.57	15.26	15.48	16.19	17.35	14.18	14.86	15.08	15.79	16.96
	4H	15.29	15.92	16.21	16.84	18.03	14.89	15.51	15.80	16.44	17.62
	6H	15.81	16.35	16.74	17.30	18.49	15.40	15.94	16.33	16.89	18.08
	8H	15.97	16.47	16.90	17.41	18.62	15.55	16.06	16.49	17.00	18.20
	12H	16.05	16.50	17.00	17.46	18.67	15.62	16.08	16.58	17.04	18.25
8H	4H	15.50	16.00	16.43	16.94	18.15	15.14	15.64	16.07	16.58	17.79
	6H	16.14	16.55	17.09	17.54	18.74	15.77	16.19	16.73	17.17	18.37
	8H	16.36	16.73	17.33	17.70	18.92	15.99	16.36	16.96	17.33	18.55
	12H	16.49	16.82	17.47	17.79	19.05	16.11	16.43	17.08	17.40	18.67
12H	4H	15.49	15.94	16.44	16.90	18.11	15.14	15.59	16.09	16.55	17.76
	6H	16.17	16.54	17.13	17.51	18.73	15.81	16.18	16.78	17.16	18.38
	8H	16.41	16.74	17.39	17.71	18.97	16.06	16.38	17.03	17.35	18.62