

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910869

Luminaire Tested: DFN2DIP-HX3F0-090D090US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910869
REPORT IS A COMBINATION OF REPORTS P899298 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-090D090US850-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17317.1 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 163.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910869

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910869

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4778	4778	4778
5°	4784	4699	4730
10°	4734	4604	4573
15°	4667	4448	4333
20°	4579	4235	4039
25°	4488	3998	3755
30°	4367	3754	3396
35°	4249	3492	3081
40°	4128	3222	2720
45°	3988	2922	2392
50°	3843	2620	2073
55°	3691	2297	1766
60°	3516	1961	1451
65°	3313	1619	1303
70°	3068	1300	1175
75°	2759	1139	1064
80°	2313	945	914
85°	1580	615	672

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3988 cd/sqm

TEST NUMBER: P910869

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	386.6	2.2
10°-20°	1061.3	6.1
20°-30°	1490.1	8.6
30°-40°	1624.3	9.4
40°-50°	1492.9	8.6
50°-60°	1172.4	6.8
60°-70°	763.1	4.4
70°-80°	392.8	2.3
80°-90°	109.3	0.6
90°-100°	195.3	1.1
100°-110°	620.6	3.6
110°-120°	1062.1	6.1
120°-130°	1396.8	8.1
130°-140°	1567.9	9.1
140°-150°	1537.5	8.9
150°-160°	1289.7	7.4
160°-170°	855.3	4.9
170°-180°	299.0	1.7
0°-30°	2938.0	17.0
0°-40°	4562.3	26.3
0°-60°	7227.6	41.7
0°-90°	8492.9	49.0
90°-120°	1878.1	10.8
90°-150°	6380.2	36.8
90°-180°	8824.0	51.0
0°-180°	17317.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4125	4125	4125	4125	4125	
5°	4125	4106	4058	4091	4080	391
15°	3924	3882	3756	3685	3648	1106
25°	3562	3442	3196	3043	2986	1638
35°	3069	2878	2550	2315	2232	1921
45°	2509	2258	1867	1601	1512	1937
55°	1908	1616	1213	989	918	1705
65°	1288	986	650	523	511	1277
75°	687	425	299	272	269	726
85°	160	82	71	71	71	184
90°	3	34	93	88	90	17
95°	139	166	170	170	166	155
105°	573	580	586	591	591	605
115°	1066	1081	1076	1074	1066	1054
125°	1550	1574	1566	1558	1555	1385
135°	2005	2035	2040	2038	2030	1550
145°	2434	2453	2468	2471	2461	1521
155°	2784	2791	2800	2813	2805	1281
165°	3028	3025	3025	3044	3031	854
175°	3151	3143	3138	3157	3140	299
180°	3157	3157	3157	3157	3157	

TEST NUMBER: P910869

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4125.1	4125.1	4125.1	4125.1	4125.1
2.5°	4143.8	4125.1	4083.9	4121.6	4114.1
5°	4125.1	4106.5	4057.8	4091.4	4080.3
7.5°	4091.4	4069.3	4017.0	4031.7	4013.0
10°	4046.7	4020.6	3946.2	3934.6	3912.4
12.5°	3990.8	3957.2	3856.2	3834.0	3792.8
15°	3923.5	3882.4	3755.6	3684.7	3647.5
17.5°	3845.1	3785.3	3628.4	3546.5	3486.7
20°	3755.6	3680.8	3494.1	3401.1	3318.7
22.5°	3658.6	3572.6	3355.9	3229.2	3173.4
25°	3561.6	3441.9	3195.6	3042.7	2986.4
27.5°	3445.9	3318.7	3046.2	2870.8	2784.8
30°	3322.7	3180.5	2881.8	2691.8	2590.7
32.5°	3203.0	3031.1	2725.4	2501.2	2407.7
35°	3068.8	2878.3	2549.9	2314.7	2232.3
37.5°	2938.1	2732.6	2385.6	2127.7	2034.7
40°	2799.9	2576.1	2213.7	1948.7	1851.7
42.5°	2658.1	2419.3	2042.1	1765.7	1672.6
45°	2508.8	2258.5	1866.7	1601.3	1511.8
47.5°	2366.9	2102.0	1698.8	1433.4	1351.4
50°	2210.1	1945.1	1534.4	1276.6	1198.5
52.5°	2056.9	1776.8	1377.6	1131.2	1060.3
55°	1907.5	1616.4	1213.1	989.4	918.5
57.5°	1754.7	1456.0	1067.9	858.7	798.9
60°	1597.7	1299.1	914.6	724.4	664.6
62.5°	1444.9	1146.3	783.8	604.8	575.1
65°	1288.0	985.5	649.5	522.8	511.4
67.5°	1138.7	836.1	522.8	459.0	447.9
70°	981.9	690.8	433.0	395.7	380.6
72.5°	832.5	556.1	362.0	332.3	324.8
75°	686.8	425.4	298.7	272.5	268.9
77.5°	541.4	302.2	235.2	220.2	212.7
80°	406.8	216.7	179.0	164.4	164.4
82.5°	283.6	145.7	123.2	115.7	115.7
85°	160.4	82.0	70.9	70.9	70.9
87.5°	59.8	29.7	29.7	26.2	26.2
90°	2.9	34.3	93.3	87.5	90.4
92.5°	59.0	80.0	82.8	85.6	85.6
95°	139.0	165.6	170.3	170.3	165.6
97.5°	231.2	256.0	266.5	266.5	266.5
100°	337.8	359.8	367.3	367.3	364.5
102.5°	450.1	466.3	476.8	479.6	476.8
105°	572.9	580.5	586.2	591.0	591.0
107.5°	694.7	706.1	706.1	708.0	694.7
110°	812.7	828.0	828.0	828.0	820.3



TEST NUMBER: P910869

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	940.2	956.4	953.5	946.0	940.2
115°	1065.9	1081.1	1076.3	1073.5	1065.9
117.5°	1190.5	1211.5	1198.2	1190.5	1182.9
120°	1316.2	1337.0	1316.2	1316.2	1307.5
122.5°	1430.3	1457.0	1443.7	1436.0	1430.3
125°	1550.3	1574.0	1566.5	1557.8	1555.0
127.5°	1667.3	1696.8	1686.3	1674.9	1667.3
130°	1776.7	1811.0	1806.2	1800.5	1790.0
132.5°	1899.5	1926.1	1928.0	1914.7	1907.1
135°	2005.1	2034.6	2040.3	2037.5	2029.9
137.5°	2123.1	2146.9	2151.7	2149.8	2138.4
140°	2226.9	2250.6	2263.9	2263.9	2253.5
142.5°	2333.4	2357.2	2364.8	2367.7	2357.2
145°	2434.4	2453.3	2468.5	2471.4	2461.0
147.5°	2524.7	2548.5	2559.9	2564.7	2554.2
150°	2618.0	2634.2	2644.6	2653.2	2644.6
152.5°	2700.7	2716.9	2730.2	2740.8	2730.2
155°	2783.6	2791.1	2799.8	2813.1	2804.6
157.5°	2854.9	2860.7	2865.4	2884.4	2871.1
160°	2918.7	2924.4	2927.3	2943.4	2932.0
162.5°	2977.7	2977.7	2980.5	2998.6	2985.3
165°	3028.1	3025.2	3025.2	3044.3	3031.0
167.5°	3073.8	3065.3	3065.3	3084.2	3070.9
170°	3108.1	3100.4	3097.7	3116.6	3100.4
172.5°	3131.8	3124.3	3121.4	3140.5	3124.3
175°	3150.9	3143.2	3137.6	3156.7	3140.5
177.5°	3161.3	3153.8	3148.0	3164.2	3148.0
180°	3156.7	3156.7	3156.7	3156.7	3156.7

TEST NUMBER: P910869

CATALOG NUMBER: DFN2DIP-HX3F0-090D090US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.45	13.27	13.42	14.25	15.54	8.42	9.24	9.39	10.23	11.51
	3H	14.12	14.85	15.10	15.84	17.15	9.61	10.34	10.59	11.33	12.64
	4H	14.72	15.41	15.71	16.41	17.73	10.05	10.75	11.05	11.74	13.06
	6H	15.13	15.77	16.14	16.77	18.10	10.37	11.01	11.38	12.01	13.34
	8H	15.26	15.86	16.27	16.88	18.21	10.46	11.07	11.47	12.08	13.41
	12H	15.31	15.89	16.33	16.90	18.25	10.50	11.08	11.52	12.09	13.44
4H	2H	12.46	13.16	13.46	14.15	15.47	9.01	9.71	10.01	10.70	12.02
	3H	14.28	14.86	15.29	15.88	17.21	10.36	10.93	11.37	11.96	13.29
	4H	14.97	15.50	15.99	16.51	17.87	10.90	11.43	11.92	12.44	13.80
	6H	15.48	15.93	16.50	16.97	18.32	11.31	11.77	12.34	12.81	14.16
	8H	15.65	16.07	16.68	17.10	18.47	11.44	11.86	12.47	12.90	14.26
	12H	15.74	16.12	16.78	17.17	18.54	11.50	11.88	12.55	12.93	14.30
8H	4H	14.93	15.36	15.96	16.39	17.76	11.18	11.60	12.21	12.63	14.00
	6H	15.49	15.84	16.55	16.91	18.28	11.69	12.04	12.74	13.11	14.47
	8H	15.70	16.01	16.76	17.07	18.45	11.87	12.18	12.94	13.24	14.62
	12H	15.84	16.11	16.90	17.16	18.58	11.99	12.26	13.05	13.31	14.74
12H	4H	14.89	15.27	15.93	16.31	17.69	11.18	11.56	12.23	12.61	13.98
	6H	15.47	15.77	16.53	16.83	18.22	11.73	12.04	12.80	13.10	14.48
	8H	15.68	15.95	16.75	17.00	18.43	11.94	12.21	13.00	13.26	14.69