

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905557

Luminaire Tested: DFN2DIP-HX4F0-110D120US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905557
REPORT IS A COMBINATION OF REPORTS P899458 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D120US835-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19970.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 185.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905557
CATALOG NUMBER: DFN2DIP-HX4F0-110D120US835-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P905557

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US835-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47	47	47	47
1	98	93	90	86	90	86	83	80	72	70	68	59	58	57	48	47	46	40	40	40	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35	35	35	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26	26	26	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23	23	23	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23	20	20	20	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16	16	16	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15	15	15	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3380	3380	3380
5°	3386	3327	3348
10°	3353	3262	3240
15°	3307	3155	3071
20°	3246	3006	2865
25°	3184	2840	2665
30°	3100	2670	2412
35°	3018	2486	2190
40°	2935	2296	1935
45°	2838	2086	1704
50°	2738	1873	1478
55°	2633	1646	1261
60°	2512	1408	1039
65°	2373	1166	935
70°	2204	941	846
75°	1993	830	770
80°	1686	697	669
85°	1179	467	504

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2862 cd/sqm



TEST NUMBER: P905557

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	2.1
10°-20°	1169.7	5.9
20°-30°	1642.2	8.2
30°-40°	1790.1	9.0
40°-50°	1645.3	8.2
50°-60°	1292.1	6.5
60°-70°	841.1	4.2
70°-80°	432.9	2.2
80°-90°	121.3	0.6
90°-100°	234.8	1.2
100°-110°	746.2	3.7
110°-120°	1276.9	6.4
120°-130°	1679.4	8.4
130°-140°	1885.0	9.4
140°-150°	1848.5	9.3
150°-160°	1550.6	7.8
160°-170°	1028.3	5.1
170°-180°	359.4	1.8
0°-30°	3238.0	16.2
0°-40°	5028.1	25.2
0°-60°	7965.5	39.9
0°-90°	9360.8	46.9
90°-120°	2257.9	11.3
90°-150°	7670.8	38.4
90°-180°	10609.0	53.1
0°-180°	19970.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	203
90°	3	41	112	105	109	20
95°	167	199	205	205	199	186
105°	689	698	705	710	710	727
115°	1281	1300	1294	1291	1281	1267
125°	1864	1892	1883	1873	1870	1666
135°	2411	2446	2453	2450	2440	1863
145°	2927	2950	2968	2971	2959	1829
155°	3347	3356	3366	3382	3372	1540
165°	3641	3637	3637	3660	3644	1027
175°	3788	3779	3772	3795	3776	360
180°	3795	3795	3795	3795	3795	



TEST NUMBER: P905557

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	3.4	41.2	112.1	105.3	108.7
92.5°	70.9	96.1	99.5	103.0	103.0
95°	167.0	199.1	204.8	204.8	199.1
97.5°	278.0	307.8	320.4	320.4	320.4
100°	406.2	432.5	441.6	441.6	438.2
102.5°	541.2	560.6	573.2	576.7	573.2
105°	688.8	697.9	704.8	710.5	710.5
107.5°	835.2	849.0	849.0	851.2	835.2
110°	977.1	995.4	995.4	995.4	986.3



TEST NUMBER: P905557

CATALOG NUMBER: DFN2DIP-HX4F0-110D120US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1130.4	1149.9	1146.4	1137.3	1130.4
115°	1281.4	1299.8	1294.0	1290.6	1281.4
117.5°	1431.3	1456.5	1440.5	1431.3	1422.2
120°	1582.4	1607.5	1582.4	1582.4	1572.1
122.5°	1719.7	1751.7	1735.7	1726.5	1719.7
125°	1863.8	1892.4	1883.3	1873.0	1869.5
127.5°	2004.6	2040.0	2027.4	2013.7	2004.6
130°	2136.1	2177.3	2171.6	2164.7	2152.1
132.5°	2283.7	2315.8	2318.0	2302.0	2292.9
135°	2410.7	2446.2	2453.1	2449.6	2440.5
137.5°	2552.6	2581.2	2586.9	2584.6	2570.9
140°	2677.3	2705.9	2721.9	2721.9	2709.3
142.5°	2805.5	2834.1	2843.2	2846.6	2834.1
145°	2926.7	2949.6	2967.9	2971.4	2958.8
147.5°	3035.4	3064.0	3077.8	3083.5	3070.9
150°	3147.6	3167.0	3179.6	3189.9	3179.6
152.5°	3247.1	3266.5	3282.6	3295.2	3282.6
155°	3346.6	3355.8	3366.1	3382.1	3371.8
157.5°	3432.5	3439.3	3445.0	3467.9	3451.9
160°	3509.1	3516.0	3519.4	3538.9	3525.1
162.5°	3580.0	3580.0	3583.5	3605.2	3589.2
165°	3640.7	3637.3	3637.3	3660.1	3644.1
167.5°	3695.6	3685.3	3685.3	3708.2	3692.2
170°	3736.8	3727.6	3724.2	3747.1	3727.6
172.5°	3765.4	3756.2	3752.8	3775.7	3756.2
175°	3788.3	3779.1	3772.3	3795.1	3775.7
177.5°	3800.9	3791.7	3784.8	3804.3	3784.8
180°	3795.1	3795.1	3795.1	3795.1	3795.1



TEST NUMBER: P905557
 CATALOG NUMBER: DFN2DIP-HX4F0-110D120US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.08	11.88	12.07	12.88	14.20	7.05	7.86	8.04	8.85	10.17
	3H	12.76	13.48	13.76	14.48	15.82	8.24	8.96	9.24	9.97	11.31
	4H	13.36	14.04	14.38	15.05	16.40	8.69	9.37	9.70	10.38	11.73
	6H	13.78	14.41	14.81	15.43	16.78	9.01	9.64	10.04	10.65	12.01
	8H	13.91	14.51	14.94	15.54	16.89	9.10	9.70	10.13	10.73	12.09
	12H	13.97	14.54	15.01	15.56	16.94	9.15	9.71	10.18	10.74	12.12
4H	2H	11.09	11.78	12.11	12.79	14.13	7.64	8.33	8.66	9.34	10.68
	3H	12.92	13.49	13.95	14.53	15.89	8.99	9.56	10.02	10.60	11.96
	4H	13.61	14.13	14.65	15.16	16.55	9.54	10.06	10.58	11.09	12.47
	6H	14.13	14.57	15.17	15.63	17.01	9.96	10.41	11.01	11.46	12.84
	8H	14.30	14.72	15.35	15.77	17.16	10.09	10.51	11.14	11.55	12.95
	12H	14.40	14.77	15.46	15.83	17.23	10.16	10.53	11.22	11.59	12.99
8H	4H	13.58	14.00	14.63	15.04	16.44	9.82	10.24	10.87	11.28	12.68
	6H	14.15	14.49	15.22	15.58	16.97	10.34	10.68	11.41	11.77	13.16
	8H	14.36	14.66	15.44	15.74	17.15	10.53	10.84	11.61	11.91	13.32
	12H	14.50	14.77	15.58	15.83	17.29	10.65	10.92	11.73	11.99	13.44
12H	4H	13.53	13.91	14.60	14.97	16.37	9.83	10.20	10.89	11.26	12.66
	6H	14.12	14.42	15.20	15.50	16.91	10.39	10.69	11.47	11.77	13.18
	8H	14.34	14.61	15.42	15.68	17.13	10.60	10.87	11.68	11.93	13.39